



C2G 25ft (7.6m) Pro-Audio XLR Male to XLR Female Cable Part No. CG-40061



Use this XLR to XLR cable to connect unbalanced sources to balanced XLR inputs. This pro-audio cable is made from 22 AWG twisted pair audio cable under an aluminum foil shield and 60% copper braid for maximum shielding from noise. The highly flexible 7mm PVC jacket reduces the risk of the cable kinking and damaging the conductors.

Bright nickel plating on solid brass connectors resists wear from reconfiguring and moving equipment from one venue to another. Spring strain relief on the 1/4in plug and a chuck strain relief inside the XLR reduce the effects of age on the solder joints and contacts.

Features & Benefits

22 AWG conductor construction

Foil and braided shield to protect from interference

Highly flexible jacket

Nickel-plated connectors

Specifications

General Info

Product Line	C2G	UPC Number	757120400615
Country Of Origin	VietNam	Application Sector	Residential, Commercial
Warranty Type	Lifetime	Type	Cable

Dimensions

Cable Length	25 ft
--------------	-------

Additional Information

Prop 65 Warning Required	Yes	Prop 65 Warning Language	Cancer and Reproductive Harm
--------------------------	-----	--------------------------	------------------------------

Technical Information

Jacket Material	PVC (Polyvinyl Chloride)	Cable Type	Audio, Adapter
Jacket Rating	Standard Non-Rated	Adapter Rear	XLR 3-pin Female

Adapter Front

XLR 3-pin Male
