


Technical Specifications

HP E24i G4 WUXGA Monitor




1. OSD Buttons

Front

2. Power Button

Technical Specifications

HP E24i G4 WUXGA Monitor



1. Power Connector
2. DisplayPort™
3. HDMI Port
4. VGA Port

Back

5. USB-B Port
6. USB-A Ports (2)
7. USB-A Ports (2)

Technical Specifications

Models: 9VJ40AA

Panel Specifications	Display Size (Diagonal)	24-in
	Display Panel Type	IPS
	Micro-Edge Bezel	Yes, 3-sided
	Native Resolution/Timing	1920 x 1200 @60Hz
	Panel Bit Depth	8bit (6bit + FRC)
	Aspect Ratio	16:10
	Brightness - Typical	250 cd/m ²
	Static Contrast Ratio - Typical	1000:1
	Static Contrast Ratio - Minimum	700:1
	Dynamic Contrast Ratio (DCR)	5M:1
	Flicker Free	Yes
	Pixel Pitch	0.2745 (H) x 0.2745 (V)
	Pixels Per Inch (PPI)	94
	Backlight Lamp Life (to half brightness - in hours)	30k minimum
	Anti-Glare Panel	Yes
	Response Time - Typical	5ms GtG (with overdrive)
	Horizontal Viewing Angle (typical CR>10)	178°
	Vertical Viewing Angle (typical CR>10)	178°
	Panel Active Area (w x h)	527.04(H) x 296.46(V) mm
	Preset Graphic Modes/Supported Resolutions	640 x 480 @60Hz
		720 x 400 @70Hz
		800 x 600 @60Hz
		1024 x 768 @60Hz
		1280 x 720 @60Hz
		1280 x 800 @60 HZ
		1280 x 1024@60Hz
		1440 x 900 @60Hz
		1600 x 900 @60Hz
		1680 x 1050 @60Hz
	Maximum Resolution	1920 x 1200 @60Hz
	Recommended Resolution	1920 x 1200 @60Hz
	Vertical Scan Range	50-60Hz
	Horizontal Scan Range	30-80kHz
	Default Color Temperature	Neutral (6500K)
	Maximum Pixel Clock Speed	170MHz

NOTE: Performance specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.

Color Gamut Coverage	NTSC	72%
Color Management	Color Space / Subsampling Support	RGB 4:4:4, YCBCR 4:4:4, YCBCR 4:2:2
	Default Color Temperature	Neutral (6500 K)

Technical Specifications

Monitor Specifications	Low Blue Light Modes	Yes, HP Eye Ease (TÜV Low Blue Light Hardware Solution certified)
	RGB Channel Adjust	Yes
	Exterior Color of Monitor Bezel and Stand	Black head, Silver stand
	Plug & Play	Yes
	Tilt	-5° to +23°
	Swivel	+/-45°
	Pivot	+/-90°
	Height Adjustment Range	150mm
	VESA Mounting	100mm x 100mm
	Security Lock Ready	Yes
On Screen Display (OSD)	Detachable Base	Yes, ships detached
	Warranty	Based on region
	On Screen Display User Controls	Brightness+, Color, Image, Input, Power, Menu, Management, Information
	Monitor Control Buttons or Switches	Menu, Minus ("-")/Information, Plus ("+") /Viewing Mode, OK/Next Active Input, Power
Connector Types	User-Assignable Function Buttons	Yes, 3 (6 Options)
	Languages	10 (German, Dutch, T-Chinese and S-Chinese, English, Spanish, French, Italian, Japanese, Portuguese)
	DisplayPort™	1 DisplayPort™ 1.2 in
USB Port Specifications	HDMI	1 HDMI1.4
	VGA	1
	HDCP support	Yes, (DisplayPort™ and HDMI)
	USB Version	3.2
	USB Hub	Yes
Special Features	Downstream Ports	4 Ports
	Upstream Ports	1 Port
	Fast Charging USB Ports	1 Port (Side) (USB-A)
	Power Output Maximum	Fast Charging: 7.5 W
	User Presets	Yes
Power & Operating Specs	User Updateable Firmware	Yes
	Power Supply	Internal
	Power Source	100 – 240 VAC 50/60 Hz
	Power Consumption - Maximum	53 W
	Energy Saving/Standby Mode	0.5 W
EU Energy Efficiency Class (ERP lot-5)	Power Consumption - Typical	36 W
	Power cable length	1.9 m
	On-mode Power Consumption	16 W
	Annual Power Consumption	24 kWh

Technical Specifications

	Energy Efficiency Class	D
	Visible Screen Size	24" / 60.69 cm Diagonal
Operating Conditions	Operating Temperature - Celsius	5° – 35°C
	Operating Temperature - Fahrenheit	41°C – 95°F
	Non-operating Temperature - Celsius	–34° – 60°C
	Non-operating Temperature - Fahrenheit	–29° – 140°F
	Operating Humidity	20 – 80% Relative Humidity (non-condensing)
	Non-operating Humidity	5 – 95%
	Operating Altitude	0 – 5,000 m (16,400 ft.)
	Non-operating Altitude	0 – 12,192 m (40,000 ft.)
Environmental Features and Certifications	Mercury-free LED display backlighting	Yes, Mercury-free LED backlighting
	Arsenic-Free Display Glass	Yes
	Low Halogen*	Yes
		GSE HP-00011-01B, table 2 defines low-halogen (BFR, CFR, PVC)
	Agency Approvals and Certifications	WW certificate CE, CB, KC/KCC/NOM/ISO 9241-307/ EAC/TUV-GS/cTUVus/PSB/CCC/CEL/ISC/VCCI/FCC/BSMI/Vietnam MEPS/Australian-New Zealand MEPS/WEEE/BIS/CEC/E- Standby/Low Blue Light/CECP/TUV-S/CECP
	Microsoft WHQL Certification	Win 10, Win 8, Win 7
	ENERGY STAR®	Yes, ENERGY STAR® 8
	EPEAT® Registered*	Yes
	TCO Certified	Yes
	China Energy Label	CEL Grade 1
	SmartWay Transport Partnership - NA only	Yes (NA SKU)

*External power supplies, power cords, cables and peripherals are not Low Halogen. Service parts obtained after purchase may not be Low Halogen.

NOTE: DisplayPort™ and the DisplayPort™ logo are trademarks owned by the Video Electronics Standards Association (VESA®) in the United States and other countries.

	Contains Recycled Plastics	85% recycled content by total weight	
Unit Product/Package Specifications	Product Dimensions (Unpacked with stand) (W x D x H)	Metric	Imperial
		53.2 x 20.69 x 50.96 cm	20.94 x 8.15 x 20.06 in
	Product Dimensions (Packed) (W x D x H)	60.5 x 42 x 22.4 cm	23.82 x 16.54 x 8.82 in
	Display Head Dimensions (Unpacked without stand) (W x D x H)	53.2 x 4.7 x 35.27 cm	20.94 x 1.85 x 13.88 in
	Base Area Footprint (w x d mm)	260 x 207 mm	10.23 x 8.15 in
	Bezel Measurements	Bottom 20.73 mm (display chin)	Bottom 8.16 in (display chin)

Technical Specifications

Pallet Information	Product Weight (Unpacked with stand)	6.06 kg	13.36 lb
	Product Weight (Packed)	9.12 kg	20.1 lb
	Product Weight (Head Only)	3.6 kg	7.94 lb
	Pallet Dimensions (L x W x H)	1220 x 1140 x 2243 mm	48.03 x 44.88 x 88.31 in
	Pallet Total Weight (L x W x H)	40" GQ: 384 kg	40" GQ: 847 lbs
		40" HQ: 476 kg	40" HQ: 1050 lbs
	Pallet Layers	GQ: 4 HQ: 5	
	Pallet Product per Layer	8	
	Total Products per Pallet	GQ: 32	
		HQ: 40	
	Container Load, 20-Foot	460	
	Container Load, 40-Foot	960	
	Container Load, 40-Foot HighQ	960	
Software Included	HP Display Center		
What's in the box?	1 HDMI	(1.8 m) 5.9 ft	
	1 DisplayPort™ (DisplayPort™ 1.2)	(1.8 m) 5.9 ft	
	1 USB-A-B cable	(1.8 m) 5.9 ft	
	1 Power Cord	(1.9 m) 6.2 ft	
	1 QSP		
	1 Doc-Kit		
User Guide and Warranty Languages	User Guide Languages	English, Arabic, S. Chinese, T. Chinese, Czech, Danish, Dutch, Finnish, French, German, Greek, Hungarian, Italian, Japanese, Kazakh, Korean, Norwegian, Polish, Brazilian Portuguese, Russian, Slovenian, Spanish, Swedish and Turkish.	
	Warranty Languages	English, Arabic, S. Chinese, T. Chinese, Czech, Danish, Dutch, Finnish, French, German, Greek, Hungarian, Italian, Japanese, Kazakh, Korean, Norwegian, Polish, Brazilian Portuguese, Russian, Slovenian, Spanish, Swedish and Turkish.	

Technical Specifications

Copyright © 2021 HP Development Company, L.P.

The information contained herein is subject to change without notice. The only warranties for HP products are set forth in the express limited warranty statements accompanying such products. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Microsoft and Windows are registered trademarks or trademarks of Microsoft Corporation in the U.S. and/or other countries.

ENERGY STAR is a registered trademark owned by the U.S. Environmental Protection Agency.

Summary

Change Log

January 3, 2021	V1 to V2		Techspecs updated
February 28, 2021	V2 to V3		Energy Efficiency Class Updated
April 9, 2021	V3 to V4		Power Consumption updated
April 13, 2021	V4 to V5	Update	VESA Mounting Specs
	V5 to V6		