Product data sheet

Specifications

Easy UPS 3S Maintenance Bypass Panel, single unit, 10-20kVA 208V

E3SBPSU10K20F

Overview

Presentation	Maintenance bypass panel for complete isolation of the UPS during service operations.
Lead time	Usually Ships within 2 Weeks

Physical

Color	White
Height	23.62 in (60 cm)
Width	21.65 in (55 cm)
Depth	10.24 in (26 cm)
Net Weight	66.14 lb(US) (30 kg)

Environmental

Ambient air temperature for operation	32…104 °F (0…40 °C)
Relative Humidity	0…95 % non-condensing
Operating altitude	0...6561.68 ft (0...2000 m)
Ambient Air Temperature for Storage	-13…131 °F (-25…55 °C)
Storage Relative Humidity	0…95 % non-condensing

Ordering and shipping details

GTIN	731304427599

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	19.69 in (500 mm)
Package 1 Width	47.24 in (1200 mm)
Package 1 Length	31.50 in (800 mm)
Package 1 Weight	92.59 lb(US) (42 kg)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: carbon black, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACh Regulation	REACh Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
RoHS exemption information	Yes

Recommended replacement(s)