



HP 125 USB WD KBD (Bulk 12) (266C9A6)

Overview

Every Day Productivity



Think how much you use your keyboard. That's why we've taken the time to design a keyboard that is comfortable to use so you can work productively every day - and all day if necessary.

Designed for Comfort

The three zone, full size HP 125 Wired Keyboard includes 0-6 degree adjustable feet so you'll be able to type comfortably. Plus, an LED indicator for the Caps, Number and Function lock easily reminds you when these features are active.

Responsibly Made

You should feel good about the products you buy and use. Rest assured, this keyboard is responsibly made with over 50% of the plastics comprised of recycled materials[1].

Plug and Play Connectivity

Connecting some peripheral devices can be a complex and time consuming task. Who needs that? With easy plug and play USB connectivity, you can get your keyboard connected quickly so you can get on with your work day.

Easy Cleaning

Use your keyboard every day and it will accumulate dirt and grime. Over time, this can affect how it performs. Because it was specifically designed to withstand every day cleaning with disinfecting wipes[2], this is one keyboard that's a snap to keep clean.

[1] Recycled plastic content percentage is based on the definition set in the IEEE 1680.1-2018 EPEAT standard.

[2] Select household wipes can be safely used to clean HP Elite Presenter Mouse, HP Premium keyboard (wireless and USB) and HP desktop wired 320 KB/Mouse up to 1,000 wipes: See wipe manufacturer's instructions for disinfecting and the HP cleaning guide for HP tested wipe solutions at How to Sanitize Your HP Device Whitepaper: <http://h20195.www2.hp.com/v2/GetDocument.aspx?docname=4AA7-7610ENW>

Specifications

Minimum dimensions (W x D x H)	6.3 x 11.2 x 3.6 cm
Minimum dimensions (W x D x H)	2.48 x 4.41 x 1.42 in
Weight	0.08 kg
Weight	0.17 lb
Sustainable impact specifications	50% post-consumer recycled plastic
UPC number	(A2M) 195161019913; (A2Q) 195161019937; (AB0) 195161058707; (AB1) 195161433214; (AB2) 195161019951; (AB4) 195161058714; (AB6) 195161433238; (AB7) 195161019968; (AB8) 195161433245; (AB9) 195161019982; (ABA) 195161019999; (ABB) 195161433252; (ABC) 195161020001; (ABD) 195161020025; (ABE) 195161020032; (ABF) 195161020575; (ABH) 195161020582; (ABJ) 4580511788162; (ABM) 195161020599; (ABN) 195161020605; (ABS) 195161020629; (ABT) 195161020636; (ABU) 195161020643; (ABV) 195161020650; (ABX) 195161020667; (ABY) 195161020681; (ABZ) 195161020704; (AC0) 195161020711; (AC3) 195161433269; (AC4) 195161433283; (ACB) 195161020728; (ACH) 195161433290; (ACJ) 195161058721; (AKB) 195161020735; (AKC) 195161020742; (AKD) 195161020759; (AKE) 195161020766; (AKL) 195161058738; (AKQ) 195161020773; (AKR) 195161020780; (AKS) 195161020353; (AR4) 195161020360; (ARK) 195161020377; (B15) 195161020384; (BCM) 195161433313; (BED) 195161020391; (UUF) 195161020407; (U UW) 195161433344; (UUZ) 195161020414
Manufacturer Warranty	One-year limited warranty.
What's in the box	Keyboard; QSP; Warranty Card; Product Notice

Additional specifications

Cable length	180 cm
Cable length (imperial)	70.86 in
Compatibility	Compatible with PCs with available USB-A port.
Compatible Operating Systems	Windows 11; Windows 10
Connection type	Wired USB Type-A
Connector description	USB Type-A
Country of origin	Made in China
Hot keys	1
Keyboard features	Spill resistant; Tilt adjustable
Keyboard type	Full size; 3-zone layout
Keys structure	Plunger; 3.0 mm; Standard key travel
LED indicator	Caps lock; Num lock
Product subgroup	Keyboard
Special keys	PC lock
UNSPSC code	43211706

Disclaimer — Copyright

Actual product may vary from image shown.

© Copyright 2023 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.