



MP RANGER

Mobile printer for mobile receipt / label issuance for logistics and delivery

MP Ranger is a latest generation mobile printer and represents the evolution of Custom's range of mobile printers. It can print on **thermal paper** in roll format, either on plain paper or peel-off format **labels**. Complete with sensors for displaying status and **battery level**, it allows the printing of 1D and 2D barcodes (QR CODE). It can handle rolls with paper width of 76.2 mm or 80 mm using the special reducer included in the package, and is designed to be used in **outdoor working contexts**, thanks to the **IP54 protection** to resist splashing of liquids and dust for use in adverse weather conditions and resistance to falls from 1 meter.

The operational equipment is completed by a **clip for belt fastening** and as an accessory the practical case with **shoulder strap** is available for greater protection. The printer is equipped with different charging options, from simple connection via USB Type-C to positioning on single charging cradles. MP Ranger can be connected to any mobile device, from simple phones, to specialized terminals, to handheld mobile computers and tablets with Bluetooth and Wi-Fi functionality thanks to the **Wireless technology**.



ACCESSORIES

- Case with shoulder strap
 - Single charging cradle
-

TECHNICAL SHEET

| | |
|-------------------------|--|
| Printing Method | Thermal printing |
| Number of dots | 8 dots / mm |
| Resolution | 203 dpi |
| Printing speed (mm/sec) | 110 mm/sec |
| Character set | PC437, PC850, PC860, PC863, PC865, PC866, PC858 (euro), Cinese esteso GB 18030-2000, Koreano PC949 |
| Supported Barcode | Codabar, Code 32, Code 39, Code 93, Code 128, EAN-8, EAN-13, GS1 dataBar Stacked, GS1 dataBar Stacked Omnidirectional, GS1 DataBar Expanded Stacked, ITF, UPC-A, UPC-E, Aztec, Aztec Rune, Data Matrix, PDF417, QRcode, Micro QRCode |
| Printing Format | Height/width from 1 to 8, negative, underlined, italic, expanded |
| Printing Direction | Normal, 90°, 180°, 270° |
| Supplies | Continuous paper and label with gap/notch |
| Roll width | 76,2mm and 80mm |
| Paper weight | from 55 to 100 g/m ² |
| Paper thickness | from 61 to 100 μ m |
| Printing width | 72 mm |
| Roll Dimension | max 40mm |
| Emulation | CUSTOM/POS |
| Interfaces | USB type-C 2.0 Full Speed Wifi 802.11 b/g/n Bluetooth 4.2 BLE |
| Tool software | PrinterSet, Custom Windows API |
| Data Buffer | 16 Kb |
| Flash Memory | 2 MB + 8 MB flash SPI |
| RAM Memory | 640 Kb + 8 MB SDRAM |
| Graphic Memory | 3 MB for logos (maximum width 576 dot) + 5 MB per font |
| Driver | Windows [®] (32/64 bit) – only on request WHQL and silent installation |
| Power supply | USB standard port from PC 5 V, 0.5 A (Slow charge) |
| Battery pack | Li-ion 7.2 V 2.6 Ah 18.72 Wh |
| Battery cycles | 750 |
| Print autonomy | 720 minutes x 300 ticket |
| MTBF | 3246 hours (electronic board) |
| Head Life | 50Km / 100 M pulses (12.5% pulses) |
| Sensors | Presence of paper, presence of alignment notch, head temperature, open cover, NFC |
| Operating temperature | -10°C + 50°C |
| Dimensions | 149(L) x 53(H) x 122(P) mm |
| Weight | 475gr (battery included) |

MODELS



911MM010200P33

MOBILE PRINTER MP RANGER

Via Berettine, 2 - 43010 Fontevivo PR - VAT: IT02498250345 - TEL: +39 0521 680111 - FAX: +39 0521 610701 - UNIQUE CODE: 8RQN7AZ

The technical data on this website are not binding and may be changed without advanced notice.

Last update: 21 December 2023