



## MAINSTREAM COMPUTING FOR A VARIETY OF BUSINESS USES



ThinkCentre M7 Series desktops offer enterprise security features, a wide range of configurations and expansion options, and reliability trusted by leading businesses across the globe.

# ThinkCentre M75s Gen 2

Smarter  
technology  
for all

Lenovo

Looking for a versatile device to support existing or new desk workers in your company? This compact, space-saving desktop can be configured to meet a wide variety of user expectations - from basic admin use to extensive productivity tasks. It comes with thoughtful features like Smart Power-On to which enables the PC to be started via a keyboard shortcut instead of reaching for the power button.



## REASONS TO BUY

For employees working with data or graphics, configure the device with 128GB DDR4 memory to boost multitasking performance, AMD Radeon 520 graphics, up to 2x fast SSD storage drives, and the latest AMD Ryzen™ 9 Pro processor.

There are 9x USB ports including 5 located on the front of the device. If data security is a concern, Smart USB protection can block data transfer but still enable keyboards, mice and printers to be used.

Optimized to reduce power consumption with EPEAT Gold and Energy Star 8.0 certifications.

# ThinkCentre M75s Gen 2

## KEY SPECIFICATIONS

Processor	Up to AMD Ryzen 9 Pro processor
Operating System	Powered by Windows 10 Pro
Graphics	AMD Radeon Vega 11, 8 or 3, optional AMD Radeon 520 2GB
Memory	Up to 128GB DDR4-3200
Storage	<b>Internal storage:</b> up to 1x 3.5" 2TB SATA HDD + 1x 2.5" 1TB SATA HDD or 2x 2.5" 256GB SATA SSD <b>M.2 SSD:</b> up to 1x 1TB M.2 PCIe NVMe
Optical	Optional DVD-ROM or DVD burner
Expansion Slots	PCIe x16, low-profile PCIe x1, low-profile
Power Supply	<i>One of the following</i> 180W 85%   260W 85%   310W 92%
Dimensions	Width: 93mm (3.6") Depth: 298mm (11.7") Height: 340mm (13.4")
Weight	Starting at 5.3kg (11.7lb)

## GREEN CERTIFICATIONS

EPEAT Gold, Energy Star 8.0.

## CONNECTIVITY

Front I/O	2x USB 3.2 Gen 2, 2x USB 3.2 Gen 1, 1x USB 3.2 Type-C Gen 1, 1x microphone (3.5mm), 1x headphone / microphone combo jack (3.5mm), optional 3-in-1 card reader
Rear I/O	4x USB 2.0, 1x serial (9-pin), 1x ethernet (RJ-45), 2x DisplayPort, 1x HDMI, 1x line-out (3.5mm); Optional: 2x USB 3.2 Gen 1 via PCIe x1, 2x USB 3.2 Type-C Gen 2 via PCIe x4, 1x 2nd serial (9-pin), 1x parallel (25-pin)
Optional Rear Ports	<i>One of the following</i> 1x Parallel   1x Parallel + 1x Serial   1x Parallel + 1x Serial + 2x USB 3.2 Gen1   1x Parallel + 2x USB 3.2 Gen1   1x Serial   1x Serial + 2x USB 2.0 + 2x USB 3.2 Gen1   1x Serial + 2x USB 3.2 Gen1   2x USB 3.2 Gen1   2x USB-C 3.2 Gen2   4x Serial
WLAN + Bluetooth	<i>One of the following</i> Intel 9260 11ac, 2x2 + BT5.0   Intel AX200 11ax, 2x2 + BT5.1   RTL8822CE 11ac, 2x2 + BT5.0   RTL8852AE 11ax, 2x2 + BT5.2
Ethernet	<i>One of the following</i> BN8E88 + Integrated 100/1000M   Integrated 100/1000M   RTL8111FP + Integrated 100/1000M

## SECURITY & PRIVACY

Chassis Intrusion Switch  
E-Lock  
Kensington lock slot  
Padlock slot  
Smart USB protection  
Hardware TPM

## MANAGEABILITY

DASH 1.1  
Non-DASH

## OPTIONAL MECHANICAL PERIPHERALS

ThinkCentre Dust Filter

## Recommended for this device



### ThinkVision T27i-10

27" Full HD monitor with wide viewing angle and 1000:1 contrast ratio

1x HDMI, 1x DisplayPort, 1x VGA, 4x USB3.0, 1x USB3.0 Type-B upstream, audio out

Lift, Tilt, Pivot, Swivel stand for viewing comfort



### ThinkVision T24i-10

23.8" Full HD monitor with 72% NTSC colour gamut & anti-glare coating

1x HDMI, 1x DisplayPort, 1x VGA, 4x USB3.0, 1x USB3.0 Type-B upstream, audio out

Lift, Tilt, Pivot, Swivel stand for viewing comfort