



C2G
15ft (4.6m) Cat5e Non-Booted Unshielded (UTP) Ethernet Network Patch Cable - Blue
Part No. CG-22709



For fast Ethernet networks that require bandwidth-intensive voice, data, or video distribution applications. Meets all Cat5e TIA/EIA standards, and drastically reduces both impedance and structural return loss (SRL). Each of the individual pairs is bonded together to help maintain the twist-spacing throughout the line right up to the termination point. Constructed from high quality copper cable, this design minimizes Near-End Crosstalk (NEXT) levels. Available in a variety of colors to easily color-code your network installation.

Features & Benefits

Designed for network adapters, hubs, switches, routers and more

Available in 10 colors to color-code a network

CMG In-Wall Rated Jacket

Constructed with unshielded twisted pair wires

Available in lengths up to 150ft

Specifications

General Info

Product Line	C2G	Color	Blue
UPC Number	757120227090	Country Of Origin	China
Application Sector	Commercial, Industrial, Residential	Warranty Type	Lifetime
Type	Cable		

Dimensions

Product Length US	15.0 FT	Cable Length	15 ft
Outside Diameter	5.3 mm		

Listing Agencies / 3rd Party Agencies

CE Certified	Yes	REACH Compliant	Yes
--------------	-----	-----------------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Jacket Material	PVC (Polyvinyl Chloride)	Category Performance Rating	Cat 5e
Wire Gauge	24 AWG	Shielded/Unshielded	Unshielded
Conductor	4-Pair Twisted	Cable Type	Ethernet Patch Cable, Unbooted, Unshielded (UTP)
Jacket Rating	Standard / Non-Rated	Cable Diameter	5.3 mm
Indoor/Outdoor	Indoor	Connector 2	RJ-45 Male
Connector 1	RJ-45 Male		