

This 48-Port Cat6 110-Type Patch Panel is made for optimum performance with black electrostatic powder-coated steel and 50 micron gold-plated contacts. Every panel comes in traditional 6-port module format with 110-type terminations, and meets and exceeds EIA/TIA TSB-40 Cat6 connecting hardware specifications.



This high density 19-inch 2RU panel design lets you mount in any standard 19-inch rack or cabinet, accommodates top, bottom or side cable entry, and also saves valuable space in your rack.

The 48-Port Cat6 110-Type Patch Panel enables effortless installation with easy identification vibrant color labels for 568 A or B specifications. Each terminal offers a wide 110 termination layout and a write-on designation label with a clear holder on the front and numbering on both the front and back to provide a quick, easy way to identify cable runs.

Features & Benefits

Designed to support Cat6 cabling infrastructure
 Meets or exceeds EIA/TIA TSB-40 Cat6 specifications

Large, highly visible labels for 568A and 568B wiring schemes
 Modular 110 punch down block termination

Specifications

General Info

Product Line	C2G	Color	Black
UPC Number	757120372004	Country Of Origin	Mexico
Application Sector	Commercial	Type	Patch Panel

Additional Information

Prop 65 Warning Required	Yes	Prop 65 Warning Language	Cancer and Reproductive Harm
--------------------------	-----	--------------------------	------------------------------

Technical Information

Number of Ports	48	Adapter Front	RJ-45 Female
-----------------	----	---------------	--------------