




**C2G**  
**9ft (2.7m) Cat6 Snagless Unshielded (UTP) Ethernet Network Patch Cable - Orange**  
Part No. CG-04020



For fast Ethernet and Gigabit computer networks that require bandwidth-intensive voice, data, or video distribution applications. Meets all Cat6 TIA/EIA standards, and drastically reduces both impedance and structural return loss (SRL). Each of the individual pairs is bonded together to help maintain the twist-spacing throughout the line right up to the termination point. Constructed from high quality copper cable, this design minimizes Near-End Crosstalk (NEXT) levels. The molded, snagless boot prevents unwanted cable snags during installation and provides extra strain relief. Available in a variety of colors to easily color-code your network installation.

## Features & Benefits

Snagless design protects clips when plugging and unplugging	Standard RJ45 connectors and unshielded twisted pair wires
Available in 10 colors to color-code a network	Available in lengths up to 150ft

## Specifications

### General Info

Product Line	C2G	Color	Orange
UPC Number	757120040200	Country Of Origin	Vietnam
Features	PoE (Power Over Ethernet)	Application Sector	Commercial, Industrial, Residential
Warranty Type	Lifetime	Type	Cable

### Dimensions

Product Length US	9.0 FT	Cable Length	9 ft
Outside Diameter	5.69 mm		

### Listing Agencies / 3rd Party Agencies

CE Certified	Yes	REACH Compliant	Yes
--------------	-----	-----------------	-----

### Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Jacket Material	PVC (Polyvinyl Chloride)	Category Performance Rating	Cat6
Wire Gauge	24 AWG	Shielded/Unshielded	Unshielded
Shield Type	UTP	Cable Type	Ethernet Patch Cable
Jacket Rating	Standard / Non-Rated	Cable Diameter	6.2 mm
Connector Type	Booted, Snagless	Indoor/Outdoor	Indoor
Connector 2	RJ-45 Male	Connector 1	RJ-45 Male