



C2G
9.8ft (3m) USB 2.0 A/B Cable - White
Part No. CG-13400



Just plug-and-play for keyboards, mice, modems, printers, and other USB peripherals. This cable provides a transfer rate up to 480 Mbps depending upon the peripheral's USB version, and easily attaches to any USB device. Foil and braid shielding reduces EMI/RFI interference and twisted pair construction helps reduce crosstalk thus ensuring high speed, error-free data transfer.

Features & Benefits

Easily connect a USB Hub, Keyboard or Mouse to a computer
PC and Mac® compatible

Supports high speed USB 2.0 and 1.1 devices
Available in lengths up to 5m

Specifications

General Info

Product Line	C2G	Color	White
UPC Number	757120134008	Country Of Origin	Vietnam
Application Sector	Residential, Commercial	Type	Cable

Dimensions

Cable Length	9.8 ft
--------------	--------

Additional Information

Prop 65 Warning Required	Yes	Prop 65 Warning Language	Cancer and Reproductive Harm
--------------------------	-----	--------------------------	------------------------------

Technical Information

Jacket Material	PVC (Polyvinyl Chloride)	Wire Gauge	24 AWG
Cable Type	USB	Amperage	100 mA

Data Transfer Rate	480 Mbps	Adapter Rear	USB-B Male
Adapter Front	USB-A Male		