



C2G
1.5ft (0.46m) 16 AWG 1-to-4 Power Cord Splitter (1 NEMA 5-15P to 4 NEMA 5-15R) (TAA Compliant)
Part No. CG-29803



Perfect for applications where a power strip or UPS is used to provide power to multiple AC transformers or AC/DC wall warts, this handy cable features a male 3-prong plug which splits to four female 3-prong shrouds. Simply plug the power cord's male prong into a standard outlet, and you're ready to power multiple electronic devices.

This cable is ideal for use in compact workplaces or home offices where there is limited space for electronic equipment. Plus this heavy duty 16 AWG cord features a fully molded design for maximum durability and long life. Compatible for power transformers, computers, monitors, scanners, printers, and other devices that use a 3-pin male to female shroud power connector.

Features & Benefits

Heavy duty 16 AWG cord

Fully molded cable design

Specifications

General Info

Product Line	C2G	Color	Black
UPC Number	757120298038	Country Of Origin	Taiwan, Province Of China
Warranty Type	Lifetime	Type	Power Cord, Splitter

Dimensions

Cable Length	1.5 ft
--------------	--------

Additional Information

Prop 65 Warning Required	Yes	Prop 65 Warning Language	Cancer and Reproductive Harm
--------------------------	-----	--------------------------	------------------------------

Technical Information

Wire Gauge	16 AWG	Jacket Rating	SJT Rated
Amperage	13 A	Voltage	125 V