



C2G
1.5ft (0.46m) 16 AWG 1-to-2 Power Cord Splitter (1 NEMA 5-15P to 2 NEMA 5-15R) (TAA Compliant)
Part No. CG-29802



Replace your overused or misplaced power cable, or just manage your power more efficiently. This handy cable features a male 3-prong plug which splits to two female 3-prong shrouds. Simply plug the power cord's male prong into a standard outlet, and you're ready to power multiple electronic devices.

Saves space by eliminating extra cords, and keeps your surge strip and UPS outlets from being blocked by bulky AC transformers. Ideal for use in compact workplaces or home offices where there is limited space for electronic equipment. Plus this heavy duty 16 AWG cord features a fully molded design for maximum durability and long life.

Compatible for power transformers, computers, monitors, scanners, printers, and other devices that use a 3-pin male to female shroud power connector.

Features & Benefits

Heavy duty 16 AWG cord

Fully molded cable design

Specifications

General Info

Product Line	C2G	UPC Number	757120298021
Country Of Origin	Taiwan, Province Of China	Application Sector	Commercial, Industrial
Type	Power Cord, Splitter		

Dimensions

Cable Length	1.5 ft
--------------	--------

Additional Information

Prop 65 Warning Required	Yes	Prop 65 Warning Language	Cancer and Reproductive Harm
--------------------------	-----	--------------------------	------------------------------

Technical Information

Wire Gauge	16 AWG	Jacket Rating	SJT-Rated
Amperage	10 A	Adapter Rear	NEMA 5-15 Female, NEMA 5-15 Female
Adapter Front	NEMA 5-15 Male	Voltage	125 V