



When you need just a little more distance, this cable will extend the reach of your existing USB A/B cable. Foil and braid shielding reduce EMI/RFI interference and twisted pair construction helps reduce crosstalk for a high speed, error-free data transfer. USB 2.0 compatible. PC and Mac compatible.

Please Note: Not for use beyond a total extended single length of 5 meters. For longer lengths or high-powered devices, please use #39978, 5m USB A Male to A Female Active Extension Cable.

Features & Benefits

Extends an existing USB cable or device

Support USB 2.0 speeds

Shielded to protect from interference

Specifications

General Info

Product Line	C2G	Color	Black
UPC Number	757120521075	Country Of Origin	Vietnam
Application Sector	Residential, Commercial	Warranty Type	Lifetime
Type	Cable		

Dimensions

Cable Length	6.6 ft
--------------	--------

Additional Information

Prop 65 Warning Required	Yes	Prop 65 Warning Language	Cancer and Reproductive Harm
--------------------------	-----	--------------------------	------------------------------

Technical Information

Jacket Material	PVC (Polyvinyl Chloride)	Wire Gauge	28 AWG
Cable Type	USB, Extension	Data Transfer Rate	480 Mbps
Adapter Rear	USB-A Female	Adapter Front	USB-A Male