



C2G
4ft (1.2m) Cat6a Snagless Shielded (STP) Ethernet Network Patch Cable - Black
Part No. CG-00709



This Snagless Shielded Cat6a patch cable is ideal for use with 10GBase-T ports and equipment, such as network adapters, hubs, switches, routers, DSL/cable modems and patch panels, and will protect a high speed 10 Gigabit network connection from noise and electromagnetic interference. For voice/data/video distribution, this cable will handle bandwidth-intensive applications and drastically reduces both impedance and structural return loss (SRL). Each patch cable is fully tested to meet ANSI/TIA 568 C.2 Cat6a component requirements.

Each of the individual pairs is bonded together to help maintain the twist-spacing throughout the line right up to the termination point. Constructed from high quality cable and plugs, this design minimizes Near-End Crosstalk (NEXT) levels. Available in a variety of colors to easily color-code a network installation. Individual length label on each cable for ease of use.

Features & Benefits

| | |
|---|--|
| Designed for network adapters, hubs, switches, routers, HDBaseT applications and more | Supports 10 Gigabit networks up to 328ft for fast data transmission and maximum performance |
| Meets the ANSI/TIA-568-C.2 Cat6a requirements for supporting a wide variety of applications | Constructed with shielded twisted pair (STP) wires, designed to protect a high speed network from noise and electromagnetic interference |
| Snagless connector design for high density environments and protecting the RJ-45 connector's lock | Available in a variety of colors to color-code a network |

Specifications

General Info

| | | | |
|---------------|---------------------------|--------------------|-------------------------------------|
| Product Line | C2G | Color | Black |
| UPC Number | 757120007098 | Country Of Origin | Vietnam |
| Features | PoE (Power Over Ethernet) | Application Sector | Commercial, Industrial, Residential |
| Warranty Type | Lifetime | Type | Cable |

Dimensions

| | | | |
|-------------------|--------|--------------|------|
| Product Length US | 4.0 FT | Cable Length | 4 ft |
|-------------------|--------|--------------|------|

Technical Information

| | | | |
|-----------------|--------------------------|------------|--------|
| Jacket Material | PVC (Polyvinyl Chloride) | Wire Gauge | 26 AWG |
|-----------------|--------------------------|------------|--------|

| | | | |
|----------------|--|---------------|----------------------|
| Cable Type | Booted, Ethernet Patch Cable, Shielded (STP), Snagless | Jacket Rating | Standard / Non-Rated |
| Cable Diameter | 6.2 mm | Adapter Rear | RJ-45 Male |
| Adapter Front | RJ-45 Male | | |