



# HP E24i G4 WUXGA No Stand Monitor (9VJ40A9)



## Overview

### Enhance your entire viewing experience

Work comfortably and stay focused with the optimized ergonomics and WUXGA resolution of the HP E24i G4 WUXGA Monitor with HP Eye Ease that is designed around you. Make life easy for IT with remote manageability.

### Total comfort begins with HP Eye Ease

Keep your eyes comfortable through the work day with HP Eye Ease, our first built-in, always-on blue light filter that presents your vivid content with zero impact on your color accuracy, no OSD required.

### Responsibly made

Energy efficiency is built into every ENERGY STAR® certified, EPEAT® 2020 registered[3], and low halogen[4] display. We go one step further with 100% recyclable packaging that's easily accepted by recycling facilities.

### Personalize your view

Never lose a moment of productivity with 4-way monitor adjustability that lets you find your sweet spot, a 3-sided micro-edge, flicker-free 24" diagonal screen that reveals more of your work, and WUXGA resolution for crisp visuals from any angle.

# Features

## Experience simple, convenient connectivity

Connect to your most frequently-used devices with VGA, HDMI, and DisplayPort™. Add up to four of your USB accessories right at the monitor with the integrated USB 3.2 hub.

## Find your comfort zone

Work comfortably with adjustable tilt, height, and swivel settings. Use pivot rotation to conveniently customize portrait or landscape views on multiple monitors.<sup>[2]</sup>

## Take your PC off the desk

Create an efficient, compact, solution when you mount your HP Desktop Mini PC directly on the column stand using the optional HP B300 PC Mounting Bracket.<sup>[5]</sup>

## Personalize and help protect your monitor

Customize your monitor and help deter its theft with easy, intuitive HP Display Center software that lets you tailor your settings, partition screens, and even dim the screen if your monitor is disconnected without approval—all through the host PC.<sup>[6]</sup>

## Complete the picture

Customize a total solution with options like the HP S101 Speaker Bar, which attaches easily to the lower bezel to add stereo audio on the monitor.<sup>[5]</sup>

## We have your back

Rest assured that this monitor has been vigorously tested for compatibility across HP PCs and workstations. It's also supported by our three-year standard limited warranty. Extend your protection to cover accidents, next-business day needs, and more with optional HP Care Pack services.<sup>[7]</sup>

---

<sup>[2]</sup> Additional monitors sold separately.

<sup>[3]</sup> Based on US EPEAT® registration according to IEEE 1680.1-2018 EPEAT®. Status varies by country. Visit [www.epeat.net](http://www.epeat.net) for more information.

<sup>[4]</sup> External power supplies, power cords, cables and peripherals are not Low Halogen. Service parts obtained after purchase may not be Low Halogen.

<sup>[5]</sup> Sold separately.

<sup>[6]</sup> Requires Windows 10 on host PC.

<sup>[7]</sup> HP Care Packs sold separately. Service levels and response times for HP Care Packs may vary depending on your geographic location. Service starts on date of hardware purchase. Restrictions and limitations apply. For details, visit [www.hp.com/go/cpc](http://www.hp.com/go/cpc). HP Services are governed by the applicable HP terms and conditions of service provided or indicated to Customer at the time of purchase. Customer may have additional statutory rights according to applicable local laws, and such rights are not in any way affected by the HP terms and conditions of service or the HP Limited Warranty provided with your HP Product.

## Specifications

<b>Display size (diagonal)</b>	24"
<b>Panel technology</b>	IPS
<b>Display size (diagonal)</b>	61 cm (24")
<b>Aspect ratio</b>	16:10
<b>Native resolution</b>	WUXGA (1920 x 1200) <sup>[1]</sup>
<b>Resolutions supported</b>	1024 x 768; 1280 x 1024; 1280 x 720; 1280 x 800; 1440 x 900; 1600 x 900; 1680 x 1050; 1920 x 1080; 1920 x 1200; 640 x 480; 720 x 400; 800 x 600
<b>Pixel pitch</b>	0.27 mm
<b>Brightness</b>	250 nits <sup>[1]</sup>
<b>Contrast ratio</b>	1000:1
<b>Response time (typical)</b>	5ms GtG (with overdrive) <sup>[1]</sup>
<b>Minimum dimensions (W x D x H)</b>	53.2 x 4.7 x 35.27 cm (Without stand.)
<b>Minimum dimensions (W x D x H)</b>	20.94 x 1.85 x 13.88 in (Without stand.)
<b>Dimensions With Stand (W x D x H)</b>	53.2 x 20.69 x 50.96 cm
<b>Weight</b>	6.06 kg (With stand.)
<b>Weight</b>	13.36 lb (With stand.)
<b>Display features</b>	Low blue light mode; Anti-glare
<b>Display Input Type</b>	1 VGA; 1 USB Type-B; 1 DisplayPort™ 1.2 (with HDCP support); 1 HDMI 1.4 (with HDCP support); 4 USB-A 3.2 Gen 1
<b>Onscreen controls</b>	Brightness; Exit; Information; Management; Power control; Input control; Menu control; Image; Color
<b>Display colors</b>	Up to 16.7 million colors supported (through FRC technology)
<b>Display scan frequency (horizontal)</b>	30-80 KHz
<b>Display scan frequency (vertical)</b>	50-60 Hz
<b>Camera</b>	No integrated camera
<b>Power</b>	Input voltage 100 to 240 VAC
<b>Power consumption</b>	53 W (maximum), 36 W (typical), 0.5 W (standby)
<b>Operating temperature range</b>	5 to 35°C
<b>Operating humidity range</b>	20 to 80% non-condensing

<b>Certifications and compliances</b>	BIS; BSMI; CB; CCC; CE; CECP; CEL; EAC; ENERGY STAR®; FCC; ISO 9241-307; KC/KCC; NOM; PSB; SEPA; TCO Certified; TCO Certified Edge; TUV LBL; TUV-S; VCCI; WEEE; ISC; California Energy Commission (CEC); WW application; ICE; TGM; TUV-GS
<b>Physical security</b>	Security lock-ready <sup>[2]</sup>
<b>Management Software</b>	HP Display Center; HP Display Manager
<b>UPC number</b>	(A2K) 195161154072; (A2N) 195161154089; (AB0) 195161154102; (AB1) 195161154119; (AB2) 195161154126; (AB4) 195161154133; (ABA) 195161154140; (ABB) 195161154157; (ABG) 195161154164; (ABJ) 4580511791919; (ABM) 195161154171; (ABT) 195161154188; (ABU) 195161154195; (ABV) 195161154201; (ABY) 195161154218; (AC4) 195161154225; (AC8) 195161154232; (ACJ) 195161154249; (ACQ) 195161154256; (AKL) 195161154263; (AR6) 195161154270; (UUF) 195161154287; (UUZ) 195161154294
<b>What's in the box</b>	Monitor; DisplayPort™ 1.2 cable; HDMI cable; USB cable; QSP; AC power cable; Doc-kit

## Additional specifications

<b>Backlight type</b>	Edge-lit
<b>Bezel</b>	3-sided micro-edge
<b>Color gamut</b>	99% sRGB
<b>Curvature</b>	Flat
<b>Detachable stand</b>	Yes
<b>Display area (imperial)</b>	20.41 x 12.76 in
<b>Display area (metric)</b>	51.84 x 32.4 cm
<b>Display contrast ratio (dynamic)</b>	5000000:1
<b>DisplayPort™</b>	1 DisplayPort™ 1.2
<b>Ethernet</b>	No
<b>Flicker-free</b>	Yes
<b>HDCP</b>	Yes, DisplayPort™ and HDMI
<b>HDMI</b>	1 HDMI 1.4
<b>Hardness</b>	3H
<b>Height adjustment range</b>	150 mm
<b>Horizontal viewing angle</b>	178°
<b>Integrated privacy filter</b>	No
<b>Low blue light</b>	Yes, HP Eye Ease (TÜV Low Blue Light Hardware Solution certified)
<b>Microphone</b>	No
<b>Non-Operating Humidity Range</b>	5 - 95%
<b>Operating temperature range</b>	41 to 95°F
<b>Package dimensions (W x D x H)</b>	60.5 x 42x 22.4 cm
<b>Package dimensions (W x D x H)</b>	23.82 x 16.54 x 8.82 in
<b>Package weight</b>	20.10 lb
<b>Package weight</b>	9.12 kg
<b>Panel bit depth</b>	8 bit (6 bit + 2 FRC)
<b>Pixels per inch (ppi)</b>	94 ppi
<b>Power supply type</b>	Internal
<b>Product dimensions with stand (W x D x H)</b>	20.94 x 8.15 x 20.06 in
<b>Recommended resolution</b>	WUXGA (1920 x 1200 @ 60 Hz)
<b>Resolution (maximum)</b>	WUXGA (1920 x 1200 @ 60 Hz)
<b>Screen treatment</b>	Anti-glare
<b>Speakers</b>	No

<b>Tilt</b>	-5 to +23°
<b>Touch-enabled</b>	Not touch-enabled
<b>UNSPSC code</b>	43211902
<b>USB Type-A</b>	4 SuperSpeed USB Type-A 5Gbps signaling rate
<b>Usb b (hub enablement)</b>	1 USB-B
<b>VESA mounting</b>	100 mm x 100 mm
<b>VGA</b>	1 VGA
<b>Vertical viewing angle</b>	178°
<b>pivot</b>	±90
<b>swivel</b>	±45°

---

*[1] All specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.*

*[2] Lock sold separately.*

---

## Accessories

### Rack Brackets/Bezels/ Panels/Rails/ Trays/Mounting

★ : Recommended

#### Mounting Kits

HP B300 PC Mounting Bracket	2DW53AA
HP Single Monitor Arm	BT861AA

### Security and Protection

#### PC Locks

HP Business PC Security Lock v3 Kit	3XJ17AA
-------------------------------------	---------

### Cabinets and Stands

#### Monitor Stands

HP Integrated Work Center for Desktop Mini and Thin Client	G1V61AA
--	---------

### Audio/Multimedia and Communication Devices

#### Speakers

HP S101 Speaker Bar	5JU40AA
---------------------	---------

---

## Disclaimer — Copyright

DisplayPort™ and the DisplayPort™ logo are trademarks owned by the Video Electronics Standards Association (VESA®) in the United States and other countries.

© Copyright 2022 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Nov 03, 2022 6:10 PM UTC+0000