

OVERVIEW



1. USB 3.2 Gen 1 (Always On)	7. Power connector
2. Headphone / microphone combo jack (3.5mm)	8. Kensington Security Slot
3. Ethernet (RJ-45)	9. Power light
4. USB-C 3.2 Gen 1 (data transfer / DP 1.2 only)	10. NOVO button hole
5. 2x USB 3.2 Gen 1	11. USB 3.2 Gen 1
6. HDMI 2.0	

PERFORMANCE

Processor

Processor Family

AMD Ryzen™ 5 / 7 Processor

Processor

Processor Name	Cores	Threads	Base Frequency	Max Frequency	Cache	Memory Support	Processor Graphics
AMD Ryzen 5 4600H	6	12	3.0GHz	4.0GHz	3MB L2 / 8MB L3	DDR4-3200	AMD Radeon™ Graphics
AMD Ryzen 7 4800H	8	16	2.9GHz	4.2GHz	4MB L2 / 8MB L3	DDR4-3200	AMD Radeon Graphics

Operating System

Operating System

- Windows® 10 Pro 64
- Windows 10 Home 64
- FreeDOS
- No operating system

Graphics

Graphics

Graphics	Type	Memory	Key Features
NVIDIA® GeForce® GTX 1660 Ti	Discrete	6GB GDDR6	VR ready, DirectX® 12
NVIDIA GeForce RTX™ 2060	Discrete	6GB GDDR6	VR ready, DirectX 12

Monitor Support

Monitor Support

Supports up to 3 independent displays via native display and 2 external monitors; supports external monitors via HDMI® (up to 4096x2160@60Hz) or USB-C (up to 3840x2160@60Hz)

Chipset

Chipset

AMD SoC (System on Chip) platform

Memory

Max Memory⁽¹⁾

Up to 16GB DDR4-3200 offering

Memory Slots

Two DDR4 SO-DIMM slots, dual-channel capable

Memory Type

DDR4-3200

Notes:

1. The max memory is based on the test results with current Lenovo® memory offerings. The system may support more memory as the technology develops.

Storage

Storage Support

- HDD/SSD mode: up to two drives, 1x 2.5" HDD + 1x M.2 SSD
 - 2.5" HDD up to 2TB
 - M.2 2242 SSD up to 512GB
 - M.2 2280 SSD up to 1TB
- Dual SSD mode: up to two drives, 2x M.2 SSD
 - M.2 2242 SSD up to 512GB

- M.2 2280 SSD up to 1TB

Storage Slot

- HDD/SSD mode: one 2.5" drive slot + one M.2 slot
 - One 2.5" drive slot, supports 2.5" SATA HDD
 - One M.2 2280 PCIe Gen 3x4 slot, supports M.2 2242/2280 SSD
- Dual SSD mode: two M.2 slots
 - Two M.2 2280 PCIe Gen 3x4 slots, support M.2 PCIe 2242/2280 SSD

Storage Type

Disk Type	Interface	RPM	Security
2.5" SATA HDD	SATA 6Gb/s	5.4K	-
2.5" SATA HDD	SATA 6Gb/s	7.2K	-
M.2 2242 SSD	PCIe NVMe, PCIe 3.0 x4	-	-
M.2 2280 SSD	PCIe NVMe, PCIe 3.0 x4	-	-

Removable Storage

Optical

None

Card Reader

No card reader

Multi-Media

Audio Chip

High Definition (HD) Audio, Realtek® ALC3287 codec

Speakers

Stereo speakers, 2W x2, Dolby® Atmos® for gaming, HARMAN-branded

Microphone

Dual array microphone

Camera

720p, with privacy shutter, fixed focus

Battery

Battery

- Integrated Li-Polymer 60Wh battery, supports Rapid Charge Pro (charge up to 50% in 30min)
- Integrated Li-Polymer 80Wh battery, supports Rapid Charge Pro (charge up to 50% in 30min)

Max Battery Life^[1]

- MobileMark® 2018: 4.2 hr (60Wh)
- MobileMark 2018: 5.7 hr (80Wh)

Notes:

1. All battery life claims are approximate maximum and based on results using the MobileMark 2014, MobileMark 2018, and/or JEITA 2.0 battery-life benchmark tests. Actual battery life will vary and depends on many factors such as product configuration and usage, software use, wireless functionality, power management settings, and screen brightness. The maximum capacity of the battery will decrease with time and use.

Power Adapter

Power Adapter

230W slim tip (3-pin) AC adapter

DESIGN

Display

Display^[1]

Size	Resolution	Touch	Type	Brightness	Surface	Aspect	Contrast	Color	Viewing	Key Features
------	------------	-------	------	------------	---------	--------	----------	-------	---------	--------------

						Ratio	Ratio	Gamut	Angle	
15.6"	FHD (1920x1080)	None	IPS	250 nits	Anti-glare	16:9	-	45% NTSC	-	Refresh rate 120Hz, DC dimmer
15.6"	FHD (1920x1080)	None	IPS	300 nits	Anti-glare	16:9	-	100% sRGB	-	Refresh rate 60Hz, DC dimmer
15.6"	FHD (1920x1080)	None	IPS	300 nits	Anti-glare	16:9	-	100% sRGB	-	Refresh rate 144Hz, DC dimmer, Dolby Vision™

Touchscreen

Non-touch

Notes:

- California Electronic Waste Recycling Fee
In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to <https://www.calrecycle.ca.gov/Electronics/Consumer>

Input Device

Keyboard

6-row, multimedia Fn keys, numeric keypad

Keyboard Backlight

- White LED backlight
- 4-Zone RGB LED backlight

Touchpad

Buttonless Mylar® surface multi-touch touchpad

Mechanical

Dimensions (WxDxH)

363.06 x 259.61 x 23.57-26.1 mm (14.3 x 10.22 x 0.93-1.03 inches)

Weight^[1]

2.46 kg (5.42 lbs)

Case Color

Phantom black

Surface Treatment

Painting

Case Material

PC + ABS (top), PC + ABS (bottom)

System Lighting

No system lighting

Notes:

- The system weight varies depending on configurations

CONNECTIVITY

Network

Onboard Ethernet

Gigabit Ethernet

WLAN + Bluetooth®

- 802.11ac 2x2 Wi-Fi® + Bluetooth 5.0, M.2 card
- Wi-Fi 6, 802.11ax 2x2 Wi-Fi + Bluetooth 5.0, M.2 card

Ports^[1]

Standard Ports^[2]

- 3x USB 3.2 Gen 1
- 1x USB 3.2 Gen 1 (Always On)
- 1x USB-C 3.2 Gen 1 (support data transfer and DisplayPort™ 1.2)
- 1x HDMI 2.0
- 1x Ethernet (RJ-45)
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Power connector

Notes:

1. The transfer speed of following ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.
USB 2.0: 480 Mbit/s;
USB 3.2 Gen 1 (SuperSpeed USB 5Gbps, formerly USB 3.0 / USB 3.1 Gen 1): 5 Gbit/s;
USB 3.2 Gen 2 (SuperSpeed USB 10Gbps, formerly USB 3.1 Gen 2): 10 Gbit/s;
USB 3.2 Gen 2x2 (SuperSpeed USB 20Gbps): 20 Gbit/s;
Thunderbolt™ 3: 40 Gbit/s;
FireWire 400: 400 Mbit/s;
FireWire 800: 800 Mbit/s
2. Depending on many factors, actual data transfer speed may be lower than theoretical speed

SECURITY & PRIVACY

Security

Security Chip

Firmware TPM 2.0 integrated in chipset

Physical Locks

Kensington® Security Slot

Fingerprint Reader

No fingerprint reader

BIOS Security

- Administrator password
- Power-on password
- Hard disk password

Other Security

Camera privacy shutter

SERVICE

Warranty

Base Warranty

- 1-year depot service
- 1-year depot with 2-year system board service
- 2-year (1-yr battery) depot service

ENVIRONMENTAL

Operating Environment

Temperature^[1]

- At altitudes up to 2438 m (8,000 ft)
 - Operating: 5°C to 35°C (41°F to 95°F)
 - Storage: 5°C to 43°C (41°F to 109°F)
- At altitudes above 2438 m (8,000 ft)
 - Maximum temperature when operating under the unpressurized condition: 31.3°C (88°F)

Humidity

- Operating: 8% to 95% at wet-bulb temperature 23°C (73°F)
- Storage: 5% to 95% at wet-bulb temperature 27°C (81°F)

Altitude

Maximum altitude (without pressurization): 3048 m (10,000 ft)

Notes:

1. When you charge the battery, its temperature must be no lower than 10°C (50°F)

ACCESSORIES

Bundled Accessories

Bundled Accessories

- Lenovo Legion™ M300 RGB Gaming Mouse (USB connector)
- None

CERTIFICATIONS

Green Certifications

Green Certifications

- ErP Lot 3
- RoHS compliant



AMD



AMD



AMD



AMD



AMD



AMD