

IM7200 Infrastructure Manager

With Smart OOB and Failover to Cellular



Features

- Smart OOB™ with embedded cellular
- Failover to Cellular™
- Flexible Connectivity – embedded cellular, PSTN, and redundant ethernet/fiber
- Additional models with 24 Port switch and 24 Port USB Console
- Simple cabling with software selectable Pin-outs
- Hyperscale, Automation ZTP, API, Lighthouse
- Powerful hardware with integrated 16 GB internal storage



Console Specifications		
Console Ports	IM72xx – 8 – 48 x RJ45 RS-232 Software Selectable Console Ports IM7216-24U – 16 x RJ45 RS-232 Software Selectable Console Ports and 24 USB Console Ports IM7216-24E – 16 x RJ45 RS-232 Software Selectable Console Ports and 24 Port Gigabit Switch	
Interface		
Ethernet Ports	2 x 10/100/1000 Ethernet/SFP Fiber port with 1500V AC Isolation and ESD Protection	
Console Port	1 x RJ45 RS-232 Console Port	
PSTN Modem	1 x Internal V.92 modem with RJ11 Socket	
Serial Ports	Software Selectable 50 to 230,400 bps	
USB	2 x USB 3.0 console ports	
Remote Access	Integrated 4G LTE Cellular Card, Integrated V.92 PSTN Dial-in, Dual Ethernet, aggregation & redundancy Automatic Network Failover, Easy browser UI IPv6	
Console Management	Built-in web terminal SSH direct to consoles Optional console keystroke logging	Alert on cable disconnects, text pattern match and more Inline power control Multiple concurrent sessions
Power Requirements		
Dual AC	Dual socket universal 100-240V AC	
Dual DC	+/- 36V to 72V DC	
Power Consumption	Less than 15W	
Power Monitoring	DDC (all models), DAC (models shipped after June 1, 2019)	
Physical Dimensions		
Dimensions and Weight	17 x 10 x 1.75 in – 10 lbs., 44 x 25.4 x 4.5 cm – 4.5 kg	
Form Factor	1 RU	
Memory & CPU		
CPU	1 GHz ARM SoC (Marvell 88F6283)	
Memory	256 MB DDR2 SDRAM 64 MB Embedded NOR Flash	
Internal Storage	16 GB Memory	
Environmental		
Operating Temperature	5°C to 50°C, 41°F to 122°F	
Storage Temperature	-30°C to +60°C, -22°F to +140°F	
Humidity	5% to 90%	
Environmental Monitoring	Serial EMD5000 to support physical, smoke, water leak and vibration sensors	
Security, Encryption & Authentication		
	SSH FIPS-140-2 compliant Open SSL Module Strong ciphers -AES encryption Cisco-compatible IPsec OpenVPN	AAA – TACACS+, RADIUS, Active Directory/OpenLDAP, Kerberos, with local fallback Two factor authentication via remote AAA Configurable stateful firewall Actively developed & support and security notifications-frequent firmware updates
Automation & Scalability		
	ZTP, Lighthouse RESTful API, programmable and extensible Auto-Response, SNMP, LLDP, NTP	
Cellular		
Modules	IM72xx-LR – Sierra Wireless MC7304 IM72xx-LMx Sierra Wireless MC7354 IM72xx-LMP – Sierra Wireless MC7430	
Cellular Certification	AT&T and Verizon Certified MIC-R and MIC-T Certified Japanese carriers PTCRB, NAPRD.03, GCF-CC, R&TTE, EN 301 511, A-Tick (GSM/UMTS) CDG TIA/EIA-690, CDG TIA/EIA-98-E (CDMA/EV-DO)	
Certifications		
Emissions	FCC Part 15 Subpart B (Class A) ICES-003 Issue 5 (2014) AS/NZS CISPR 22: 200410 (Class A)	EN 55032:2015 (Class A) EN 61000-3-2 Harmonics Current Emissions (2014) EN 61000-3-3 Voltage Fluctuation and Flicker (2013)
Immunity	EN 55024 ITE Immunity (2010) IEC 61000-4-2 (2008) IEC 61000-4-3 (2006) A1 (2007) A2 (2010) IEC 61000-4-4 (2012)	IEC 61000-4-5 (2014) IEC 61000-4-6 (2014) IEC 61000-4-8 (2010) IEC 61000-4-11 (2004)
Other Agency Approvals	IEC 60950-1:2005 (Second Edition) + Am 1:2009 + Am 2:2013, C-Tick FIPS 140-2 validated module Certificate #2473, CCC for IM7208-2-DAC, IM7216-2-DAC, IM7232-2-DAC, IM7248-2-DAC models	
MTBF	100,000 hours	
Warranty	4 Years hardware and support	



Available Models

	Model	Cellular		Model	Cellular
8 Port Dual AC Models	IM7208-2-DAC	No	32 Port Dual AC Models	IM7232-2-DAC	No
	IM7208-2-DAC-LMA	Multicarrier AT&T		IM7232-2-DAC-LMA	Multicarrier AT&T
	IM7208-2-DAC-LMCT	Multicarrier Telus Canada		IM7232-2-DAC-LMCT	Multicarrier Telus Canada
	IM7208-2-DAC-LMCB	Multicarrier Bell Canada		IM7232-2-DAC-LMCB	Multicarrier Bell Canada
	IM7208-2-DAC-LMCR	Multicarrier Rogers Canada		IM7232-2-DAC-LMCR	Multicarrier Rogers Canada
	IM7208-2-DAC-LMV	Multicarrier Verizon		IM7232-2-DAC-LMV	Multicarrier Verizon
	IM7208-2-DAC-LMP	Multicarrier APAC		IM7232-2-DAC-LMP	Multicarrier APAC
	IM7208-2-DAC-LR	Multicarrier Rest of World		IM7232-2-DAC-LR	Multicarrier Rest of World
8 Port Dual DC Models	IM7208-2-DDC	No	32 Port Dual DC Models	IM7232-2-DDC	No
	IM7208-2-DDC-LMA	Multicarrier AT&T		IM7232-2-DDC-LMA	Multicarrier AT&T
	IM7208-2-DDC-LMCT	Multicarrier Telus Canada		IM7232-2-DDC-LMCT	Multicarrier Telus Canada
	IM7208-2-DDC-LMCB	Multicarrier Bell Canada		IM7232-2-DDC-LMCB	Multicarrier Bell Canada
	IM7208-2-DDC-LMCR	Multicarrier Rogers Canada		IM7232-2-DDC-LMCR	Multicarrier Rogers Canada
	IM7208-2-DDC-LMV	Multicarrier Verizon		IM7232-2-DDC-LMV	Multicarrier Verizon
	IM7208-2-DDC-LMP	Multicarrier APAC		IM7232-2-DDC-LMP	Multicarrier APAC
	IM7208-2-DDC-LR	Multicarrier Rest of World		IM7232-2-DDC-LR	Multicarrier Rest of World
16 Port Dual AC Models	IM7216-2-DAC	No	48 Port Dual AC Models	IM7248-2-DAC	No
	IM7216-2-DAC-LMA	Multicarrier AT&T		IM7248-2-DAC-LMA	Multicarrier AT&T
	IM7216-2-DAC-LMCT	Multicarrier Telus Canada		IM7248-2-DAC-LMCT	Multicarrier Telus Canada
	IM7216-2-DAC-LMCB	Multicarrier Bell Canada		IM7248-2-DAC-LMCB	Multicarrier Bell Canada
	IM7216-2-DAC-LMCR	Multicarrier Rogers Canada		IM7248-2-DAC-LMCR	Multicarrier Rogers Canada
	IM7216-2-DAC-LMV	Multicarrier Verizon		IM7248-2-DAC-LMV	Multicarrier Verizon
	IM7216-2-DAC-LMP	Multicarrier APAC		IM7248-2-DAC-LMP	Multicarrier APAC
	IM7216-2-DAC-LR	Multicarrier Rest of World		IM7248-2-DAC-LR	Multicarrier Rest of World
16 Port Dual DC Models	IM7216-2-DDC	No	48 Port Dual DC Models	IM7248-2-DDC	No
	IM7216-2-DDC-LMA	Multicarrier AT&T		IM7248-2-DDC-LMA	Multicarrier AT&T
	IM7216-2-DDC-LMCT	Multicarrier Telus Canada		IM7248-2-DDC-LMCT	Multicarrier Telus Canada
	IM7216-2-DDC-LMCB	Multicarrier Bell Canada		IM7248-2-DDC-LMCB	Multicarrier Bell Canada
	IM7216-2-DDC-LMCR	Multicarrier Rogers Canada		IM7248-2-DDC-LMCR	Multicarrier Rogers Canada
	IM7216-2-DDC-LMV	Multicarrier Verizon		IM7248-2-DDC-LMV	Multicarrier Verizon
	IM7216-2-DDC-LMP	Multicarrier APAC		IM7248-2-DDC-LMP	Multicarrier APAC
	IM7216-2-DDC-LR	Multicarrier Rest of World		IM7248-2-DDC-LR	Multicarrier Rest of World
16 Port + 24 Port Gigabit Switch Dual AC Models	IM7216-2-24E-DAC	No	16 Port + 24 Port Console USB Dual AC Models	IM7216-2-24U-DAC	No
	IM7216-2-24E-DAC-LMA	Multicarrier AT&T		IM7216-2-24U-DAC-LMA	Multicarrier AT&T
	IM7216-2-24E-DAC-LMV	Multicarrier Verizon		IM7216-2-24U-DAC-LMV	Multicarrier Verizon
	IM7216-2-24E-DAC-LMP	Multicarrier APAC		IM7216-2-24U-DAC-LMP	Multicarrier APAC
	IM7216-2-24E-DAC-LR	Multicarrier Rest Of World		IM7216-2-24U-DAC-LR	Multicarrier Rest Of World
16 Port + 24 Port Gigabit Switch Dual DC Models	IM7216-2-24E-DDC	No			
	IM7216-2-24E-DDC-LMV	Multicarrier Verizon			

Available country codes: -US, -AU, -UK, -EU, -JP, -CN

- Append model number with destination country, e.g. "IM7216-2-DAC-US" for USA.
- -CN models are not available with cellular.

Package Checklist

- Infrastructure Manager IM72xx
- Rack Mount Kit – Two ears and screws (Part# 590001)
- 1 x Cisco Straight DB9F-RJ45 Adapter (Part# 319015)
- 1 x CAT5 Patch Cable 5' (Part# 440016)
- Quick Start Guide
- 2 x Country Specific A/C Power cords (DDC models do not come with power cords)

Cellular Enabled Models Also Include:

- 2 x Cellular antennas (Part# 569028)
- 1 x Cellular Antenna extender with magnetic Base (Part# 449041)

Optional Accessories

	Part Number	Description
Adapters	319014	Adapter - DB9F to RJ45 straight serial - DCE -For X2 Pinout
	319015	Adapter - DB9F to RJ45 crossover serial - DTE -For X2 Pinout
	319016	Adapter - DB9M to RJ45 straight serial - DCE - For X2 Pinout
	440016	Cable - Straight through CAT5 - 6' length
Environmental	EMD5000-02	Environmental Monitoring Device - X2 Pinout
	EMD5781-10	Door contact sensor - 10' Cable length
	EMD5782	Vibration sensor - 3' Cable length
	EMD5779-QA	Smoke detector/alarm (220V AC, IEC C-13)
	EMD5890-QA	Smoke detector/alarm (110V AC, NEMA 5-15)
Mounting	EMD5780	Water leak detector - 3' Cable length
	590001	Rack Mount Kit - Ears and Screws - CM7100 / IM4200 / IM7200

Warranty

Part Number	Description
Included	4 year Standard Warranty
OGEXTWAR5-IM72	Warranty IM7200 (Extends to 5th year warranty)
OGEXTWAR6-IM72	Warranty IM7200 (Extends to 6th year warranty)