



The Swing-Out Wall-Mount Reinforced SWMR Series wall-mount cabinets provide a convenient and easy-to-use solution for edge, IoT, PoE and small network applications. The small form factor cabinets are 28 in deep for medium to large network equipment. The cabinets are made of rugged welded steel and feature locking doors. The SWMR series feature heavy duty latch and hinges to accommodate heavier weight loads.

Features & Benefits

Cable knockouts at top and bottom of fixed rear pan	UL2416 load rated
PCI Compliant	Reversible hinged solid front locking door
Vented sides with mounting locations for optional cooling fans	Reversible rails for network or server configurability
12-24 threaded and square punched mounting holes	2 reversible mounting rails
2 front door lock keys	8 cable management rings
Ruggedized hinges and latches	Multiple Heights available

Specifications

General Info

Product Line	Ortronics	Color	Black
Finish	Powder Coat	UPC Number	662875032410
Country Of Origin	Mexico	Product Series	Swing-Out Wall Mount Series
Features	Plexiglass Door	Included	Mounting Hardware
Number of Knockouts	3	Application Sector	Commercial
Standard	UL2416	Warranty Type	5-Year
Type	Cabinet		

Dimensions

Product Width US	26.0 in	Product Depth US	26.0 in
Product Height US	24.88 in	Rack Depth	26 in

Technical Information

Rack Units	12	Load Capacity	225 lb
Cable Entry	Back, Top	Frame	Adjustable
Mounting Type	Bolt	Mounting	Wall
