


OVERVIEW



1. Card reader	6. HDMI 2.1 TMDS
2. USB 3.2 Gen 1	7. USB 3.2 Gen 1 (Always On)
3. Ethernet (RJ-45)	8. Headphone / microphone combo jack (3.5mm)
4. Kensington Nano Security Slot	9. NOVO button hole
5. 2x USB-C 3.2 Gen 2	

PERFORMANCE

Processor

Processor Family

AMD Ryzen™ 3 / 5 / 7 Processor

Processor**

Processor Name	Cores	Threads	Base Frequency	Max Frequency	Cache	Memory Support	Processor Graphics
AMD Ryzen 3 5425U	4	8	2.7GHz	4.1GHz	2MB L2 / 8MB L3	DDR4-3200	AMD Radeon™ Graphics
AMD Ryzen 5 5625U	6	12	2.3GHz	4.3GHz	3MB L2 / 16MB L3	DDR4-3200	AMD Radeon Graphics
AMD Ryzen 7 5825U	8	16	2.0GHz	4.5GHz	4MB L2 / 16MB L3	DDR4-3200	AMD Radeon Graphics

Operating System

Operating System**

- Windows® 11 Pro 64
- Windows 11 Home 64
- Windows 11 DG Windows 10 Pro 64
- No operating system

Graphics

Graphics

Graphics	Type	Memory	TGP	Key Features
AMD Radeon Graphics	Integrated	Shared	Shares CPU TDP	DirectX® 12

Monitor Support

Monitor Support

Supports up to 4 independent displays (native display and 3 external monitors via HDMI® and USB-C)

- HDMI supports up to 3840x2160@60Hz
- USB-C supports up to 3840x2160@60Hz

Chipset

Chipset

AMD SoC (System on Chip) platform

Memory

Max Memory^[1]

Up to 40GB (8GB soldered + 32GB SO-DIMM) DDR4-3200

Memory Slots

One memory soldered to systemboard, one DDR4 SO-DIMM slot, dual-channel capable

Memory Type

DDR4-3200

Notes:

1. The max memory is based on the test results with current Lenovo® memory offerings. The system may support more memory as the technology develops.

Storage

Storage Support^[1]

Up to two drives, 2x M.2 SSD

- M.2 2242 SSD up to 1TB
- M.2 2280 SSD up to 1TB

Storage Slot

- Two M.2 slots
- One M.2 2242 PCIe® Gen 3x4 slot, supports M.2 2242 SSD
 - One M.2 2280 PCIe Gen 3x4 slot, supports M.2 2280 SSD

Storage Type**[2]

Disk Type	Interface	Offering
M.2 2242 SSD	PCIe NVMe®, PCIe 3.0 x4	256GB / 512GB
M.2 2242 SSD	PCIe NVMe, PCIe 4.0 x4	256GB / 512GB / 1TB
M.2 2280 SSD	PCIe NVMe, PCIe 4.0 x4	512GB / 1TB

- Notes:
1. The storage capacity supported is based on the test results with current Lenovo storage offerings. The system may support larger storage as the technology develops.
 2. The SSD with PCI 4.0x4 is downgraded to closer to PCIe 3.0x4 due to AMD platform limitation.

Removable Storage

Optical

None

Card Reader

4-in-1 card reader (SD, SDHC, SDXC, MMC)

Multi-Media

Audio Chip

High Definition (HD) Audio, Realtek® ALC3287 codec

Speakers

Stereo speakers, 2W x2, Dolby® Audio™

Microphone

Dual array microphone with AI-based noise cancellation, switchable audio modes

Camera**

- HD 720p, with privacy shutter, fixed focus
- 1080p, with privacy shutter, fixed focus

Battery

Battery**

- Integrated Li-Polymer 45Wh battery, supports Rapid Charge Pro (charge up to 50% in 30min)
- Integrated Li-Polymer 60Wh battery, supports Rapid Charge (charge up to 80% in 1hr)

Max Battery Life[1]

- Model with 45Wh battery:
MobileMark® 2018: 6 hr
Local video (1080p) playback@150nits: 8 hr
- Model with 60Wh battery:
MobileMark 2018: 8 hr
Local video (1080p) playback@150nits: 10 hr

- Notes:
1. All battery life claims are approximate maximum and based on results using the MobileMark 2014, MobileMark 2018, JEITA 2.0, continuous 1080p video playback (with 150nits brightness and default volume level) or Google Power Load Test (PLT) battery-life benchmark tests. Actual battery life will vary and depends on many factors such as product configuration and usage, software use, wireless functionality, power management settings, and screen brightness. The maximum capacity of the battery will decrease with time and use.

Power Adapter

Power Adapter**[1]

- 65W USB-C slim (2-pin, wall-mount) AC adapter, supports PD 3.0, 100-240V, 50-60Hz
- 65W USB-C (3-pin) AC adapter, supports PD 3.0, 100-240V, 50-60Hz

Notes:

1. AC adapter offerings depend on the country.

DESIGN

Display

Display**[1]

Size	Resolution	Touch	Type	Brightness	Surface	Aspect Ratio	Contrast Ratio	Color Gamut	Viewing Angle
14.0"	FHD (1920x1080)	None	TN	250 nits	Anti-glare	16:9	500:1	45% NTSC	90°
14.0"	FHD (1920x1080)	None	IPS	300 nits	Anti-glare	16:9	700:1	45% NTSC	170°
14.0"	FHD (1920x1080)	None	IPS	300 nits	Anti-glare	16:9	1200:1	100% sRGB	170°

Touchscreen

Non-touch

Notes:

1. California Electronic Waste Recycling Fee
In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product.
For more information, go to <https://www.calrecycle.ca.gov/Electronics/Consumer>

Input Device

Keyboard

6-row, spill-resistant, multimedia Fn keys

Keyboard Backlight

- LED backlight
- No support

Touchpad

Buttonless Mylar® surface multi-touch touchpad, supports Precision TouchPad (PTP), 70 x 105 mm (2.76 x 4.13 inches)

Mechanical[1]

Dimensions (WxDxH)

323 x 218 x 17.9 mm (12.72 x 8.58 x 0.7 inches)

Weight

Starting at 1.4 kg (3.09 lbs)

Case Color

Mineral grey, dual-tone design

Surface Treatment

Anodizing sandblasting

Case Material

Aluminium (top), aluminium (bottom)

Notes:

1. The system dimensions and weight vary depending on configurations.

CONNECTIVITY

Network

Onboard Ethernet

Gigabit Ethernet, 1x RJ-45, supports Wake-on-LAN

WLAN + Bluetooth®**[1]

- 802.11ac 2x2 Wi-Fi® + Bluetooth 5.0, M.2 card
- Wi-Fi 6, 802.11ax 2x2 Wi-Fi + Bluetooth 5.2, M.2 card

Notes:

1. Wi-Fi 6 and Wi-Fi 6E full features might be limited by country-level restrictions.
6GHz Wi-Fi 6E operation is dependent on the support of the operating system, routers/APs/Gateways that support Wi-Fi 6E, and the regional regulatory certifications & spectrum allocation.
Wi-Fi 6E is only enabled on Windows 11 and operates as Wi-Fi 6 with Windows 10.

Ports^[1]**Standard Ports**

- 1x USB 3.2 Gen 1
- 1x USB 3.2 Gen 1 (Always On)
- 2x USB-C 3.2 Gen 2 (support data transfer, Power Delivery 3.0, and DisplayPort™ 1.4)
- 1x HDMI 2.1 TMDS
- 1x Card reader
- 1x Ethernet (RJ-45)
- 1x Headphone / microphone combo jack (3.5mm)

Notes:

1. The transfer speed of following ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.
USB 2.0: 480 Mbit/s;
USB 3.2 Gen 1 (SuperSpeed USB 5Gbps, formerly USB 3.0 / USB 3.1 Gen 1): 5 Gbit/s;
USB 3.2 Gen 2 (SuperSpeed USB 10Gbps, formerly USB 3.1 Gen 2): 10 Gbit/s;
USB 3.2 Gen 2x2 (SuperSpeed USB 20Gbps): 20 Gbit/s;
Thunderbolt™ 3/4: 40 Gbit/s;
FireWire 400: 400 Mbit/s;
FireWire 800: 800 Mbit/s

Docking**Docking**

Various docking solutions supported via or USB-C.

For more compatible docking solutions, please visit [Docking for ThinkBook 14 G4 ABA](#)

SECURITY & PRIVACY**Security****Security Chip**

Firmware TPM 2.0 integrated in chipset

Physical Locks

Kensington® Nano Security Slot, 2.5 x 6 mm

Fingerprint Reader

Touch style fingerprint reader on smart power button

BIOS Security

- Power-on password
- Supervisor password
- Hard disk password

Other Security

Camera privacy shutter

SERVICE**Warranty****Base Warranty**^[1]**

- 1-year depot service
- 2-year (1-yr battery) depot service

Notes:

1. More information of warranty policy, please access <https://pcsupport.lenovo.com/warranty>

ENVIRONMENTAL

Operating Environment

Temperature^[1]

- At altitudes up to 2438 m (8,000 ft)
 - Operating: 5°C to 35°C (41°F to 95°F)
 - Storage: 5°C to 43°C (41°F to 109°F)
- At altitudes above 2438 m (8,000 ft)
 - Maximum temperature when operating under the unpressurized condition: 31.3°C (88°F)

Humidity

- Operating: 8% to 95% at wet-bulb temperature 23°C (73°F)
- Storage: 5% to 95% at wet-bulb temperature 27°C (81°F)

Altitude

Maximum altitude (without pressurization): 3048 m (10,000 ft)

Notes:

1. When you charge the battery, its temperature must be no lower than 10°C (50°F).

CERTIFICATIONS

Green Certifications

Green Certifications

- EPEAT™ Gold
- ENERGY STAR® 8.0
- ErP Lot 6
- RoHS compliant

Other Certifications

Mil-Spec Test

MIL-STD-810H military test passed

Other Certifications^[1]

TÜV Rheinland® Low Blue Light (Software Solution)

Notes:

1. TÜV Rheinland Low Blue Light is Not applicable for TN display.


- Feature with ** means that only one offering listed under the feature is configured on selected models.
- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION "AS IS," WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.
- The specifications on this page may not be available in all regions, and may be changed or updated without notice.



AMD



AMD



AMD



AMD



AMD



AMD