

Triple display support and fanless design makes it quieter in every scenario.

Triple displays


Support for triple displays in stunning 4K UHD resolution lets you extend your workspace across multiple monitors for more efficient and comfortable productivity experiences.

Fanless design

Fanless chassis makes PN41 even more reliable and durable in industrial applications, and quieter in every scenario. With SSD Heatsink design, PN41 fanless also supports M.2 SSD, and the average temperature of SSD is only 50°C.

Power Delivery Input

With support for USB Power Delivery, ASUS Mini PC PN41 can charge a connected phone or accessory and receive power from a supported display or other device, eliminating the need for a separate power adapter for a cleaner workspace uncluttered with cables.



Accessories list:



Model		PN41	
OS		Windows®11 64Bit, Windows®11 Pro 64Bit, Windows®10 Pro 64Bit or W/O OS	
CPU		Intel® Pentium® Silver N6000, Intel® Celeron® N5100, N4500	
Chipset		Integrated	
Graphics		Integrated - Intel® Gen11 Graphics	
Memory		Memory support 2 x SO-DIMM DDR4 2933 MHz (4GB, 8GB or 16GB)	
Storage		Storage support 1 x 2.5" SATA HDD, 1 x M.2 PCIe SSD or eMMC onboard (32G, 64G, 128G, 256G, 512G or 1TB)	
Wireless Network		Intel® 9462 802.11ac + BT V5.1, 1*1 Intel® 9560 802.11ac + BT V5.1, 2*2 Intel® Wi-Fi 6 AX201 (Gig+) + BT V5.2, 2*2 <small>*Bluetooth version support may vary from OS. Bluetooth v5.2 function will be ready in Windows 11 or later.</small>	
LAN		Intel® LAN, 10/100/1000/2500 Mbps Onboard: Realtek® RTL8125B(G)-CG Configurable port: Intel I211AT Supports Wake on LAN / PXE / Auto Power on / RTC Wake	
Interface	Front I/O	1 x USB 3.2 Gen2 Type-C (Support Battery Charging 1.2) 1 x USB 3.2 Gen1 1 x Audio Jack (Line in/ Mic in/ Headphone out) 1 x Dual-Microphone Array (optional) 1 x IR receiver (optional) 1 x 3 in 1 Card reader (optional)	
	Side I/O	1 x Kensington Lock	
	Rear I/O	1 x USB 3.2 Gen1 Type-C (Support Display Port 1.4, PD input) 2 x USB 3.2 Gen1 1 x HDMI 2.0 Port 1 x Configurable Port (options: Display Port 1.4/COM/ VGA/ LAN) 1 x RJ45 LAN 1 x DC-in <small>* Supports up to 3 displays via the USB 3.2 Gen 1 Type-C ports, configurable port(DP/VGA), and on-board HDMI port.</small>	
TPM		fTPM 2.0 or TPM 2.0 chip (Optional)	
BIOS Function		64 Mb Flash ROM, UEFI AMI BIOS, PnP, DMI2.0, WfM2.0, SM BIOS 2.8, ACPI 5.0, Multi-language BIOS, ASUS EZ Flash 3, ASUS CrashFree BIOS 3, My Favorites, Quick Note and ASUS DRAM SPD (Serial Presence Detect) memory information	
Software		ASUS Business manager, ASUS Product registration program, Asus Control Center test, Watchdog timer	
Power Supply		19Vdc, 3.42A or 19.5Vdc, 3.33A 65.0W Power Adapter (80cm)	
Physical	Dimension	115 x 115 x 49 mm (0.62L)	
	Weight	0.7 kg (Including 2.5" HDD)	
Max Resolution	HDMI	4096x2160 @ 60 Hz	
	DP	3840x2160 @ 60 Hz	
	VGA	1920x1200 @ 60 Hz	
Temperature	Operating	0°C~50°C	
	Storage	-40°C~85°C	
Humidity		0%~95% Relative Humidity	
Acoustic	Idle mode	<25 dBA	N/A
	Full loading	<35 dBA <small>* Test results will vary slightly depending on the HDD/SSD SKU selected by customer</small>	
Certificates		BSMI / CB / CE / FCC / UL / CCC / Energy Star / C-Tick / WiFi / RF / VCCI	