

OVERVIEW



1. Headphone / microphone combo jack (3.5mm)	5. Ethernet (RJ-45)
2. USB 3.2 Gen 1	6. HDMI 2.0
3. USB 3.2 Gen 1	7. USB-C 3.2 Gen 1 (data transfer only)
4. Power connector	

PERFORMANCE

Processor

Processor Family

11th Generation Intel® Core™ i5 / i7 Processor

Processor**

Processor Name	Cores	Threads	Base Frequency	Max Frequency	Cache	Memory Support	Processor Graphics
Core i5-11300H	4	8	3.1GHz	4.4GHz	8MB	DDR4-3200	Intel Iris® Xe Graphics
Core i5-11320H	4	8	3.2GHz	4.5GHz	8MB	DDR4-3200	Intel Iris Xe Graphics
Core i7-11370H	4	8	3.3GHz	4.8GHz	12MB	DDR4-3200	Intel Iris Xe Graphics
Core i7-11390H	4	8	3.4GHz	5.0GHz	12MB	DDR4-3200	Intel Iris Xe Graphics

Operating System

Operating System**

- Windows® 11 Pro 64
- Windows 11 Home 64
- Windows 10 Pro 64
- Windows 10 Home 64
- No operating system

Graphics

Graphics**

Graphics	Type	Memory	Boost Clock	TGP	Key Features
NVIDIA® GeForce® GTX 1650	Discrete	4GB GDDR6	-	-	DirectX® 12
NVIDIA GeForce RTX™ 3050 Laptop GPU	Discrete	4GB GDDR6	1500 MHz / 1740 MHz	90W	Resizable BAR, Dynamic Boost 2.0, DirectX 12
NVIDIA GeForce RTX 3050 Ti Laptop GPU	Discrete	4GB GDDR6	1485 MHz / 1695 MHz	90W	Resizable BAR, Dynamic Boost 2.0, DirectX 12

Monitor Support

Monitor Support

Supports up to 2 independent displays (native display and 1 external monitor via HDMI®)

- HDMI supports up to 3840x2162@60Hz

Chipset

Chipset

Intel SoC (System on Chip) platform

Memory

Max Memory^[1]

Up to 16GB DDR4-3200 offering

Memory Slots

Two DDR4 SO-DIMM slots, dual-channel capable

Memory Type

DDR4-3200

Notes:

1. The max memory is based on the test results with current Lenovo® memory offerings. The system may support more memory as the technology develops.

Storage

Storage Support^[1]

IdeaPad Gaming 3 15IHU6

Up to two drives, 1x 2.5" HDD + 1x M.2 2242 SSD or 1x M.2 2242/2280 SSD + 1x M.2 2242 SSD

- 2.5" HDD up to 1TB
- M.2 2242 SSD up to 512GB
- M.2 2280 SSD up to 1TB

Storage Slot^[2]

One 2.5" drive slot + two M.2 slots

- One 2.5" drive slot, supports 2.5" HDD
- One M.2 2242 PCIe® Gen 3x4 slot, supports M.2 2242 SSD
- One M.2 2280 PCIe Gen 3x2 slot, supports M.2 2242/2280 SSD

2.5" drive slot and M.2 2280 slot are used exclusively

Storage Type^{***}

Disk Type	Interface	RPM	Offering	Security
2.5" SATA HDD	SATA 6Gb/s	5.4K	-	-
M.2 2242 SSD	PCIe NVMe®, PCIe 3.0 x4	-	-	-
M.2 2280 SSD	PCIe NVMe, PCIe 3.0 x4	-	-	-

Notes:

1. The storage capacity supported is based on the test results with current Lenovo storage offerings. The system may support larger storage as the technology develops.
2. Installed M.2 2280 SSD is PCIe 3x4 but run at PCIe 3x2 due to M.2 SSD adapter limitation

Removable Storage

Optical

None

Card Reader

No card reader

Multi-Media

Audio Chip

High Definition (HD) Audio, Realtek® ALC3287 codec

Speakers

Stereo speakers, 2W x2, Nahimic Audio

Microphone

Dual array microphone

Camera

HD 720p, with camera shutter, fixed focus

Battery

Battery

Integrated Li-Polymer 45Wh battery, supports Rapid Charge Pro (charge up to 50% in 30min)

Max Battery Life^[1]

MobileMark® 2014: 8 hr

Notes:

1. All battery life claims are approximate maximum and based on results using the MobileMark 2014, MobileMark 2018, JEITA 2.0, continuous 1080p video playback (with 150nits brightness and default volume level) or Google Power Load Test (PLT) battery-life benchmark tests. Actual battery life will vary and depends on many factors such as product configuration and usage, software use, wireless functionality, power management settings, and screen brightness. The maximum capacity of the battery will decrease with time and use.

Power Adapter

Power Adapter^{**}

- 135W slim tip (3-pin) AC adapter, 100-240V, 50-60Hz
- 170W slim tip (3-pin) AC adapter, 100-240V, 50-60Hz

DESIGN

Display

Display**^[1]

Size	Resolution	Touch	Type	Brightness	Surface	Aspect Ratio	Contrast Ratio	Color Gamut	Viewing Angle	Key Features
15.6"	FHD (1920x1080)	None	IPS	250 nits	Anti-glare	16:9	800:1	45% NTSC	170°	Refresh rate 60Hz, DC dimmer
15.6"	FHD (1920x1080)	None	IPS	250 nits	Anti-glare	16:9	800:1	45% NTSC	170°	Refresh rate 120Hz, DC dimmer
15.6"	FHD (1920x1080)	None	IPS	300 nits	Anti-glare	16:9	1000:1	100% sRGB	170°	Refresh rate 165Hz, DC dimmer

Touchscreen

Non-touch

Notes:

1. California Electronic Waste Recycling Fee

In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to <https://www.calrecycle.ca.gov/Electronics/Consumer>

Input Device

Keyboard

6-row, multimedia Fn keys, numeric keypad

Keyboard Backlight**

- White backlight
- 4-Zone RGB backlight

Touchpad

Buttonless Mylar® surface multi-touch touchpad, 70 x 120 mm (2.76 x 4.72 inches)

Mechanical^[1]

Dimensions (WxDxH)

359.6 x 251.9 x 24.2 mm (14.16 x 9.92 x 0.95 inches)

Packaging Dimensions (WxDxH)

535 x 324 x 104 mm (21.06 x 12.76 x 4.09 inches)

Weight

2.25 kg (4.96 lbs)

Packaging Weight

3.44 kg (7.58 lbs)

Case Color

Shadow black

Surface Treatment

IMR (in-mold decoration by roller)

Case Material

PC + ABS (top), PC + ABS (bottom)

Notes:

1. The system dimensions and weight vary depending on configurations.

CONNECTIVITY

Network

Onboard Ethernet

Gigabit Ethernet

WLAN + Bluetooth®

Wi-Fi® 6, 802.11ax 2x2 Wi-Fi + Bluetooth 5.0, M.2 card

Ports^[1]

Standard Ports

- 2x USB 3.2 Gen 1
- 1x USB-C 3.2 Gen 1 (support data transfer only)
- 1x HDMI 2.0
- 1x Ethernet (RJ-45)
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Power connector

Notes:

1. The transfer speed of following ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.
USB 2.0: 480 Mbit/s;
USB 3.2 Gen 1 (SuperSpeed USB 5Gbps, formerly USB 3.0 / USB 3.1 Gen 1): 5 Gbit/s;
USB 3.2 Gen 2 (SuperSpeed USB 10Gbps, formerly USB 3.1 Gen 2): 10 Gbit/s;
USB 3.2 Gen 2x2 (SuperSpeed USB 20Gbps): 20 Gbit/s;
Thunderbolt™ 3/4: 40 Gbit/s;
FireWire 400: 400 Mbit/s;
FireWire 800: 800 Mbit/s

SECURITY & PRIVACY

Security

Security Chip

Firmware TPM 2.0 integrated in chipset

Fingerprint Reader

No fingerprint reader

BIOS Security

- Power-on password
- Supervisor password
- Hard disk password

Other Security

Camera privacy shutter

SERVICE

Warranty

Base Warranty**^[1]

- 1-year depot service
- 1-year depot with 2-year system board service
- 2-year (1-yr battery) depot service
- 3-year (1-yr battery) depot service

Notes:

1. More information of warranty policy, please access <https://pcsupport.lenovo.com/warranty>

ENVIRONMENTAL

Operating Environment

Temperature^[1]

- At altitudes up to 2438 m (8,000 ft)
 - Operating: 5°C to 35°C (41°F to 95°F)
 - Storage: 5°C to 43°C (41°F to 109°F)
- At altitudes above 2438 m (8,000 ft)
 - Maximum temperature when operating under the unpressurized condition: 31.3°C (88°F)

Humidity

- Operating: 8% to 95% at wet-bulb temperature 23°C (73°F)
- Storage: 5% to 95% at wet-bulb temperature 27°C (81°F)

Altitude

Maximum altitude (without pressurization): 3048 m (10,000 ft)

Notes:

1. When you charge the battery, its temperature must be no lower than 10°C (50°F).

ACCESSORIES

Bundled Accessories

Bundled Accessories

- Lenovo Gaming M100 RGB Mouse (USB connector)
- None

CERTIFICATIONS

Green Certifications

Green Certifications

- ErP Lot 3
- RoHS compliant

- Feature with ** means that only one offering listed under the feature is configured on selected models.
- Feature with *** means that one or more offerings listed under the feature could be configured on selected models.
- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION “AS IS,” WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.
- The specifications on this page may not be available in all regions, and may be changed or updated without notice.



intel



intel



intel



intel



intel



intel