

You are browsing the product catalog for

Pakistan



MOBILE PRINTERS

RP4f

The RP4F mobile thermal printers are built for the most rugged environments, offering exceptional media and battery capacity, quiet operation, and excellent value to help operations increase efficiency and minimize downtime.

Overview



Feedback

Print Anywhere, Anytime

The RPF portable printer boosts productivity by allowing workers to print labels on-site for immediate application. This capability minimizes errors and ensures labels are applied precisely where needed.

Reliable Performance

With a powerful CPU and smart power management, the RPF printer delivers smooth, uninterrupted operation. This functionality reduces media reloading and battery swaps, minimizing downtime and letting workers focus on their tasks.

Versatile Media Handling

The RPF Series prints labels and receipts from 25.4 mm (1 in) to 104.1 mm (4.1 in) wide, accommodating various media types including heavy stock for hang tags and specialty labels.

Advanced Connectivity Options

Equipped with 802.11 a/b/g/n/ac Wi-Fi, the RPF printer offers superior range and fast data communication within your WLAN. It also features Bluetooth 5.0 LE, perfect for use with mobile devices or outdoor settings.

Secure and Manageable

Built on Honeywell's robust software platform, the RPF provides integrated device management and strong security, ensuring your printers evolve alongside your business needs.

Specifications

FEATURES

Compatible Software

- BarTender
- Nicelabel
- Operational Intelligence
- SOTI
- Teklynx Labelview

Compatible Drivers

- CUPS Driver for Linux
- Certified Device Types for SAP
- InterDriver Windows

DIMENSIONS

Overall Dimensions

- H x W x D: 187 mm x 164 mm x 77 mm (7.36 in x 6.46 in x 3.0 in)

SOFTWARE & FIRMWARE

2D Barcodes

- All major 2D barcodes

Linear Barcodes

- All major 1D barcodes

Downloadable Font Type

- Bitmap Font
- OpenType Font (TrueType based)
- TrueType Font

Printer Command Language

- C# Smart Printing
- CPCL
- DPL
- Direct Protocol (DP)
- EZ-Print
- Fingerprint (FP)
- Intermec Printer Language (IPL)
- PDF
- XML-enabled for SAP All and Oracle WMS
- ZSim2 (ZPL-II)

Image File Format

- BMP
- GIF
- PCX
- PNG

Feedback

PRINTING SPECIFICATIONS

Resolutions

- 203 dpi

Print Speeds

- 25-125 mm/s (1-5 ips)

Print Method

- Direct Thermal

MEDIA

Printer Media Type

- Label
- Lined
- Linerless
- Receipt
- Tag

Maximum Media Roll Diameter

- 58 mm (2.25 in)

HARDWARE

Printer Connection Interface

- USB 2.0

ELECTRICAL

Battery Capacity Options

- 4900 mAh

ENVIRONMENTAL

Operating Humidity

- 20 - 80 % non-condensing

Storage Humidity

- 20 - 80 % non-condensing

STANDARDS & APPROVALS

Protection Ratings

- IP54

Drop Specifications

- 2 m (6.6 ft)

Tumble Specifications

- 1,000 cycles at 0.5 m (1.6 ft)

NETWORK

Bluetooth Specifications

- Bluetooth 5.0 + LE dual radio mode

Feedback

OTHERS

Features

- High power efficiency
- Rugged and reliable
- Smart printing

Application

- Healthcare
- Retail
- T&L

Weight range

- 1.02 kg (2.24 lb) with battery, no media keg

Wireless Communication

- IEEE 802.11 a/b/g/n/ac
- NFC for pairing
- OPEN, WEP, WPA/WPA2/WPA3 (Personal and Enterprise)

Storage Temperature

- -30°C to 65°C (-22°F to 149°F)

Operating Temperature

- -20°C to 55°C (-4°F to 131°F)

Warranty Duration

- Two years factory warranty

Print Width

- 4 inch

Print Volume

- Up to 2,000

Print Technology

- Direct Thermal

Print Resolution

- 203 dpi

Platform

- Honeywell Printer Edge

Industry

- Aerospace
- Logistics & Warehouses
- Manufacturing


Font Engine

- Language support
- Monotype Font Engine
- WTLE for global

Connectivity

- Bluetooth
- Wi-Fi

•Retail

 Please sign in to view part numbers available for purchase based on your account [Sign In](#)

Showing 1 to 10 of 10 parts


<input type="text" value="Search"/>		
PART NUMBER	DESCRIPTION	ORDER ONLINE
RP4F0000B12	RP4, BT5, BATT	SIGN IN
RP4F0000D12	RP4, BT5+WIFI5 NA, BATT	SIGN IN
RP4F0000D22	RP4, BT5+Wifi5 ROW, BATT	SIGN IN
RP4F0001B12	RP4, BT5, LNRLSS, BATT	SIGN IN
RP4F0001D12	RP4, BT5+WIFI5 NA, LNRLSS, BATT	SIGN IN
RP4F0001D22	RP4, BT5+WIFI5 ROW, LNRLSS, BATT	SIGN IN
RP4F00N0B12	RP4, BT5, BATT	SIGN IN
RP4F00N0D12	RP4, BT5+WIFI5 NA, BATT, MX	SIGN IN
RP4F00N1B12	RP4, BT5, LNRLSS, BATT	SIGN IN
RP4F00N1D12	RP4, BT5+WIFI5 NA, LNRLSS, BATT, MX	SIGN IN

Rows

[Previous](#) [1](#) [Next](#)

Product Number

Feedback

 Please sign in to view part numbers available for purchase based on your account [Sign In](#)

PART NUMBER	DESCRIPTION
RP4F0000B12	RP4, BT5,BATT
RP4F0000B12	RP4, BT5,BATT
RP4F0000D12	RP4, BT5+WIFI5 NA,BATT
RP4F0000D12	RP4, BT5+WIFI5 NA,BATT
RP4F0000D22	RP4, BT5+Wifi5 ROW,BATT
RP4F0000D22	RP4, BT5+Wifi5 ROW,BATT
RP4F0001B12	RP4, BT5, LNRLSS, BATT
RP4F0001B12	RP4, BT5, LNRLSS, BATT
RP4F0001D12	RP4, BT5+WIFI5 NA, LNRLSS, BATT
RP4F0001D12	RP4, BT5+WIFI5 NA, LNRLSS, BATT
RP4F0001D22	RP4, BT5+WIFI5 ROW, LNRLSS, BATT

RP4F0001D22	RP4, BT5+WIFI5 ROW, LNRLSS, BATT
RP4F0010B12	RP4fB, BT5, BATT, IN&GC
RP4F0010B12	RP4fB, BT5, BATT, IN&GC
RP4F0010D22	RP4, BT5+WIFI5 ROW, BATT, IN&GC
RP4F0010D22	RP4, BT5+WIFI5 ROW, BATT, IN&GC
RP4F0011B12	RP4fB, BT5, LNRLSS, BATT, IN&GC
RP4F0011B12	RP4fB, BT5, LNRLSS, BATT, IN&GC
RP4F0011D22	RP4fD, BT5+Wifi5 ROW, LNRLSS, BATT, IN&GC
RP4F0011D22	RP4fD, BT5+Wifi5 ROW, LNRLSS, BATT, IN&GC



Unboxing - RP4f



Tap to Pair - RP2f and RP4f



Load and Calibrate Media - RP2f and RP4f



Print Test - RPf and RP4f



Wireless Connection - RP2f and RP4f



Bluetooth Pairing - RP2f and RP4f



Using the Belt Clip - RP2f and RP4f



Installing Hand Strap - RP4f



Installing Shoulder Strap - RP4f



Vehicle-Mounted Bracket Charger - RP2f and RP4f



Quad Battery Charger - RP2f and RP4f



Printer Cleaning - RP4f and RP2f



Battery Hot Swap - RP2f and



Install Printer Driver -



Install PrintSets Configuration

Feedback

RP4f

RP2f and
RP4f

Tool - RP2f
and RP4f




Printer
Softcase -
RP4f



How to Add
a Prefix
and Suffix
using
EZConfig -
RP2f and
RP4f

Complete Your Solution



Honeywell Operational Intelligence

Intelligence data insights, asset management and automation for specific pain points to improve functionality and increase ROI.

[→ LEARN MORE](#)



Honeywell Support Services

Maximize the value of your printers with complete support throughout the full lifecycle.

[→ LEARN MORE](#)

Feedback

Honeywell
Industrial Automation
855 S Mint St
Charlotte, NC 28202
800-582-4263

Product name
© Current year Honeywell International Inc.
All rights reserved.

[Safety and Productivity Solutions homepage](#)



This document was generated on (YYYY-MM-DD, HH:mm:ss). Subject to change without notice.

Feedback