

Office 100

SKU: 50 Ohm: 652060 **MSRP:** \$1,649.99
 75 Ohm: 653060

FEATURES

- Ideal amplifier system for small businesses and warehouses
- Covers 8,000 to 25,000 square feet
- Includes LED indicators
- Is ISED approved and works on all Canadian carriers, including Rogers, Telus, Bell, and more



Kit Includes

| | | | | | | | |
|-----------------------------|-------------------------|--------------------------------|----------------------------------|----------------------------------------|-------------------------------------------|--------------------------------------------|--------------------------------------------|
| 652060 50 Ohm Kit | Office 100 Amplifier | Omni Plus Antenna 314422 | Inside Dome Antenna 304412 | Lightning Surge Protector 859902 | 2ft Low-Loss Wilson400 Cable 952302 | 60ft Low-Loss Wilson400 Cable 952360 | 75ft Low-Loss Wilson400 Cable 952375 |
| 653060 75 Ohm Kit | Office 100 Amplifier | Omni Plus Antenna 314423 | Inside Dome Antenna 304419 | Lightning Surge Protector 859992 | 2ft Low-Loss RG11 Cable 951127 | 60ft Low-Loss RG11 Cable 951160 | 75ft Low-Loss RG11 Cable 951175 |


About

weBoost **Office 100** is an ideal amplifier solution for small businesses and warehouses up to 25,000 square feet. With Office 100, anyone who walks into the business will enjoy fewer dropped calls, uninterrupted texts, better voice quality, improved hotspot capability, faster internet speeds, better streaming, and more. All components needed for do-it-yourself installation are included. Office 100 is 5G compatible and improves cell signal on all Canadian carriers, including Rogers, Telus, Bell, and more. Office 100 comes with an industry-leading 3-year manufacturer's warranty and a 30-day money-back guarantee.

Specifications

| | |
|---------------------------|----------------------------------------------------------------------------------------------------------------------|
| SKU NUMBER | 652060 / 653060 |
| FREQUENCIES | Band 12/17 700 MHz Band 13 700 MHz Band 5 850 MHz Band 4 1700/2100 MHz Band 25/2 1900 MHz |
| MAX GAIN | 72 dB |
| MAX UPLINK POWER | 24 dBm |
| MAX DOWNLINK POWER | 12 dBm |
| IMPEDANCE | 50 Ohm / 75 Ohm |
| POWER | 110-240V AC, 50-60 Hz, 20 W |
| CONNECTORS | N-Female / F-Female |
| BOOSTER DIMENSIONS | 6 x 6 x 1.8 in |
| BOOSTER WEIGHT | 1.9 lbs |

How It Works




- 1 Outside antenna:** The outside antenna communicates back and forth with nearby cell towers.
- 2 Booster:** The booster amplifies any cell signals it receives from the outside antenna.
- 3 Inside antenna:** The inside antenna broadcasts these signals for use throughout your business.

Package Dimensions

13 L x 13 W x 15 H



FRONT



SIDE



TOP/BOTTOM



WEIGHT

MASTER CARTON: 13 L x 13 W x 15 H | 16 Lbs. | Qty 1

Support



3-Year Warranty from Purchase.

Website: www.weboost.ca/support

Phone: +1 866 294 1660

Monday to Saturday

FOR PARTNER'S USE

ASSEMBLED IN THE USA



Innovation, Science and Economic Development Canada

UPC

