

SD4839P USB-C 10Gbps Triple Video Driverless Docking Station — 85W PD - DP++/HDMI - Windows

Part Number: K33480NA/AP | UPC Code: 0 85896 33480 4

Add up to three screens, and so much more, quickly and easily.

If you're looking for a driverless USB-C docking solution that offers triple video, 85W Power delivery, and data transfer speeds up to 10Gbps, then the SD4839P is for you.

Simply connect it to any USB-C laptop running Windows 10 or later, and choose the right connections and resolutions for your needs.

Nine-in-one design features plenty of ports for all your connectivity needs, while a zero-footprint mounting option and security cable lock slots let you maximize desktop space, reduce clutter, and protect your investment.


Free DockWorks™ software and a three-year limited warranty. Features include:

- Driverless USB-C connectivity
- Universal Windows compatibility
- Numerous video ports
- Dynamic video support
- 85W Power Delivery
- 9-in-1 design with
 4 USB ports
- Zero-footprint mounting option and security cable lock slots
- Free Kensington DockWorks™ software
- Three-year limited warranty


SD4839P USB-C 10Gbps Triple Video Driverless Docking Station — 85W PD - DP++/HDMI - Windows

Part Number: K33480NA/AP | UPC Code: 0 85896 33480 4

Front



Back



SD4839P USB-C 10Gbps Triple Video Driverless Docking Station — 85W PD - DP++/HDMI - Windows

Part Number: K33480NA/AP | UPC Code: 0 85896 33480 4



Driverless USB-C Connectivity Univers

No driver to download, install, or update. 10Gbps data transfer speed and 85W Power Delivery (PD 3.0) make this an ideal solution for all USB-C Windows laptops supporting DisplayPort Alt Mode and Power Delivery.



Universal Windows Compatibility

Connects seamlessly to any laptop running Windows 10 or later.



Numerous Video Ports

With two DisplayPort++ 1.4 ports and one HDMI 2.0 port, select the right connections and resolutions for your needs. Resolutions supported vary by the device connected (see manual or specifications table for more information).



Dynamic Video Support

Supports up to Triple 1080p @ 60Hz — an ideal solution for multi-monitor setups.



85W Power Delivery

Allows you to quickly and easily charge any Thunderbolt 3, Thunderbolt 4, USB4, or USB-C enabled laptop (USB-C laptops must support Power Delivery).



9-in-1 Design with 4 USB Ports

The front features one USB-C 3.2 Gen2 port (up to 5V/1.5A/10Gbps), three USB-A 3.2 Gen2 ports (up to 5V/0.9A/10Gbps), and a combo audio port. The rear features a Gigabit Ethernet port, two DP++ 1.4 ports, and one HDMI 2.0 port.



Zero-Footprint Mounting Option and Security Cable Lock Slots

Maximize desktop space and reduce cable clutter by mounting your docking station out of the way (mounting bracket K34050WW, sold separately). Lock slots allow you to protect your investment with a cable lock (K65020WW or K64444WW, sold separately).





Free Kensington DockWorks™ Software and Three-Year Limited Warranty

DockWorks™ WiFi Auto-Switch guarantees the fastest, most reliable internet connection; while MAC Address ID Pass-Through and Reset, and Device Connection Monitoring give IT managers maximum network monitoring and visibility. A three-year limited warranty lets you rest assured knowing you're covered by Kensington.

SD4839P USB-C 10Gbps Triple Video Driverless Docking Station — 85W PD - DP++/HDMI - Windows

Part Number: K33480NA/AP | UPC Code: 0 85896 33480 4

C 1	ъ.	1	
SUCTAM	וווחםא	rements	
JVJLLIII	NCUUI	ICHICHES	


	Systems Supported	All Laptops with a USB-C port (must support USB-C Alt Mode and Power Delivery)
	Operating Systems Supported	Windows® 10 or later
	Plug & Play	Yes
	System Resource Requirement	CPU: Intel® Core™ i5 6th generation or above Memory: 8Gb or above GPU: Intel® HD Graphics 620 or above
	Additional Software Information	DockWorks (Windows 10 or later)
	USB-C Power Delivery	PD3.0, 5V/ 9V/ 15V/ 20V@4.25A (up to 85W)
USB Interface		
	Type of USB Connector	USB-C Connector
	Host Connector	Supports USB3.2 Gen2 Type-C with USB-C Alt Mode and Power Delivery
USB Connections		
	Ports	Front Panel - 1 x Power Button - 1 x USB-C 3.2 Gen2 10Gbps (up to 5V/1.5A) - 3 x USB-A 3.2 Gen2 10Gbps (up to 5V/0.9A) - 1 x Audio Combo Jack
		Side Panel - 1 x USB-C Host Port (up to 85W Charging)
		Back Panel - 1 x HDMI 2.0 - 2 x DP1.4++ - 1 x 1Gbps Ethernet - 1 x DC Jack
Network Connections		
	Ethernet Port	RJ45
	Compatible Ethernet Speeds	10/100/1000 Mbps
Host Connectivity		
	Host Docking Connector	USB-C with Power Delivery up to 85W


SD4839P USB-C 10Gbps Triple Video Driverless Docking Station — 85W PD - DP++/HDMI - Windows

Part Number: K33480NA/AP | UPC Code: 0 85896 33480 4


Video Connections


Video Connectors	2 x DisplayPort v1.4 ++ 1 x HDMI 2.0
Maximum Resolution Supported (Host with DP1.4 and DSC turned on)	Triple Display Up to 2 x 4K@30Hz (DP+DP) + 1 x 1080p@60Hz (HDMI)
	Dual Display up to 2 x 4K@60Hz (DP+DP)
	Single Display 1 x 4K@60Hz (DP or HDMI)
HDCP Support	HDCP 2.2 & 1.4
	Maximum Resolution Supported (Host with DP1.4 and DSC turned on)





△	DP1.2	DP1.4 (DSC ON)
DP++ DP++	1080p @ 60Hz	4K @ 60Hz
DP++	1080p @ 60Hz	4K @ 30Hz(DP)
номі		4K @ 30Hz(HDMI)





Audio Connections

	Audio Connectors	1 x 3.5mm audio combo jack
	Audio Channels Supported	Stereo LR
LED Indicator		
	Blue LED	Power indicator
Material Specifications		
	Exterior	PC + ABS with texture
	Bottom	PC + ABS with texture
	Product Color	Pantone Black C
Other Features		
	Kensington Security Slot	Kensington Security Slot Kensington Nano Security Slot
	VESA Mount Compatible	Yes

SD4839P USB-C 10Gbps Triple Video Driverless Docking Station — 85W PD - DP++/HDMI - Windows

Part Number: K33480NA/AP | UPC Code: 0 85896 33480 4

Product	Dimensions
FIOUULL	DIFFICIONS

Product Dimensions		
	Unit Weight	0.59lbs (270g)
	Unit Dimensions without Peripherals (L x W X H)	7.08 x 3.14 x 0.86in (180 x 80 x 22mm)
	Enclosure Color & Material	PC + ABS with texture, Pantone Black C
	Desktop Footprint	22.32in² (144cm²)
Packaging Dimensions		
	Packaging Style	Bulk Package (K33480 NA/EU/UK/AP/JP)
	Packaging Dimensions (L x W X H)	7.71 x 3.97 x 3.97in (196 x 101 x 101mm)
	Packaging Weight	2.31lbs (1.05kg)
	Packaging Content	1 x SD4839P Dock 1 x 1m USB-C cable 1 x Power Supply Unit (Power Cord is varied by different SKUs) 1 x Instruction Guide 1 x Warranty Card 1 x Compliance Sheet
	Master Carton	4pcs
Power & Environmental		
	Power Adapter Rating	Input: 100-240V; 2.5A/Output: 20V DC 6.75A (135W
	Relative Humidity	55% RH operating temperature @ 77°F (25°C)
	Operating Temperature	32 to 113°F (0 to 45°C)
	Storage Temperature	32 to 140°F (0 to 60°C)
Country of Origin, Regula	tory, and Warranty	
	Country of Origin	China for EU/UK/AP/JP, Vietnam for NA
	Certifications & Compliance	CE, CB, ErP, FCC, ICES, UKCA, VCCI, ACCO RSL
	Warranty	3-Year Limited - worldwide
Special Notes		
	Multiple SKUs	Bulk Package (K33480 NA/EU/UK/AP/JP)
		<u> </u>



