

Introducing FortiGate® 70F Series



The FortiGate 70F series provides a fast and secure Next-Generation Firewall and SD-WAN solution in a compact fanless desktop form factor for enterprise branch offices and mid-sized businesses. Protects against cyber threats with system-on-a-chip acceleration and industry-leading secure SDWAN in a simple, affordable, and easy to deploy solution. Fortinet's Security-Driven Networking approach provides tight integration of the network to the new generation of security.

Security

- Identifies thousands of applications inside network traffic for deep inspection and granular policy enforcement
- Protects against malware, exploits, and malicious websites in both encrypted and non-encrypted traffic
- Prevent and detect against known and unknown attacks using continuous threat intelligence from AI-powered FortiGuard Labs security services

Performance

- Delivers industry's best threat protection performance and ultra-low latency using purpose-built security processor (SPU) technology
- Provides industry-leading performance and protection for SSL encrypted traffic

Certification

- Independently tested and validated for best-in-class security effectiveness and performance

Networking

- Delivers advanced networking capabilities that seamlessly integrate with advanced layer 7 security and virtual domains (VDMs) to offer extensive deployment flexibility, multi-tenancy and effective utilization of resources
- Delivers high-density, flexible combination of various high-speed interfaces to enable best TCO for customers for data center and WAN deployments

Management

- Includes a management console that is effective, simple to use, and provides comprehensive network automation and visibility
- Provides Zero Touch Integration with Fortinet's Security Fabric's Single Pane of Glass Management
- Predefined compliance checklist analyzes the deployment and highlights best practices to improve overall security posture

Security Fabric

- Enables Fortinet and Fabric-ready partners' products to provide broader visibility, integrated end-to-end detection, threat intelligence sharing, and automated remediation

SPECIFICATIONS

FG-70F*
FG-71F*



10 Gbps
Firewall Throughput
35,000
New Sessions/Sec.
1.5 Million
Concurrent Sessions



6.5 Gbps
VPN



1.4 Gbps
IPS



1 Gbps
NGFW




800 Mbps
Threat Protection

* Target performance, subject to final values.



Deployment Modes

Next Generation Firewall
Secure SD-WAN



Power Supply

AC Power Adapter



Interfaces

- 7× GE RJ45 Internal Ports
- 2× GE RJ45 WAN Ports
- 1× GE RJ45 DMZ Port



Highlights

- **Centralized Management** - Configure and manage policies centrally. Take action with rich reporting and analytics of network traffic, user activity, and threats.
- **VPN and Zero Trust Network Access** - High IPsec VPN performance enables fast, stable, and secure access for remote employees while ensuring compliance and strengthening security with zero-trust policies enforcement that verify only authorized users, devices, and applications are accessing data.
- **Built-in SD-WAN** - predictable application performance with real-time traffic steering, self-healing networks and sub-second failover
- **Security Fabric Integration** - Share actionable threat intelligence across the entire attack surface to build a consistent and coordinated end-to-end security posture.



www.fortinet.com

Copyright © 2022 Fortinet, Inc. All rights reserved. Fortinet®, FortiGate®, FortiCare® and FortiGuard®, and certain other marks are registered trademarks of Fortinet, Inc., and other Fortinet names herein may also be registered and/or common law trademarks of Fortinet. All other product or company names may be trademarks of their respective owners. Performance and other metrics contained herein were attained in internal lab tests under ideal conditions, and actual performance and other results may vary. Network variables, different network environments and other conditions may affect performance results. Nothing herein represents any binding commitment by Fortinet, and Fortinet disclaims all warranties, whether express or implied, except to the extent Fortinet enters a binding written contract, signed by Fortinet's General Counsel, with a purchaser that expressly warrants that the identified product will perform according to certain expressly-identified performance metrics and, in such event, only the specific performance metrics expressly identified in such binding written contract shall be binding on Fortinet. For absolute clarity, any such warranty will be limited to performance in the same ideal conditions as in Fortinet's internal lab tests. Fortinet disclaims in full any covenants, representations, and guarantees pursuant hereto, whether express or implied. Fortinet reserves the right to change, modify, transfer, or otherwise revise this publication without notice, and the most current version of the publication shall be applicable.