

OVERVIEW



1. Power connector	6. Power button
2. HDMI 1.4	7. Headphone / microphone combo jack (3.5mm)
3. 2x USB 3.2 Gen 2	8. Optical drive eject button
4. Ethernet (RJ-45)	9. Top camera
5. 2x USB 2.0	

PERFORMANCE

Processor

Processor Family

Intel® Celeron®, Intel Pentium®, or 12th Generation Intel Core™ i3 / i5 Processor

Processor

Processor Name	Cores	Threads	Base Frequency	Max Frequency	Cache	Memory Support	Processor Graphics
Celeron 7305	5 (1 P-core + 4 E-core)	6	P-core 1.1GHz / E-core 0.9GHz	-	8MB	DDR4-3200	Intel UHD Graphics
Pentium 8505	5 (1 P-core + 4 E-core)	6	P-core 1.2GHz / E-core 0.9GHz	P-core 4.4GHz / E-core 3.3GHz	8MB	DDR4-3200	Intel UHD Graphics
Core i3-1220P	10 (2 P-core + 8 E-core)	12	P-core 1.5GHz / E-core 1.1GHz	P-core 4.4GHz / E-core 3.3GHz	12MB	DDR4-3200	Intel UHD Graphics
Core i5-1240P	12 (4 P-core + 8 E-core)	16	P-core 1.7GHz / E-core 1.2GHz	P-core 4.4GHz / E-core 3.3GHz	12MB	DDR4-3200	Intel Iris® Xe Graphics

Operating System

Operating System

- Windows® 11 Home 64
- No operating system

Graphics

Graphics^[1]

Graphics	Type	Memory	Connector	Max Resolution	Key Features
Intel UHD Graphics	Integrated	Shared	1x HDMI® 1.4	1920x1080@60Hz(HDMI)	DirectX® 12
Intel Iris Xe Graphics	Integrated	Shared	1x HDMI 1.4	1920x1080@60Hz(HDMI)	DirectX 12

Notes:

- The information of integrated graphics are not applicable for the models without integrated graphics (for the details, please refer to processor section)

Monitor Support

Monitor Support

Supports up to 2 independent displays via native display and 1 external monitor; supports external monitor via HDMI

Chipset

Chipset

Intel SoC (System on Chip) platform

Memory

Max Memory^[1]

Up to 16GB DDR4-3200

Memory Slots

Two DDR4 SO-DIMM slots

Memory Type

DDR4-3200

Memory Protection

Non-ECC

Notes:

- The max memory is based on the test results with current Lenovo® memory offerings. The system may support more memory as the technology develops.

Storage

Storage Support^[1]

Up to two drives, 1x 2.5" HDD + 1x M.2 SSD

- 2.5" HDD up to 1TB
- M.2 SSD up to 512GB

Storage Type

Disk Type	Interface	RPM	Offering	Security
2.5" SATA HDD	SATA 6Gb/s	5.4K	-	-
M.2 2242 SSD	PCIe® NVMe®, PCIe 3.0 x4	-	-	-
M.2 2280 SSD	PCIe NVMe, PCIe 4.0 x4	-	-	-

RAID

No support

Notes:

1. The storage capacity supported is based on the test results with current Lenovo storage offerings. The system may support larger storage as the technology develops.

Removable Storage

Optical

- DVD burner (DVD±RW), SATA 1.5Gb/s, slim (9.0mm)
- None

Card Reader

No card reader

Multi-Media

Audio Chip

High Definition (HD) Audio, Realtek® ALC256 codec

Speakers

Stereo speakers, 3W x2, Audio by HARMAN

Microphone

- Single microphone
- Dual array microphone

Camera

- HD 720p, fixed focus
- No camera

Power Supply

Power Supply

Power	Type	Efficiency	Key Features
90W	Adapter	89%	100V - 240V

DESIGN

Display

Display^{[1][2]}

Size	Resolution	Touch	Type	Brightness	Surface	Aspect Ratio	Contrast Ratio	Color Gamut	Viewing Angle	Key Features
21.5"	FHD (1920x1080)	None	IPS	250 nits	Anti-glare	16:9	1000:1	72% NTSC	horizontal: +/- 89°, vertical: +/- 89°	Borderless design
21.5"	FHD	Multi-	IPS	250 nits	Anti-	16:9	1000:1	72%	horizontal: +/-	Borderless

	(1920x1080)	touch			glare			NTSC	89°, vertical: +/- 89°	design
--	-------------	-------	--	--	-------	--	--	------	---------------------------	--------

Touchscreen

- Advanced In-cell Touch (AIT), supports 10-point touch
- Non-touch

Notes:

- California Electronic Waste Recycling Fee
In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product.
For more information, go to <https://www.calrecycle.ca.gov/Electronics/Consumer>
- IPS

Input Device

Pen

No support

Keyboard

- EOS Wireless Keyboard, black
- EOS Wireless Keyboard, white
- Lenovo Calliope Keyboard (USB connector), black
- Lenovo Calliope Keyboard (USB connector), white
- Lenovo Calliope Wireless Keyboard, black
- Lenovo Calliope Wireless Keyboard, silver
- Lenovo Calliope Wireless Keyboard, white

Mouse

- Lenovo Calliope Mouse (USB connector), black
- Lenovo Calliope Mouse (USB connector), white
- Lenovo Calliope Wireless Mouse (2.4GHz via USB receiver), black
- Lenovo Calliope Wireless Mouse (2.4GHz via USB receiver), white

Mechanical

Form Factor

AIO (21.5 inches)

Dimensions (WxDxH)

490.26 x 185.34 x 404.89 mm (19.31x 7.29 x 15.93 inches)

Packaging Dimensions (WxDxH)

231 x 588 x 525 mm (9.09 x 23.14 x 20.66 inches)

Weight

6.09 kg (13.42 lbs)

Packaging Weight

All models: 8.3 kg (18.29 lbs)

Case Color

- Black
- White

Bays

- 1x 2.5" disk bay
- 1x slim ODD bay

Expansion Slots

Two M.2 slots (one for WLAN, one for SSD)

Stand

Monitor stand, supports -5° to +25° tilt

CONNECTIVITY

Network

Onboard Ethernet

Gigabit Ethernet, 1x RJ-45

WLAN + Bluetooth^[1]

- 802.11ac 2x2 Wi-Fi® + Bluetooth 5.0, M.2 card
- Wi-Fi 6, 802.11ax 2x2 Wi-Fi + Bluetooth 5.2, M.2 card

Notes:

1. Bluetooth 5.2 is hardware ready but may run at a lower version due to OS limitation

Ports^[1]**Rear Ports^{[1][2]}**

- 2x USB 2.0
- 2x USB 3.2 Gen 2
- 1x HDMI 1.4
- 1x Ethernet (RJ-45)
- 1x power connector

Bottom Ports

1x headphone / microphone combo jack (3.5mm)

Notes:

1. The transfer speed of following ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.
USB 2.0: 480 Mbit/s;
USB 3.2 Gen 1 (SuperSpeed USB 5Gbps, formerly USB 3.0 / USB 3.1 Gen 1): 5 Gbit/s;
USB 3.2 Gen 2 (SuperSpeed USB 10Gbps, formerly USB 3.1 Gen 2): 10 Gbit/s;
USB 3.2 Gen 2x2 (SuperSpeed USB 20Gbps): 20 Gbit/s;
Thunderbolt™ 3/4: 40 Gbit/s
2. For video ports on discrete graphics, please see graphics section

SECURITY & PRIVACY

Security

Security Chip

Firmware TPM 2.0 integrated in SoC

Physical Locks

No physical locks

BIOS Security

- Administrator password
- Power-on password
- Hard disk password

SERVICE

Warranty

Base Warranty^[1]

- 1-year mail-in service
- 1-year depot service
- 1-year limited onsite service
- 2-year depot service
- 3-year depot service
- OB

Notes:

1. More information of warranty policy, please access <https://pcsupport.lenovo.com/warranty>

ENVIRONMENTAL

Operating Environment

Temperature

- Operating: 5°C (41°F) to 35°C (95°F)
- Storage: -20°C (-4°F) to 60°C (140°F)

Humidity

- Operating: 20% to 80%
- Storage: 10% to 90%

Altitude

- Operating: 0 m (0 ft) to 3048 m (10,000 ft)
- Storage: 0 m (0 ft) to 12192 m (40,000 ft)

CERTIFICATIONS

Green Certifications

Green Certifications

- ENERGY STAR® 8.0
- ErP Lot 3 and Lot 7
- RoHS compliant

- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION “AS IS,” WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.
- The specifications on this page may not be available in all regions, and may be changed or updated without notice.



intel



intel



intel



intel



intel



intel