



HP 150 Wired Mouse and Keyboard (240J7AA)

Overview

Sometimes everything just clicks

Pick up and go with these perfect plug-in-play companions, a precise mouse and ergonomic keyboard with all the bells and whistles for wherever your journey takes you.

Quiet is just your type

This chiclet-style keyboard's design is sleek and silent to the touch. The low-profile design keeps keystrokes quick, comfy, and quite accurate...just your type.

Click real quick

Click in quick with USB plug-and-play setup that'll have you dragging and dropping before you can pick up your jaw.

Keystroke of genius

Common controls are integrated into 12 shortcut combos with the fn key—music, movies, volume, homepage, bookmarks, and email. Now that's a shortcut above.

Features

Looks good, feels good

This keyboard and mouse are ergonomically designed to fit your natural comfortable position. Left, right, and scroll wheel mouse buttons keep your motions in control.

Precisely right

With its 1600 DPI optical sensor, this mouse works on almost any surface with astounding accuracy. Stash it in your bag with your laptop and you'll be good to go.

Let there be LED

LED indicators illuminate Number Lock, Caps Lock, and Scroll Lock so you don't have to guess what's on or off. One less thing.

Specifications

Minimum dimensions (W x D x H)	42.59 x 14.61 x 2.68 cm (keyboard); 10.34 x 6.11 x 3.42 cm (mouse)
Minimum dimensions (W x D x H)	16.77 x 5.75 x 1.06 in (keyboard); 4.07 x 2.41 x 1.35 in (mouse)
Weight	0.44 kg (keyboard); 0.06 kg (mouse)
Weight	0.97 lb (keyboard); 0.13 lb (mouse)
Package dimensions (W x D x H)	50.5 x 16.6 x 4 cm
Package weight	0.84 kg
Minimum System Requirements	Available USB-A port
UPC number	196337852525
Manufacturer Warranty	One-year limited warranty.
What's in the box	Mouse; Keyboard; Quick Start guide; Warranty

Additional specifications

Buttons	3
Cable length	100 cm
Cable length (imperial)	39.37 in
Color	Black
Compatibility	Compatible with PCs with available USB-A port.
Compatible Operating Systems	Windows 11; Windows 10
Connection type	Wired USB Type-A
Connector description	USB Type-A
Country of origin	Made in China
Datasheet photo 1	https://prism.hp.com/PRO.Crystal.1/DAMHandler/Accessories/Elephanta and Oreo_HP Wired Combo_100 wired mouse and keyboard combination_CoreSet_main1.png
Datasheet photo 2	https://prism.hp.com/PRO.Crystal.1/DAMHandler/Accessories/Elephanta and Oreo_HP Wired Combo_100 wired mouse and keyboard combination_CoreSet_FrontLeft_main2.png
Keyboard type	Full size; 2.5-zone layout
Keys structure	Plunger; Low profile key travel; 2.5 mm
LED	Number Lock, Caps Lock and Scroll Lock
LED indicator	Caps lock; Num lock; Scroll lock
Package dimensions (W x D x H)	19.88 x 6.54 x 1.57 in
Package weight	1.85 lb
Product subgroup	Keyboard & Mouse
Sensor nominal value	1600 dpi
Sensor technology	Red optical tracking
UNSPSC code	43211733

Disclaimer — Copyright

Actual product may vary from image shown.

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.