



**C2G**  
**5ft (1.5m) Cat6 Snagless Unshielded (UTP) Ethernet Network Patch Cable - Black**  
Part No. CG-31342



For fast Ethernet and Gigabit computer networks that require bandwidth-intensive voice, data, or video distribution applications. Meets all Cat6 TIA/EIA standards, and drastically reduces both impedance and structural return loss (SRL). Each of the individual pairs is bonded together to help maintain the twist-spacing throughout the line right up to the termination point. Constructed from high quality copper cable, this design minimizes Near-End Crosstalk (NEXT) levels. The molded, snagless boot prevents unwanted cable snags during installation and provides extra strain relief. Available in a variety of colors to easily color-code your network installation.

## Features & Benefits

- |   |  |
|---|--|
| Snagless design protects clips when plugging and unplugging | Standard RJ45 connectors and unshielded twisted pair wires |
| Available in 10 colors to color-code a network              | Available in lengths up to 150ft                           |

## Specifications

### General Info

Product Line	C2G	Color	Black
UPC Number	757120313427	Country Of Origin	Vietnam
Features	PoE (Power Over Ethernet)	Application Sector	Residential, Commercial, Industrial
Type	Cable		

### Dimensions

Cable Length	5 ft
--------------	------

### Additional Information

Prop 65 Warning Required	Yes	Prop 65 Warning Language	Cancer and Reproductive Harm
--------------------------	-----	--------------------------	---------------------------------

### Technical Information

Jacket Material	PVC (Polyvinyl Chloride)	Wire Gauge	24 AWG
Cable Type	Ethernet Patch Cable, Booted, Snagless, Unshielded (UTP)	Jacket Rating	Standard Non-Rated
Adapter Rear	RJ-45 Male	Adapter Front	RJ-45 Male