



C2G
6ft (1.8m) Velocity™ 3.5mm M/M Mono Audio Cable
Part No. CG-40620



This cable is specifically designed to provide quality signal transfer for mono audio and data transfer applications. It features two 27 AWG oxygen-free copper conductors, a drain wire, an aluminum foil shield to prevent unwanted EMI/RFI interference, and fully molded, gold-plated connectors providing strain relief for a quality connection.

Features & Benefits

Two 27 AWG oxygen-free copper conductors

Aluminum foil shield to prevent unwanted EMI/RFI interference

Fully molded, gold-plated connectors

Specifications

General Info

Product Line	C2G	UPC Number	757120406204
Country Of Origin	China	Application Sector	Residential, Commercial
Type	Cable		

Dimensions

Cable Length	6 ft
--------------	------

Additional Information

Prop 65 Warning Required	Yes	Prop 65 Warning Language	Cancer and Reproductive Harm
--------------------------	-----	--------------------------	------------------------------

Technical Information

Jacket Material	PVC (Polyvinyl Chloride)	Cable Type	Audio
Jacket Rating	Standard Non-Rated	Adapter Rear	3.5mm Mono Male

Adapter Front

3.5mm Mono Male
