

Important Note

P002-000 does not transform voltage. Verify your device or power supply is within the output range before use.

NEMA 5-15R to C14 Power Cord Adapter - 15A, 125V, Black

MODEL NUMBER: P002-000



5-15R to C14 adapter allows you to connect your PC or other device with a NEMA 5-15P plug to a UPS with a C13 power outlet.

Features

C14 to NEMA 5-15R Adapter Connects Computers, Monitors and Other Equipment This UL-listed power cord adapter is designed for low-voltage home/office setups. It converts a NEMA 5-15P plug into a C14 connector and is ideal for a device's built-in power cord that doesn't match the available outlet. You can use this adapter to connect a computer, monitor, printer or other device with a NEMA 5-15P plug to an AC wall outlet or UPS system with C13 power outlets. You can also connect your C13 printer or monitor to a switched source on your PC, allowing you to turn both devices on and off at the same time.

Specifications

OVERVIEW	
UPC Code	037332217936
Device Compatibility	Computer; Monitor/HDTV; Printer; UPS; PDU; Server
Country/Region	North America
INPUT	
Maximum Input Amps	15
Voltage Compatibility (VAC)	125
CONNECTIONS	

Highlights

- Recommended for powering computers, printers and other peripherals
- Converts a NEMA 5-15P connector into a C14 connector to match available outlet

Applications

- Connect devices like computers, printers and monitors to a C13 outlet near your workstation

Package Includes

- P002-000 NEMA 5-15R to C14 Power Cord Adapter, Black



Powering Business Worldwide

TRIPP LITE
SERIES

Side A - Connector 1	IEC-320-C14
Side B - Connector 1	NEMA 5-15R
PHYSICAL	
Plug Color	Black
Wire Gauge (OD - mm ²)	0
Cable Length (ft.)	0
Cable Length (m)	0.00
Shipping Dimensions (hwd / in.)	5.00 x 3.98 x 0.50
Shipping Dimensions (hwd / cm)	12.70 x 10.11 x 1.27
Shipping Weight (lbs.)	0.11
Shipping Weight (kg)	0.05
ENVIRONMENTAL	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	14° to 140°F (-10° to 60°C)
Operating Humidity Range	30% to 80% RH
Storage Humidity Range	30% to 80% RH
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	No
Locking Plug	No
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	CSA (Canada); cUL Listed; UL Listed
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.