



A KLEIN TOOLS COMPANY
WWW.ERGODYNE.COM



EXTREME CUT-RESISTANT HANDLING GLOVES

FOR OPTIMAL GRIP AND HEAVY-DUTY CUT PROTECTION FROM SHARP MATERIALS



LEVEL A7 CUT RESISTANCE

FOR THE HIGHEST LEVEL OF CUT PROTECTION



ProFlex 7072 Nitrile Coated Cut-Resistant Gloves - ANSI/ISEA 105-2016 A7, EN388: 4X44F, 18g

FEATURES

- CUT RESISTANT – ANSI/ISEA 105-2016 level A7 cut protection and level 6 abrasion resistance for protection when working with incredibly sharp or jagged materials
- INDUSTRY-LEADING ASX NITRILE – 20% better gripping performance than sandy nitrile, outperforms other coatings on all surfaces (wet, oily and dry)
- DUAL-LAYER COATING – Smooth nitrile layer + anti-slip nitrile layer for ultimate water wicking grip performance, comfort and durability
- BREATHABLE – Smooth nitrile layer allows airflow to pass through surface coating

SPECIFICATIONS

ANSI ABRASION LEVEL	6
ANSI CUT LEVEL	A7
COATING	NITRILE
CUFF	KNIT
GAUGE	18
PALM	NITRILE
PRODUCT FEATURES	MACHINE WASHABLE
PRODUCT TYPE	GLOVES
PROTECTION	CUT RESISTANT, ABRASION RESISTANT
STANDARDS/COMPLIANCE	ANSI/ISEA 105-2016, EN 388
TECHNOLOGY	ASX™

ORDER MULTIPLES

ORDER IN MULTIPLES OF:

ITEMS



SIZE & CUFF COLOR	FITS HANDS
XS (6) ●	5.5-6IN (14-15CM)
S (7) ●	7-8IN (18-20CM)
M (8) ●	8-9IN (20-23CM)
L (9) ●	9-10IN (23-25CM)
XL (10) ●	10-11IN (25-28CM)
2XL (11) ○	11-12IN (28-30CM)

INSTRUCTIONS
Measure around the palm.
DO NOT include the thumb area.



ITEM #	COLOR	SIZE	TYPE
10302	GRAY	S	12-PAIR
10303	GRAY	M	12-PAIR
10304	GRAY	L	12-PAIR
10305	GRAY	XL	12-PAIR
10306	GRAY	2XL	12-PAIR
10311	GRAY	XS	1-PAIR
10312	GRAY	S	1-PAIR
10313	GRAY	M	1-PAIR
10314	GRAY	L	1-PAIR
10315	GRAY	XL	1-PAIR
10316	GRAY	2XL	1-PAIR

For more information and full size images, visit <https://www.ergodyne.com/proflex-7072-nitrile-coated-cut-resistant-gloves-ansi-a7-18g>