

OVERVIEW



1. Headphone / microphone combo jack (3.5mm)	4. ThinkSmart One Cable
2. Power button	5. Kensington Security Slot
3. Power connector	

PERFORMANCE

Processor

Processor Family

8th Generation Intel® Core™ i5 Processor

Processor

Processor Name	Cores	Threads	Base Frequency	Max Frequency	Cache	Memory Support	Processor Graphics
Core i5-8365U	4	8	1.6GHz	4.1GHz	6MB	DDR4-2400	Intel UHD Graphics

Operating System

Operating System

Windows® 10 IoT Enterprise

Graphics

Graphics

Graphics	Type	Memory	Connector	Max Resolution	Key Features
Intel HD graphics	Integrated	Shared	2x HDMI®	4096x2160@60Hz(HDMI)	DirectX® 11.2

Monitor Support

Monitor Support

Supports up to 3 independent displays via native display and 2 external monitors; supports external monitors via 2x HDMI (on ThinkSmart™ One Cable)

Chipset

Chipset

Intel SoC (System on Chip) platform

Memory

Max Memory^[1]

Up to 8GB DDR4-2400

Memory Slots

Memory soldered to systemboard, no slots, dual-channel

Memory Type

DDR4-2400

Memory Protection

Non-ECC

Notes:

1. The max memory is based on the test results with current Lenovo® memory offerings. The system may support more memory as the technology develops.

Storage

Storage Support^[1]

One drive, 128GB M.2 2242 SSD

Storage Type^{**}

Disk Type	Interface	RPM	Security
M.2 2242 SSD	PCIe® NVMe®, PCIe 3.0 x4	-	-
M.2 2280 SSD	PCIe NVMe, PCIe 3.0 x4	-	-

Notes:

1. The storage capacity supported is based on the test results with current Lenovo storage offerings. The system may support larger storage as the technology develops.

Removable Storage

Card Reader

No card reader

Multi-Media

Audio Chip

High Definition (HD) Audio

Speakers

4 premium tuned speakers, 3W x4

Microphone

Four omnidirectional microphones for 360° audio capture

Camera

No camera

Sensor

Sensors

IR-based proximity sensor, automatically dim / brighten display (detection angle: +/- 45% (from display); detection distance: 3 meters at maximum)

Power Supply

Power Supply

Power	Type	Efficiency	Key Features
90W	Adapter	88%	Autosensing

DESIGN

Display

Display^[1]

Size	Resolution	Touch	Type	Brightness	Surface	Aspect Ratio	Contrast Ratio	Color Gamut	Viewing Angle	Key Features
10.1"	FHD (1920x1200)	Multi-touch	WVA	320 nits	Anti-glare	16:10	1000:1	-	horizontal: +/- 80°	Smudge resistant, 360° rotation support

Touchscreen

TDDI technology, supports 10-point touch

Notes:

1. California Electronic Waste Recycling Fee
- In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product.
- For more information, go to <https://www.calrecycle.ca.gov/Electronics/Consumer>

Input Device

Keyboard

No keyboard

Mouse

No mouse

Mechanical

LED indicators

360 degree LED ring on hinge neck and LED on top, indicates status for all users in the room

Buttons

Power button

Dimensions (WxDxH)

240 x 200 x 185.3 mm (9.45 x 7.87 x 7.30 inches)

Weight

Around 2.45 kg (5.4 lbs)

Case Color

Raven black and red bottom

EOU

No support

Stand

No stand

CONNECTIVITY

Network

Ethernet

Gigabit Ethernet, Intel Ethernet Connection I219-LM, 1x RJ-45, supports Wake-on-LAN

WLAN + Bluetooth^[1]

Intel Wireless-AC 9560, 802.11ac Dual Band 2x2 Wi-Fi® + Bluetooth 5.0, Intel vPro technology support, M.2 card

Notes:

1. Bluetooth 5.2 is hardware ready but may run at a lower version due to OS limitation

Ports^[1]

Front Ports

1x headphone / microphone combo jack (3.5mm)

Rear Ports

None

Left Ports^[2]

- 2x USB 3.1 Gen 2
- 1x USB-C® 2.0 (support data transfer and display)
- 1x HDMI-in
- 1x Ethernet (RJ-45)
- 1x DisplayPort™
- 1x power connector

Right Ports

None

One Cable

Ports on ThinkSmart One Cable: 3x USB 3.2 Gen 1, 1x USB-C 3.2 Gen 1, 2x HDMI out, 1x Ethernet (RJ-45), 1x power connector

Notes:

1. The transfer speed of following ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.
USB 2.0: 480 Mbit/s;
USB 3.2 Gen 1 (SuperSpeed USB 5Gbps, formerly USB 3.0 / USB 3.1 Gen 1): 5 Gbit/s;
USB 3.2 Gen 2 (SuperSpeed USB 10Gbps, formerly USB 3.1 Gen 2): 10 Gbit/s;
USB 3.2 Gen 2x2 (SuperSpeed USB 20Gbps): 20 Gbit/s;
Thunderbolt™ 3/4: 40 Gbit/s
2. ThinkSmart One Cable occupies the ports on base (2x USB, 1x USB-C, 1x DP, 1x Ethernet, 1x Power DC-IN)

SECURITY & PRIVACY

Security

Security Chip

Discrete TPM 2.0, TCG certified

Physical Locks

- Cable lock box and secure cable management door to secure the cable connections
- Kensington® Security Slot, 3 x 7 mm

BIOS Security

- Administrator password
- Power-on password
- Hard disk password
- Boot sequence control
- Boot without keyboard and mouse
- USB port disablement

MANAGEABILITY**System Management****System Management**

Intel vPro with Intel AMT 11.0

SERVICE**Warranty****Base Warranty**^[1]**

- 3-year limited onsite service
- 3-year premier support service

Notes:

1. More information of warranty policy, please access <https://pcsupport.lenovo.com/warranty>

SOFTWARE**Preinstalled Software****Preinstalled Software**

- Microsoft® Teams Rooms (for MT 11H0 / 11H1)
- Zoom Rooms (for MT 11H2 / 11H3)

CERTIFICATIONS**Green Certifications****Green Certifications**

RoHS compliant

Other Certifications**Other Certifications**

TÜV Rheinland® Ultra Low Noise

- This is a telepresence technology product.
- Feature with ** means that only one offering listed under the feature is configured on selected models.
- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION "AS IS," WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow

disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.

- The specifications on this page may not be available in all regions, and may be changed or updated without notice.

