

Replacement Universal AC/DC Power Adapter with NA Power Cord for Docking Stations - 150W (19.5V/7.7A)

Product ID: 158-DOCKPOWERADAPTER



This 150W AC/DC power supply can provide a power source for any electronic device that has an N-type barrel and requires 19.5 volts and up to 7.7 amps of power.

The power supply is a perfect replacement for the lost or damaged 19.5-volt 7.7-amp power adapter you've used to power your existing electronics.

When downtime isn't an option, keeping spare power adapters on hand ensures that you won't be left waiting for a replacement to arrive or have to replace your devices just for the sake of a compatible power source.

This 19.5V 7.7A DC power supply is a direct replacement for the power adapters included with the following StarTech.com products:

DK30C2DPEP Laptop Docking Station

DK30C2DPPD Laptop Docking Station

DK31C3HDPD Laptop Docking Station

DK30CH2DEP Laptop Docking Station

DK30CH2DPPD Laptop Docking Station

DK30CHDDPPD Laptop Docking Station

DK30CHHPD Laptop Docking Station

DK30CHDPD Laptop Docking Station

MST30C2HHPD Laptop Docking Station

This product is backed for 3-years by StarTech.com, including free lifetime 24/5 multi-lingual technical assistance.

Certifications, Reports and Compatibility



Applications

- Replace a lost or broken 19.5V DC power supply
- Keep an extra power adapter on hand for your mission-critical devices

Features

- **REPLACEMENT POWER ADAPTER:** Replaces the power adapter included with models of StarTech.com docking stations
- **WORKS WITH:** DK30C2DPEP, DK30C2DPPD and DK31C3HDPPD laptop docking stations
- **TECHNICAL SPECIFICATIONS:** 150W Power Adapter - 100 - 240 AC Input Voltage - 19.5V Output Voltage - 7.7A Output Current - NEMA 1-15P - N-Barrel Connector (5.5 mm outside diameter / 2.5 mm inside diameter)
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this power adapter is backed for 3-years including free lifetime 24/5 multi-lingual technical assistance

Power

Warranty	3 Years
Power Source	AC Adapter Included
Input Voltage Frequency	50 - 60Hz
Max Inrush Current	29% margin of the I ² T (Ampere Squared Seconds) rating of the input fuse and bridge rectifier
Input Voltage	100 - 240 AC
Input Current	2.5
Output Voltage	19.5V DC
Output Current	7.7A
Center Tip Polarity	Positive

Plug Type	N
Power Consumption (In Watts)	150

Physical Characteristics

Product Length	2.6 in [6.5 cm]
Product Width	5.4 in [13.7 cm]
Product Height	0.8 in [2.1 cm]
Weight of Product	1.4 lb [0.6 kg]

Packaging Information

Package Quantity	1
Package Length	7.9 in [20.0 cm]
Package Width	9.4 in [24.0 cm]
Package Height	1.6 in [4.0 cm]
Shipping (Package) Weight	1.4 lb [0.6 kg]

What's in the Box

Included in Package	1 - universal power adapter (NA)
---------------------	----------------------------------

****Product appearance and specifications are subject to change without notice.***