

HP LaserJet Pro 4001ne Printer (2Z599E)



Get blazing fast speeds and a smart printing system for effortless, secure, and sustainable printing.

This modern printer is built for maximum productivity with fast speeds and reliable hardware, delivering effortless everyday use so you can focus more on your business. And with HP+, printers have never been easier to manage and use from anywhere.



Maximum productivity.

Support your dynamic workteam with this high-performing printer, ideal for up to 10 users.

Effortless management.

Guided, cloud-based setup makes it easy to configure new printers and onboard users from any location.[2]

HP Wolf Pro security, made better with HP+.

Get printer security out of the box. Preconfigured settings mean it's ready when you are.

Featuring

Large workteam solution

Blazing fast speed ^[1]

Simple shortcuts

Set up. Invite users. And done. ^[2]

Control at your fingertips

HP Smart ^[1]

Specifications

| | |
|------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Print Resolution Technologies | HP FastRes1200, HP ProRes1200, Economode |
| Print quality black (best) | Fine Lines (1200 x 1200 dpi) |
| Print speed black (ISO, A4) | Up to 40 ppm |
| Print speed black (ISO, letter) | Up to 42 ppm |
| Print speed | Prints up to 42/40 ppm (Letter/A4) |
| Functions | Print |
| Duty cycle (monthly, A4) | Up to 80,000 pages |
| Duty cycle (monthly, letter) | Up to 80,000 pages |
| Printer smart software features | Manual duplex and booklet printing, HP Auto-On/Auto-Off Technology, Job Storage with PIN printing, N-up printing, collation, watermarks, install printer driver only, Economode for toner savings, accepts a variety of paper sizes and types ^[3] |
| Energy savings feature technology | HP Auto-On/Auto-Off Technology; EcoSmart black toner; Instant-on Technology; Power save |
| Replacement cartridges | HP 148A Black Original LaserJet Toner Cartridge (~2,900 pages), W1480A; HP 148X Black Original LaserJet Toner Cartridge (~9,500 pages), W1480X ^[6] |
| Supplies feature | HP JetIntelligence Cartridge |
| Connectivity, standard | 1 Hi-Speed USB 2.0; 1 host USB at rear side; Gigabit Ethernet 10/100/1000BASE-T network; 802.3az(EEE) |
| Mobile printing capability | HP Smart App; Apple AirPrint™; Mopria™ Certified |
| Network protocols, supported | TCP/IP, IPv4, IPv6; Print: TCP-IP port 9100 Direct Mode, LPD (raw queue support only), Apple AirPrint™, Mopria, IPP Print; Discovery: SLP, Bonjour, Web Services Discovery; IP Config: IPv4 (BootP, DHCP, AutoIP, Manual), IPv6 (Stateless Link-Local and via Router, Statefull via DHCPv6), SSL Security and Certificate management; Management: SNMPv1, SNMPv2, SNMPv3, HTTP/HTTPS, Syslog, FTP FW Download |
| Software included | No software solutions are included in the Box only on http://hp.com ; http://123.hp.com ; |
| Compatible Operating Systems | Windows 11; Windows 10; Windows 7; Windows Client OS; Android; iOS; macOS 10.15 Catalina; macOS 11 Big Sur; macOS 12 Monterey; Chrome OS |
| Technical features | AirPrint; Compact size; ENERGY STAR®; Ethernet; Fast First Page Out; HP Auto-On/Auto-Off; JetIntelligence Toners; Professional print quality; Private Print via PIN |
| Sustainable impact specifications | Recyclable through HP Planet Partners; Net zero-deforestation prints with HP+; Compatible with Accessibility Accessories; Contains post-consumer recycled plastic |
| Energy star certified | No |
| Ecolabels | IT ECO Declaration |
| Blue Angel compliant | No, please refer to the ECI (Ecolabel Comparison Information) document |
| Display area (imperial) | 1.79 x 0.53 in |
| Display area (metric) | 4.55 x 1.35 cm |
| Display | 2-line back lit LCD graphic display |
| Minimum dimensions (W x D x H) | 381 x 357 x 216 mm (Without trays and covers not extended) |
| Minimum dimensions (W x D x H) | 15 x 14.06 x 8.5 in (Without trays and covers not extended) |
| Weight | 8.22 kg |
| Weight | 18.13 lb |
| Power consumption | 495 watts (active printing), 5.5 watts (ready), 0.5 watts (sleep), 0.5 (Auto Off/Wake on LAN, enabled at shipment), 0.05 watts (Auto-off/Manual-on), 0.05 (Manual Off) (Power requirements are based on the country/region where the printer is sold. Do not convert operating voltages. This will damage the printer and void the product warranty.) |
| Power supply type | Internal (built-in) Power Supply |
| What's in the box | Preinstalled HP Black Original LaserJet Toner Cartridge; Getting Started Guide; Support Flyer; Warranty Guide; Regulatory Flyer; Power cord; USB cable (AP & Wireless Only) ^[2] |
| Manufacturer Warranty | Two-year Bench/Depot Repair warranty. Warranty and support options vary by product, country and local legal requirements. Contact your Contractual Vendor or go to hp.com/support to learn about HP award winning service and support options in your region. |

Top Recommended Displays, Accessories and Services

No Top Recommended Displays, Accessories and Services

Messaging Footnotes

[1] Smart app (Smart Pro): Requires the HP Smart app download. For details on local printing requirements see www.hp.com/go/mobileprinting. Certain features/software are available in English language only and differ between desktop and mobile applications. Subscription may be required.

[2] Easy to set up and manage - Requires use of Smart Admin Dashboard for printer setup and onboarding of users.

Technical Specifications Footnotes

[2] For yield information on the cartridge included with your printer, see <http://www.hp.com/go/toneryield>. Yield values measured in accordance with ISO/IEC 19752 and continuous printing. Actual yields vary considerably based on images printed and other factors.

[3] Job Storage feature requires a purchase of separate USB flash drive with a minimum of 16 GB capacity.

[6] Declared yields based on ISO/IEC 19752 and continuous printing. Actual yields vary considerably based on images printed and other factors. For details see <http://www.hp.com/go/toneryield>

© Copyright 2022 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

