

Tripp Lite

1111 W. 35th Street Chicago, IL 60609 USA Telephone: 773.869.1234 www.tripplite.com

USB-A to USB-C AOC Cable (M/M) - USB 3.2 Gen 2 Plenum-Rated Fiber Active Optical - Data Only, Backward Compatible, Black, 15 m

MODEL NUMBER: U428F-15M-D321











High-speed in-wall fiber cable connects a USB-C device to the USB-A port on your computer up to 15 meters away.

Features

Active Optical Cable Connects Servers, Hard Drives and Other USB-C Components

This USB 3.2 Gen 2 fiber optic cable (M/M) securely connects the USB-A port on your desktop, laptop or notebook computer to a USB-C device, such as a server, external hard drive or surveillance camera, located up to 15 meters (49 feet) away. This data-only cable supports USB 3.2 Gen 2 data transfer rates up to 10 Gbps, and is backward compatible with USB 3.2 Gen 1, 2.0 and 1.1 devices.

Advanced Fiber Cable Is Easier to Install than Copper

Because the fiber cable is slimmer and more flexible than standard copper USB cables, the U428F-15M-D321 is easier to install around corners and in hard-to-reach spaces behind equipment. It draws power from the connected device, so no external power supply is needed to transmit the USB signal across the longer distances unique to fiber optic cabling. **Note**: The cable must be installed in the correct direction to function properly, so please check the Host and Device labels on the connectors before installation.

CMP Jacket Designed for In-Wall Installations

The plenum-rated jacket has low smoke and flame characteristics, making it suitable for premise applications in ceilings, walls and ducts.

15 m Cable Lets You Design an Application to Your Custom Specifications

This long cable allows you greater flexibility in placing your USB components. For instance, your camera or hard drive may be located in a different room away from your office or in a central location where others have access to it. The plug-and-play U428F-15M-D321 supports all major operating systems, including Windows, macOS and Linux. *Note:* If your device is not detected by the source, external power is needed for the device to receive and transmit data to the source.

Specifications

OVERVIEW

Highlights

- 15 m (49 ft.) length allows flexibility in placing USB-C devices where most needed
- Fiber optic construction ideal for long-distance connections not supported by copper
- USB 3.2 Gen 2 (10 Gbps) cable is backward compatible with earlier USB generations
- Plenum rated for horizontal premise applications in air ducts and drop ceilings
- Slim, flexible cable easily installs around corners and through hard-to-reach areas

Applications

- Connect a USB-C device to the USB-A port on your PC, tablet, laptop or notebook
- Ideal for those who need longer cables with USB-C to USB-A connections

Package Includes

U428F-15M-D321 USB 3.2 Gen 2 Fiber Active Optical Cable, M/M, 15 m (49 ft.)





UPC Code	037332275066	
Technology	USB; USB 3.x	
USB Cable Type	Active	
INPUT		
Bus Powered	Yes	
POWER		
USB Power Delivery (PD) Charging Support	No	
PHYSICAL		
Material of Construction	PVC (Plenum Rated Cable) + Zinc Alloy (Connector Ends)	
Cable Jacket Color	Black	
Connector Color	Black; Light Gray	
Cable Jacket Material	PVC	
Cable Jacket Rating	CMP	
Cable Outer Diameter (OD)	4.5MM	
Cable Length (ft.)	49.2	
Cable Length (m)	15.00	
Cable Length (in.)	393.7	
Unit Dimensions (hwd / in.)	1.540 x 9.250 x 8.860	
Unit Packaging Type	Вох	
ENVIRONMENTAL		
Operating Temperature Range	32 to 122F (0 to 50C)	
Storage Temperature Range	-4 to 158F (-20 to 70C)	
Operating Humidity Range	5% TO 90% RH, Non-Condensing	
Storage Humidity Range	5% TO 90% RH, Non-Condensing	
CONNECTIONS		
Side A - Connector 1	USB A (MALE)	
Side B - Connector 1	USB C (MALE)	
Connector Plating	Gold; Nickel	
Contact Plating	Gold; Nickel	
FEATURES & SPECIFICATIONS		
Data Transfer Rate	10 Gbps	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

USB Specification	USB 3.1 Gen 2 (up to 10 Gbps); USB 3.2 Gen 2 (Up to 10 Gbps)	
Driver Required	No	
STANDARDS & COMPLIANCE		
Product Certifications	CAN/CSA C22.2; UL 444	
Product Compliance	CE (Europe); FCC (USA); REACH; RoHS; UKCA	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	3-year limited warranty	

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies