



Industrial 4-Port Gigabit Ethernet PoE++ Switch with 2 SFP Ports

IEEE 802.3bt (4PPoE) Compliant, PoE Power Budget up to 240 W, Output up to 95 W per Port, IP40-Rated Metal Housing, DIN-Rail Mount
Part No.: 508995

EAN-13: 0766623508995 | UPC: 766623508995

Hardened PoE Switch - Industrial 6-Port Gigabit PoE++ Switch with DIN Rail Mount - unmanaged 802.3bt Power over Ethernet connectivity for harsh environments

The Industrial 4-Port Gigabit Ethernet PoE++ Switch with 2 SFP Ports from Intellinet Network Solutions was designed to give you the network connections and device power you need in places that are less than calm or temperate. With a rugged IP40-rated metal case, the switch operates reliably and quietly, even in extreme temperatures that range from -20 - 75°C (-4 - 167°F). In combination with its DIN-rail mounting option and two safe, redundant DC power inputs and plenty of other safety features, this switch is ideal for IoT applications in Industry 4.0 and more.

Ultra-high 4PPoE output of 95 W per port paired with a large Power Budget and Gigabit Speeds

Featuring four auto-sensing 10/100/1000 Mbps RJ45 Gigabit Ethernet ports, this unmanaged switch offers plenty of performance for the devices in your network. Two small form-factor pluggable (SFP) GBIC module slots provide fiber connectivity for greater distances. The switch features a power budget of 240 W and can distribute a full 95 W (per the IEEE 802.3bt standard) to an RJ45 port while being downwards compatible with IEEE 802.3at/af. The output power rating up to 95 watts is enough for even very power-hungry PoE++ devices like motorized PTZ cameras, thin clients, point-of-sale systems, lighting controllers and digital signage applications.

Safe protection for your expensive network equipment

The auto-sensing technology of this PoE Switch ensures that your products are protected from power problems like short circuits (short GND), current overloads and high voltages. Port surge protection up to 6 kV and ESD protection up to 15 kV make its safety complete.

Features:

- Provides up to four PoE network devices with power and data
- Power over Ethernet with output up to 95 watts per port
- PoE power budget of 240 watts (depending on the power supply used)
- Two small form-factor pluggable (SFP) GBIC module slots
- IP40 slim-type metal housing to withstand harsh industrial conditions
- Suitable for extreme operating temperatures of -20 to 75°C (-4 to 167°F)
- Option for DIN-rail installation
- 10/100/1000 auto-sensing ports that automatically detect optimal network speeds
- Compatible with IEEE 802.3bt/at/af-compliant powered devices (PD) such as network cameras, wireless access points, VoIP phones and more
- Two redundant DC inputs (48 - 57 V) with I/O terminal block
- ESD protection up to 15 kV (air) and 8 kV (contact)
- Port surge protection up to 6 kV
- Grounding point to protect equipment from external electrical surges
- Rated for shock (IEC 60068-2-27), freefall (IEC 60068-2-32) and vibration (IEC 60068-2-6)
- 12 Gbps switch fabric
- Supports IEEE 802.3bt/at/af detection and short circuit, overload and high-voltage protection
- Auto-MDIX and NWay auto-negotiation support on all RJ45 ports
- Supports 2k MAC address entries with Auto-Learning and Auto-Aging
- Supports jumbo frames up to 9.2 kBytes
- Store and forward switching architecture
- Full/half duplex operation
- IEEE 802.3x flow control for full duplex
- LEDs for power, link/activity and PoE
- Fanless design for silent operation
- Requires additional industrial power supply (not included)
- Fully NDAA-compliant
- Three-year warranty

Specifications:

Standards

For more information on Intellinet products, consult your local dealer or visit www.intellinet-network.com.

All names of products or services mentioned herein are trademarks or registered trademarks of their respective owners. Distribution and reproduction of this document, and use and disclosure of the contents herein, are prohibited unless specifically authorized.

- IEEE 802.3 (10Base-T Ethernet)
- IEEE 802.3ab (Twisted Pair Gigabit Ethernet)
- IEEE 802.3af (Power over Ethernet 802.3at Type 1)
- IEEE 802.3at (Power over Ethernet 802.3at Type 2)
- IEEE 802.3bt (PoE++/4PPoE Power over Ethernet 802.3bt Type 4)
- IEEE 802.3i (Twisted Pair 10BASE-T Fast Ethernet)
- IEEE 802.3u (100Base-TX Fast Ethernet)
- IEEE 802.3x (Flow control for full-duplex mode)
- IEEE 802.3z (1000BASE-X Gigabit Ethernet)

General

- Media support:
 - 10Base-T Cat5e UTP/STP RJ45, 8 pin
 - 100Base-TX Cat5e UTP/STP RJ45, 8 pin
 - 1000Base-T Cat5e UTP/STP RJ45, 8 pin
- MAC address table: 2k
- Buffer memory: 2 MBytes
- Forwarding rate: 8.93 Mpps
- Backplane speed / switch fabric: 12 Gbps
- Switch architecture: store and forward
- Certifications: FCC Class B, CE, RoHS, UKCA, NDAA

PoE Pinout

- Pin 1: DC (+)
- Pin 2: DC (+)
- Pin 3: DC (-)
- Pin 4: DC (+)
- Pin 5: DC (+)
- Pin 6: DC (-)
- Pin 7: DC (-)
- Pin 8: DC (-)

LEDs

- Power
- Link/activity
- PoE

Electrical

- DC input: 48.0 - 57.0 V DC, 5-pin terminal block
- DC output: up to 95.0 W per RJ45 PoE port
- Power consumption: 240.0 W (max.)

Physical

- IP40-rated metal housing
- DIN-rail: In accordance with IEC/EN 60715 (top hat)
- Dimensions (L x W x H): 119 x 100 x 30 mm (4.69 x 3.94 x 1.19 in.)
- Net weight: 500 g (1.1 lbs.)

- Gross weight: 650 g (1.43 lbs.)
- Operating temperature: -20 - 75°C (-4 - 167°F)
- Storage temperature: -40 - 85°C (-40 - 185°F)
- Operating humidity: 5 - 90% RH, non-condensing
- Storage humidity: 5 - 95% RH, non-condensing

Package Contents

- Industrial 4-Port Gigabit Ethernet PoE++ Switch with 2 SFP Ports
- DIN-rail mount bracket
- Instructions



For more information on Intellinet products, consult your local dealer or visit www.intellinet-network.com.

All names of products or services mentioned herein are trademarks or registered trademarks of their respective owners. Distribution and reproduction of this document, and use and disclosure of the contents herein, are prohibited unless specifically authorized.

