

EXTENSION CORDS & OUTLETS

OUTDOOR VINYL EXTENSION CORDS

- Designed for industrial and contractor use
- Vinyl jacket protects against rough use, chemicals, and moisture and provides added flexibility
- Molded-on and bonded plugs and connectors resist breaking

3-CONDUCTOR SJTW, 300 V GROUNDING

Model No.	Length'	AWG	Amps	Watts	Colour	Price /Each
HEAVY-DUTY						
XC482	25	14/3	15	1875	Orange	
XC483	50	14/3	15	1875	Orange	
XC484	100	14/3	13	1625	Orange	
EXTRA HEAVY-DUTY						
XC485	25	12/3	15	1875	Yellow	
XC486	50	12/3	15	1875	Yellow	
XC487	100	12/3	15	1875	Yellow	

aurora tools®



XC485



NEMA 5-15P



NEMA 5-15R

OUTDOOR VINYL TRIPLE TAP EXTENSION CORDS

- Designed for industrial and contractor use
- Vinyl jacket protects against rough use, chemicals, and moisture
- Vinyl jacket provides added flexibility
- Molded-on and bonded plugs and connectors resist breaking

3-CONDUCTOR SJTW, 300 V GROUNDING

Model No.	Length'	AWG	Amps	Watts	Colour	Price /Each
HEAVY-DUTY						
XC488	25	14/3	15	1875	Red	
XC489	50	14/3	15	1875	Red	
XC490	100	14/3	13	1625	Red	
EXTRA HEAVY-DUTY						
XC491	25	12/3	15	1875	Red	
XC492	50	12/3	15	1875	Red	
XC493	100	12/3	15	1875	Red	

aurora tools®



XC491



NEMA 5-15P



NEMA 5-15R

OUTDOOR VINYL TRIPLE TAP EXTENSION CORDS

- Designed for use by contractors and industrial personnel
- Jacket protects against rough use, chemicals, moisture, ozone and gives added flexibility at below freezing temperatures
- Molded-on and bonded vinyl plugs and connectors resist breaking or pulling off cord
- Nickel-coated brass blades resist corrosion
- XA719, XA720, XA721 are No Overload® circuit breaker extension cords

3-CONDUCTOR SJTW, 300 V GROUNDING

Model No.	Length'	AWG	Amps	Watts	Colour	Price /Each
HEAVY-DUTY						
XA719	25	14/3	15	1875	Red	
XA720	50	14/3	15	1875	Red	
XA721	100	14/3	13	1625	Red	
EXTRA HEAVY-DUTY						
XA722	25	12/3	15	1875	Yellow	
XA723	50	12/3	15	1875	Yellow	
XA724	100	12/3	15	1875	Yellow	



XA719



NEMA 5-15P



NEMA 5-15R

GLACIER FLEX™ 3-OUTLET ENGINE BLOCK HEATER CORDS

- 3 conductors, SJTW -50°C, 300 V grounding
- Water-resistant
- Flame retardant
- Ultra flexible
- Nickel-coated brass blades resist corrosion
- Temperature range from -50°F to +140°F (-50°C up to +60°C)
- Prinelight® indicator light flashes blue and red when power is on



Model No.	Length'	AWG	Amps	Watts	Price /Each
XC730	15	16/3	13	1625	

XC730

