






THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



DETAIL A
SCALE 1: 3



SPECIFICATION:

- STANDARD:
 - UPS TOPOLOGY: DOUBLE CONVERSION
 - KVA: 1
 - BATTERY TYPE: VALVE REGULATED LEAD ACID
 - FULL-LOAD RUN TIME (MIN): 4.7 MINUTES
 - INPUT PLUG: SCHUKO CEE 7/EU1-16P AND BS1363A
 - NOMINAL INPUT VOLTAGE: 220/230/240VAC
 - INPUT PHASE: SINGLE
 - OUTPUT PHASE: SINGLE
 - NOMINAL OUTPUT VOLTAGE: 220/230/240VAC
 - OUTLET TYPE AND QTY: IEC-C13(8) SOCKET
 - DISPLAY TYPE: 2.8 INCH, 4 BUTTON
 - PARALLEL PORT SUPPORT: NO
 - INPUT BREAKER TYPE: 8A PUSH BUTTON
 - OUTPUT BREAKER TYPE: N/A
- ADDITIONAL: NONE
- ACCESSORY COMPONENTS:
 - P/N U01N12V CONTAINS AN INTELLIGENT NETWORK CARD,(INSTALLED)
 - STABILIZER BRACKET, QTY:(4),
 - INSTALLATION EARS, QTY:(2),
 - SAFETY WARNING SHEET,QTY:(1)
 - SELECTION GUIDE(POCKET GUIDE),QTY:(1)
 - DB9/DB9 RS232 1.5M COMMUNICATION CABLE, QTY:(1)
 - USB-A/USB-B 1.2M SERIAL COMMUNICATION CABLE, QTY:(1)
 - INCLUDES P/N:UVCO36 INTERNAL BATTERY CARTRIDGE, QTY (1),(INSTALLED)
 - INCLUDES P/N:URMKIT1 INSTALLATION RAIL KIT, QTY (1),(U01N12V ONLY)
 - REFER TO ASSOCIATED DRAWINGS FOR PHYSICAL DIMENSIONS AND SPECIFICATIONS
 - EPO PLUG WITH SHORTING WIRE,QTY:(1),(INSTALLED)

NOTES:

- PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSIONS ARE IN INCHES
- INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.
- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PRODUCT
- ALL PURCHASED ITEMS CONFORM TO C2-0834 PANDUIT SPECIFICATION FOR CHEMICAL SUBSTANCES TO BE CONTROLLED IN PRODUCT AND PACKAGING

IDENTIFICATION:

PART NUMBER	DESCRIPTION	SHIPPING WEIGHT (KG)
U01S12V	SMARTZONE IRUPS, 1000VA, 2U, 230V, SINGLE PHASE, DOUBLE-CONVERSION ON-LINE POWER PROTECTION	20.3
U01N12V	SMARTZONE IRUPS, 1000VA, 2U, 230V, SINGLE PHASE, DOUBLE-CONVERSION ON-LINE POWER PROTECTION WITH INTELLIGENT NETWORK CARD,RAIL KIT,INSTALLATION EARS	20.5

REV	DATE	BY	CHK	APR	DESCRIPTION	EON	U01N12V	PROJ	08/17/2021	MJD	VARIOUS	SHT 1 OF 2
00A	0817	D.L.	ZRZ	GLM/DB								

DATE	08/26/2021	BY	CJ
DATE	09/06/2021	BY	

SMARTZONE UPS
U01S12V/U01N12V
CUSTOMER DRAWING

U01S12V/U01N12V/00
U01S12V/U01N12V-DC/00A
DIMENSIONS TOLERANCES ARE IN (mm)

U01N12V-DC
N/A

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT

18900 PANDUIT DRIVE, 60487, USA
WWW.PANDUIT.COM

UNINTERRUPTIBLE POWER SYSTEMS

MODEL NUMBER: 1A1V1E
INPUT: 230 VAC | 50Hz | 4.83 A | 1 PHASE
BATTERY INPUT: 36 VDC | 50 A

OUTPUT: 230 VAC | 50Hz | 4.35 A
CAPACITY: 1 kVA-1 kW
ICC: 2 kA

PROHIBIDO SU USO EN EXTERIORES

MADE IN CHINA
HECHO CHINA






P/N: U01N12V



UPC#

6 9919 42 2333 11



DISPLAY FIRMWARE VERSION: 3040-0243
CORE FIRMWARE VERSION: V0008000000

DATE	08/26/2021	BY	CJ
DATE	09/06/2021	BY	

SMARTZONE UPS U01S12V/U01N12V				CUSTOMER DRAWING	
U01S12V/U01N12V-000				U01S12V/U01N12V-DC/00A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE IN (IN)				N/A	
00A	08/17	DJL	ZR2	GLM/DLR	U01N12V
REV	DATE	BY	CHK	APR	DESCRIPTION
	08/17/2021	MJD			THIRD ANGLE PROJECTION
					U01N12V-DC
					SHT 1 OF 2