



HSM Pure Document Shredders

Product Overview



HSM Pure document shredders for the home or the small office

Unbelievably compact. Always a top performance. For people who have to shred confidential documents at their desks.

Product features SmallOffice series:


























- Steel cutting rollers with lifetime warranty.
- Quiet operation minimises noise development in the workplace.
- Low power consumption in stand-by mode.
- Paper feed with overload protection reduces paper jams.
- The device automatically switches off if pressure is applied to the safety element.

- 1 Automatic start/stop**
The device starts automatically when fed with paper and automatically stops after shredding is complete.
- 2 Simple emptying HSM Pure 120 / 220**
To empty the waste container, the housing top can be easily removed.
- 3 Effortless emptying HSM Pure 320**
The waste container can be easily removed and emptied.



HSM Pure
SmallOffice
in operation



Model	HSM Pure 120		HSM Pure 220		HSM Pure 320	
Scope of application	Home / small office (up to 3 persons)		Home / small office (up to 3 persons)		Home / small office (up to 3 persons)	
Cutting version	Strips	Particles	Strips	Particles	Strips	Particles
Cutting size in mm / Product number	3.9 / 2310111	4 x 25 / 2313111	3.9 / 2320111	4 x 25 / 2323111	5.8 / 2331121 3.9 / 2330121	3.9 x 30 / 2333121
Security level ISO/IEC 21964 (DIN 66399) / Shredder material	P-2 / T-2 / E-2   	P-4 / T-4 / E-3 / F-1    	P-2 / T-2 / E-2   	P-4 / T-4 / E-3 / F-1    	P-2 / O-2 / T-2 / E-2     P-2 / T-2 / E-2   	P-4 / T-4 / E-3 / F-1    
Cutting capacity in sheets DIN A4 80 g/m ² (70 g/m ²)	10-12 (12-14)	5-6 (6-7)	12-14 (13-15)	6-7 (7-8)	17-19 (19-20) 13-15 (14-16)	8-9 (10-11)
Noise level in dB(A)*	55	55	55	55	55	55
Intake width in mm	225	225	225	225	230	230
Power consumption in Watts	160	160	185	185	360	360
Voltage / Frequency	230 V / 50 Hz	230 V / 50 Hz	230 V / 50 Hz	230 V / 50 Hz	230 V / 50 Hz	230 V / 50 Hz
Dimensions (W x D x H) in mm	366 x 258 x 415	366 x 258 x 415	366 x 258 x 466	366 x 258 x 466	365 x 255 x 556	365 x 255 x 556
Weight in kg	4	5	4	5	10	11
Collection volume in l	20	20	25	25	25	25

*in idle operation

All specifications are listed without guarantee. Technical and design modifications reserved.



HSM Pure document shredders for the workplace

Simple elegance. Absolute security. For professional users who shred important business documents or personal data in the office or in small working groups.

Product features Office series:










































- The powerful motor ensures a high cutting capacity and reliable continuous operation.
- Low power consumption in stand-by mode.
- Paper feed with overload protection reduces paper jams.
- Document shredders can be moved on castors.
- Effortless emptying
HSM Pure 420: removable waste container for effortless emptying.
HSM Pure 530 / 630: sturdy design with wooden cabinet and convenient emptying.

- 1 Solid steel cutting rollers**
With a lifetime warranty, can easily cope with staples and paper clips and guarantee durability.
- 2 High level of user safety**
The device automatically switches off if pressure is applied to the safety element.
- 3 Automatic start/stop**
The device starts automatically when fed with paper and automatically stops after shredding is complete.



HSM Pure
Office in operation



Model	HSM Pure 420		HSM Pure 530 DIN A3		HSM Pure 630 DIN A3	
Scope of application	Office (up to 5 persons)		Office (up to 5 persons)		Large office (up to 8 persons)	
Cutting version	Strips	Particles	Strips	Particles	Strips	Particles
Cutting size in mm / Product number	5.8 / 2341111 3.9 / 2340111	4.5 x 30 / 2343111 1.9 x 15 / 2342111	5.8 / 2351111 3.9 / 2350111	4.5 x 30 / 2353111 1.9 x 15 / 2352111	3.9 / 2360111	4.5 x 30 / 2363111 1.9 x 15 / 2362111
Security level ISO/IEC 21964 (DIN 66399) / Shredder material	P-2 / O-2 / T-2 / E-2    	P-4 / O-3 / T-4 / E-3 / F-1     	P-2 / O-2 / T-2 / E-2    	P-4 / O-3 / T-4 / E-3 / F-1     	P-2 / O-2 / T-2 / E-2    	P-4 / O-3 / T-4 / E-3 / F-1     
Shredder material	P-2 / O-2 / T-2 / E-2    	P-5 / T-5 / E-4 / F-2  	P-2 / O-2 / T-2 / E-2    	P-5 / T-5 / E-4 / F-2  		P-5 / T-5 / E-4 / F-2  
Cutting capacity in sheets DIN A4 80 g/m ² (70 g/m ²)	22-24 (25-27) 17-19 (19-21)	13-15 (14-16) 9-11 (11-13)	25-27 (28-30) 19-21 (21-23)	14-16 (16-18) 9-11 (11-13)	26-28 (29-31)	21-22 (25-27) 14-15 (17-19)
Noise level in dB(A)*	56	56	55	55	55	55
Intake width in mm	240	240	300	300	310	310
Power consumption in Watts	610	610	610	610	700	700
Voltage / Frequency	230 V / 50 Hz	230 V / 50 Hz	230 V / 50 Hz	230 V / 50 Hz	230 V / 50 Hz	230 V / 50 Hz
Dimensions (W x D x H) in mm	397 x 293 x 621	397 x 293 x 621	497 x 362 x 716	497 x 362 x 716	538 x 487 x 889	538 x 487 x 889
Weight in kg	18	21	27	30	43	48
Collection volume in l	35	35	80	80	130	130

*in idle operation

All specifications are listed without guarantee. Technical and design modifications reserved.



HSM Pure document shredders for the department

Convincingly powerful. Unbelievably economical. For multiple users who process large quantities of data media with sensitive, company or confidential information frequently and regularly and need to shred the data securely and reliably in-house.

Product features Department series:

- Solid steel cutting rollers with lifetime warranty.
- High degree of energy saving due to stand-by.
- The device automatically switches off if pressure is applied to the safety element.
- High quality wooden cabinet with door.
- Document shredders can be moved on castors.

- 1 Continuous operation**
The powerful motor ensures a reliable continuous operation.
- 2 Convenient emptying**
After opening the door, the collecting bag can be easily removed and emptied.
- 3 Anti-paper jam function**
Paper feed with overload protection reduces paper jams.



HSM Pure
Department
in operation



Model	HSM Pure 740 DIN A3		HSM Pure 830 DIN A3		HSM Pure 940 DIN A3	
Scope of application	Department (8 up to 15 persons)		Department (8 up to 15 persons)		Department (8 up to 15 persons)	
Cutting version	Strips		Particles		Strips	
Cutting size in mm / Product number	5.8 / 2371111 3.9 / 2370111	4.5 x 30 / 2373111 1.9 x 15 / 2372111	3.9 / 2380131	4.5 x 30 / 2383131 1.9 x 15 / 2382131	5.8 / 2391131	3.9 x 40 / 2393131 1.9 x 15 / 2392131
Security level ISO/IEC 21964 (DIN 66399) / Shredder material	P-2 / O-2 / T-2 / E-2 	P-4 / O-3 / T-4 / E-3 / F-1 	P-2 / O-2 / T-2 / E-2 	P-4 / O-3 / T-4 / E-3 / F-1 	P-2 / O-2 / T-2 / E-2 	P-4 / O-3 / T-4 / E-3 / F-1
Shredder material	P-2 / O-2 / T-2 / E-2 	P-5 / T-5 / E-4 / F-2 		P-5 / O-4 / T-5 / E-4 / F-2 		P-5 / O-4 / T-5 / E-4 / F-2
Cutting capacity in sheets DIN A4 80 g/m ² (70 g/m ²)	35-37 (39-41) 26-28 (29-31)	21-22 (25-27) 14-15 (16-18)	42-44 (47-49)	33-35 (39-41) 19-21 (20-22)	51-53 (65-67)	33-35 (39-41) 19-21 (20-22)
Noise level in dB(A)*	56	56	56	56	56	56
Intake width in mm	400	400	330	330	400	400
Power consumption in Watts	700	700	1920	1920	1920	1920
Voltage / Frequency	230 V / 50 Hz		230 V / 50 Hz		230 V / 50 Hz	
Dimensions (W x D x H) in mm	620 x 487 x 889	620 x 487 x 889	579 x 548 x 954	579 x 548 x 954	620 x 478 x 1005	620 x 478 x 1005
Weight in kg	48	54	67	72	70	75
Collection volume in l	145	145	150	150	165	165

*in idle operation

All specifications are listed without guarantee. Technical and design modifications reserved.

HSM Pure document shredder for the centralised destruction

Particularly easy. Uniquely practical. The strong document shredder with a 240 litre bin for demanding in-house data destruction. The robust shredder has a powerful cutting unit with a wide feed-in opening for formats up to DIN A3.



External oiler

For a consistently high cutting performance, this low maintenance document shredder has an external automatic oiler.



Removable collecting bag

After opening the door, the collecting bag can be easily removed and emptied.



Alternative waste bin



A mobile 240 litre waste bin, in accordance with DIN EN 840, can be integrated (not included in scope of supply).

Product features:

- Solid steel cutting rollers with lifetime warranty.
- Paper feed with overload protection reduces paper jams.
- Low power consumption in stand-by mode.
- The powerful motor ensures a high cutting capacity and reliable continuous operation.
- The device automatically switches off if pressure is applied to the safety element.
- Optimum stability due to glide feet.
- **Alternative waste bin:** a 240 l paper bin in accordance with DIN EN 840 can be integrated as a collecting container. This enables simple and comfortable emptying of the bin.
- Correct removal and disposal of the cut material using the particle distributor to disperse the waste material evenly.
- High quality wooden cabinet with door and steel reinforced base plate against wear when the waste bin is used.



Learn more, scan the QR-Code.

Model	HSM Pure 740 max	DIN A3
Scope of application	Central station	
Cutting version	Particles	Particles
Cutting size in mm / Product number	4.5 x 30 / 2373111X	1.9 x 15 / 2372111X
Security level ISO/IEC 21964 (DIN 66399) / Shredder material	P-4 	P-5 
Cutting capacity in sheets DIN A4 80 g/m ² (70 g/m ²)	20-22 (24-26)	14-15 (16-18)
Noise level in dB(A)*	56	56
Intake width in mm	400	400
Power consumption in Watts	700	700
Voltage / Frequency	230 V / 50 Hz	230 V / 50 Hz
Dimensions (W x D x H) in mm	670 x 784 x 1347	670 x 784 x 1347
Weight in kg	76	76
Collection volume in l	240	240

*in idle operation

HSM Pure document shredders – quality “Made in Germany”



The high quality materials and proven HSM “Made in Germany” quality guarantee you are receiving a safe and durable machine.



The cutting rollers with a lifetime warranty can easily cope with staples and paper clips and guarantee durability.

High degree of energy saving:



The stand-by feature ensures a high degree of energy saving when the shredder is not in use.

You can find the corresponding consumables at www.hsm.eu

HSM – the company

Shredding and Compressing.



Since 1971, HSM has been pursuing a clear strategy – a consistent commitment to “Made in Germany” quality. This product and service quality is the key to our success in both the office technology and environmental technology business sectors. As a specialist in products and services for data protection as well as technologies for improving logistics and recycling processes, HSM is one of the world’s leading providers in these sectors.

Contact us now! We are always glad to help.

Head office in Germany:

HSM GmbH + Co. KG · Austraße 1-9 · 88699 Frickingen / Germany
Tel. +49 7554 2100-0 · Fax +49 7554 2100-160
info@hsm.eu · www.hsm.eu

E-mail / hotline:

Gratis Hotline
DE, AT, IT, ES, BE, NL, LU
Tel. 00800 44 77 77 66

HSM Vertrieb Deutschland
deutschland@hsm.eu

HSM Vertrieb Österreich
austria@hsm.eu

HSM Vertrieb Schweiz
schweiz@hsm.eu

HSM Verkoop België, Nederland,
Luxemburg
benelux@hsm.eu

HSM Commerciale Italia
italia@hsm.eu

HSM Ventas Portugal
iberia@hsm.eu

HSM subsidiaries:

HSM Técnica de Oficina y
Medioambiente España, S.L.U.
Calle de José Echegaray, 10
28100 Alcobendas, Madrid
Spain
Tel. +34 91 103 4859
Fax +34 91 103 4858
iberia@hsm.eu
www.hsm.eu

HSM France SAS
Parc de Genève
240, Rue Ferdinand Perrier
69800 Saint-Priest
France
Tél. +33 472 210580
Fax +33 472 517481
france@hsm.eu
www.hsm.eu

HSM (UK) Ltd.
14 Attwood Road / Zone 1
Burntwood Business Park
Burntwood · Staffordshire
WS7 3GJ
United Kingdom
Tel. +44 1543 272-480
Fax +44 1543 272-080
sales.uk@hsm.eu
www.hsm.eu

HSM Polska Sp. z o.o.
ul. Emaliowa 28
02-295 Warsaw
Poland
Tel. +48 22 862-2369
Fax +48 22 862-2368
handlowy@hsm.eu
www.hsm.eu

HSM of America LLC
419 Boot Road
Downingtown, PA 19335
USA
Tel. +1 800 613 2110
Fax +1 484 698 7978
customerservice@hsm.us
info@hsm.us
www.hsm.us

HSM China Ltd.
Room 504, Building C
Hangcheng Guangchang
Nanfaxin Town
Shunyi District
Beijing, PRC, 101300
China
Tel. +86 10 61429168
Fax +86 10 61429169
info@hsm-china.cn
www.hsm-china.cn

Your local HSM distributor: