

OVERVIEW



1. Joystick	8. DP out
2. Source Key	9. Ethernet (RJ-45)
3. Kensington Security Slot	10. USB 3.2 Gen 1
4. Power Connector	11. USB 3.2 Gen 1
5. HDMI 2.1	12. Audio-combo (3.5mm, In/Out)
6. DP 1.4	13. USB 3.2 Gen 1
7. USB-C 3.2 Gen 1 (90W)	14. USB 3.2 Gen 1

PERFORMANCE

Panel

Panel

3-side Borderless In-Plane Switching

Display Size

27 inches

Max View Area

WxH: 596.7 x 335.6 mm (23.5 x 13.2 inches)

Resolution

2560 x 1440

Aspect Ratio

16:9

Pixel Pitch

0.233 x 0.233 mm

Dot / Pixel Per Inch

109 dpi

Brightness

300 nits

Contrast Ratio

- Contrast Ratio: 1000:1
- Dynamic Contrast Ratio: 3M:1

View Angle (H / V)

Horizontal: 178°, Vertical: 178°

Response Time

- Extreme Mode: 4 ms
- Normal Mode: 6 ms

Refresh Rate

75 Hz (HDMI® only)

Color Gamut

99% sRGB

Color Support

16.7 Million

Color Depth

8-bit

Anti-glare

Support

Operating System

Operating System

- Windows® 10 Support
- Windows 11 Support

Multi-Media

Camera

2592 x 1944, 5.0-megapixel, IR + RGB camera

Microphone

Integrated microphone

Speakers

Integrated Speakers, 2x 5W

Power Supply

Power Consumption

- Typical / Max: 30W / 168.5W
- Sleep / Off mode: <0.5W
- Switch-off Mode: <0.3W
- Energy Star Power On: 21.1W
- Energy Star TEC: 69.5kWh
- Internal Power Supply

Voltage Required

AC 100 to 240 V (50-60Hz)

Special Features

Special Features

Smart Power

The Smart Power function intelligently detects overall power consumption and dynamically manages the power delivery to each device

DESIGN

Mechanical

Bezel Width

- Side: 8.6mm
- Top / Bottom: 8.5mm / 43.4mm

Video Cables

1x USB-C® to USB-C Cable (1.8m)

Cable Management

Support

Case Color

Raven black

Dimensions (WxDxH)

Models	Dimensions
Highest Position	613.8 x 199.7 x 584.5 mm (24.17 x 7.86 x 23.01 inches)
Lowest Position	613.8 x 199.7 x 429.5mm (24.17 x 7.86 x 16.91 inches)
Head Only	613.8 x 53.9 x 404.7mm (24.17 x 2.12 x 15.93inches)

Packaging Dimensions (WxDxH)

720 x 160 x 510 mm (28.35 x 6.30 x 20.08 inches)

Weight

Models	Weight
Monitor With Stand	7.9 kg (17.4 lbs)
Monitor Head Only	5.7 kg (12.7 lbs)

Packaging Weight

10.9 kg (24.03 lbs)

Mounting

Supports VESA mount 100mm

Stand

Supports -5° to +23.5° tilt, left & right 45 swivel, 90° pivot, up to 155mm lift

In the Box

- Monitor with Stand
- 1x Power cable (1.8m)
- 1x USB-C to USB-C Cable (1.8m)
- Quick Setup Guide

CONNECTIVITY

Ports

Rear Ports^[1]

- 1x HDMI 2.1
- 1x DisplayPort™ 1.4
- 1x DisplayPort out
- 1x USB-C 3.2 Gen 1 (DP alt mode, up to 90W), USB upstream
- 4x USB 3.2 Gen 1, USB downstream
- 1x Ethernet (RJ-45)
- 1x audio-combo (3.5mm, In/Out)
- 1x Power Connector

Notes:

1. Up to 90W power delivery to compatible devices by USB-C. Listed as maximum capacity of power delivery. Actual capacity of power delivery may vary depending upon devices connected or monitor configuration, and may decline with downstream USB ports connected or higher brightness setting.

SECURITY & PRIVACY

Security

Physical Locks

Kensington® Security Slot™

SERVICE

Warranty

Base Warranty

3-year courier or carry-in service

CERTIFICATIONS

Green Certifications

Green Certifications

- EPEAT™ Gold
- ENERGY STAR® Certified
- TCO Certified 9.0
- TCO edge 2.0
- RoHS compliant

Other Certifications

Other Certifications

- Eyesafe® Display 2.0
- TÜV Rheinland® Flicker Free
- TÜV Rheinland Eye Comfort Certification
- TÜV Rheinland Low Blue Light (Hardware Solution)

- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION “AS IS,” WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.

- The specifications on this page may not be available in all regions, and may be changed or updated without



