

TOSHIBA

Keep Storage Simple.

Canvio Basics Portable Hard Drive

Storing your photos, videos, and data has never been easier. Toshiba's Canvio Basics portable hard drive offers up to 4TB¹ of storage space in a sleek compact casing for increased portability. Simply plug it in to start saving and accessing your files. That's storage made simple.



TOSHIBA

Canvio Basics Portable Hard Drive



Keeping data storage simple, the Canvio Basics lets you collect and store your favorites with its portability and lightning fast transfer speeds. With USB 3.0 you'll be able to transfer files on the go while powering the drive through your laptop's USB connection.



Simple Add-On Storage



Drag & Drop to Save Files



Sleek, Matte Black
Design



Up to 4TB Storage¹



Easy Access to
Your Content



USB Plug & Play



1 Year Limited Warranty³

Canvio Basics Portable Hard Drive

Contents

- Toshiba Canvio Basics Portable Hard Drive
- USB 3.0 Cable (works with USB 2.0)
- Quick Start Guide
- 1-year standard limited warranty³

System Requirements⁴

- Formatted NTFS for Microsoft® Windows® 11, Windows® 10, Windows® 8.1
- Requires reformatting for macOS v12.0, v11.5, v10.15
- Available USB 2.0 or USB 3.0 Port

Specifications

- Capacity¹: up to 4TB
- Interface: USB 3.0, USB 2.0
- Interface Transfer Rate²:
 - Up to 5 Gbit/s (USB 3.0)
 - Up to 480 Mbit/s (USB 2.0)
- Size (mm):
 - 1TB/2TB
78(W) x 109(L) x 14(H) mm
 - 4TB
78(W) x 109(L) x 19.5(H) mm
- Color: Black
- Weight (g):
 - 1TB/2TB: 149g
 - 4TB: 217.5g



Part Number	Capacity ¹	Color	UPC
HDTB510XK3AA	1TB	Black	723844001339
HDTB520XK3AA	2TB	Black	723844001346
HDTB540XK3CA	4TB	Black	723844001353

To see our full line of consumer HDD storage products, visit: storage.toshiba.com/consumer-hdd

¹ One Gigabyte (1GB) means $10^3 = 1,000,000,000$ bytes and One Terabyte (1TB) means $10^{12} = 1,000,000,000,000$ bytes using powers of 10. A computer operating system, however, reports storage capacity using powers of 2 for the definition of $1GB = 2^{30} = 1,073,741,824$ bytes and $1TB = 2^{40} = 1,099,511,627,776$ bytes, and therefore shows less storage capacity. Available storage capacity (including examples of various media files) will vary based on file size, formatting, settings, software and operating system and other factors. Actual formatted capacity may vary.

² Five (5) Gbit/s is the maximum interface transfer rate per the specifications of the Universal Serial Bus 3.0. Actual transfer rate will vary depending on your system configuration and other factors.

³ One (1) year standard limited warranty applies. The warranty brochure is preloaded on the hard drive or can be viewed online at: <http://storage.toshiba.com/consumer-hdd/support/warranty-info>.

⁴ Compatibility may vary depending on user's hardware configuration and operating system. Reformatting required for use with Mac® or other operating systems.

⁵ Read and write speed may vary depending on the host device, read and write conditions, and file size.

Product prices, specifications, configurations, colors, components, features, and availability are subject to change without notice.

Microsoft and Windows are trademarks of the Microsoft group of companies in the United States and other countries.

Mac and macOS are trademarks of Apple Inc., registered in the U.S. and other countries and regions.

Canvio and the Canvio logo are either trademarks or registered trademarks of Toshiba Electronic Devices & Storage Corporation in the United States and other countries.

© 2023 Toshiba America Electronic Components, Inc. All rights reserved.