

The USB-C® Hybrid Triple 4K Display Docking Station with DisplayLink and DP Alt Mode transforms USB-C enabled laptops into total desktop solutions through connection – allowing them to have more video outputs, more connected peripherals, and quick data transfers, all while keeping the laptop charged and ready to go.

This docking station supports crisp, high definition images and video when connecting one, two, or three 4K displays. When connecting to the HDMI port labeled "DP Alt Mode", be sure that the connected laptop supports DP alt mode. The front USB-A and USB-C 3.2 Gen 2 ports support BC 1.2 for quick mobile device charging and data transfer up to 10Gbps, while the two USB-A Gen 1 ports on the rear support 5Gbps data transfers. The Ethernet port allows for reliable internet connectivity with file transfer speeds up to 1000Mbps.

The included 130W power supply keeps the connected laptop charged and ready to go with 100W power delivery while supporting connected devices, such as key portable hard drives, and other peripherals. The maximum power capacity depends on how much power the connected adapter can supply. The right amount of power is needed to keep the laptop battery charged, for all connected devices to function, and for the dock to provide that connectivity. Laptops or tablets that require more than 100W will operate at lower speeds.

The USB-C Hybrid Triple 4K Display Docking Station maximizes desktop space while providing a single cable solution for Windows, Mac OS devices (including M1 and M2) and Chrome OS. Download and install the latest DisplayLink drivers at [www.displaylink.com/downloads](http://www.displaylink.com/downloads).

**Note:** The latest DisplayLink drivers must be downloaded to support the first and second connected displays. To use the HDMI port labeled "DP Alt Mode", the connected laptop must support DP alt mode.

#### MAXIMUM SUPPORTED RESOLUTIONS

**3 Displays:** 4K (3840 × 2160) at 30Hz

**2 Displays:** 4K (3840 × 2160) at 60Hz

**1 Display:** 4K (3840 × 2160) at 60Hz (DP Alt Mode HDMI port supports 4K 30Hz)

**Note:** HDMI output labeled "DP Alt Mode" to be used with DP alt mode laptops

#### PORTS

**2x HDMI [DisplayLink] Ports:** Connect to HDMI port 1 or port 2 for a single 4K display or dual 4K displays, supporting audio and video.

**2x DisplayPort [DisplayLink] Ports:** Connect to DisplayPort port 1 or port 2 for a single 4K display or dual 4K displays, supporting audio and video.

**1x HDMI [DP Alt Mode] Port:** Connect to the HDMI port labeled "DP Alt Mode" when using a triple display setup with a connected laptop that supports DP alt mode.

**3x USB-C:** The left side USB-C port delivers up to 100W of power to the connected laptop, the front battery labeled USB-C Gen 2 port supports 10Gbps and BC 1.2 device charging, and the front USB-C Gen 1 port supports data transferring up to 5Gbps.

**3x USB-A:** Connect storage devices and transfer data up to 5Gbps through the two rear USB-A Gen 1 ports, with the front USB-A Gen 2 port supporting 10Gbps and mobile device charging.

**Gigabit Ethernet:** Connect to a local network for network and internet access.

**Audio Combo Jack:** Connect a headset microphone or speakers for audio output.

**Note:** Only a single video output is supported with the original M1 MacBook. Newer Apple devices (M1 Max and M1 Pro, etc.) are not impacted and support dual video outputs.

#### ADDITIONAL TECHNICAL SPECS

##### Electrical Specifications

- Power Adapter: Electrical: Input AC: 100-240V; Input Dock: 24V, 4A
- Power Consumption: 130W
- USB-C Power Delivery: 100W

##### Physical Specifications

- Operating Temperature: 0°C to +70°C
- Storage Temperature: -10°C to +55°C; 0 to 85% RH (Non-Condensing)

##### Physical Characteristics

- Cables: Color: Black
- Docking Station: Dimensions: 7.52in (191mm) x 1.25in (31.8mm) x 3.35in (85mm) LxHxD
- Material: Housing: Plastic (ABS+PC), black, covered by soft silicone sheet
- Product Certifications: RoHS, REACH, Prop65, CE, FCC

##### Package Contents

- 1 x USB-C Hybrid Triple Display Docking Station
- 1 x 1.5ft (0.5m) Male USB-C to Male USB-C Cable
- 1 x 1.5ft (0.5m) Male USB-C to Male USB-A Cable
- 1 x 130W Power Supply with US, EU, & UK Plugs
- 1 x Manual

## Features & Benefits

Supports single 4K 60Hz, dual 4K 60Hz, or triple 4K 30Hz video output, for viewing Ultra HD content

Battery labeled front USB-A and USB-C ports support BC 1.2 for enhanced mobile charging and quick data transferring up to 10Gbps

Hard wired Ethernet port for when security requires it or when WiFi™ is not available 130W power supply to support connected displays and devices

Supports up to 100W of power delivery to keep your laptop charged

Reversible, symmetrical USB-C connector, so no guessing how to plug it into your laptop

Compatible with Windows and Mac operating systems

5 year warranty, for peace of mind – with the highest quality docking stations

## Specifications

### General Info

Product Line	C2G	Color	Black
UPC Number	757120545385	Country Of Origin	China
Features	Triple Display, USB-A Charging, USB-C Charging	Application Sector	Commercial, Residential
Warranty Type	5-Year	Type	Docking Station

### Dimensions

Product Depth US	3.35 in	Product Height US	1.25 in
Product Length US	7.52 in		

### Listing Agencies / 3rd Party Agencies

CE Certified	Yes
--------------	-----

### Technical Information

Operating Temperature Min	0 °C	Video Resolution	4K, 4K 30Hz, 4K 60Hz
Storage Humidity	85% RH (Non-Condensing)	USB Wattage	100 W
Operating Temperature Max	50 °C	Technology Specifications	USB 2.0, USB 3.0
Data Transfer Rate	10 Gbps	Connector Type	3.5mm Audio Jack, DisplayPort, HDMI, RJ-45, USB-A, USB-C
Connector 2	3.5mm Female, DisplayPort Female, HDMI Female, RJ-45 Female, USB-A Female, USB-C Female	Connector 1	USB-C Male
Video Output Support	USB-C	Power Delivery	100 W
Operating Temperature	0°-50°C, 32°-122°F	Operating Humidity	10-90% RH (Non-Condensing)
Video Input Support	DisplayPort, HDMI	Operating System	Chrome OS, macOS, Microsoft Windows
Storage Temperature	-13° - 158° F, -25° - 70° C		