

Elo M60 Pay

Mobile POS Computer





6" HD Display



Dip. Swipe. Tap.



Android 10

Product Overview

Designed to support your everyday business, the Elo M60 Pay delivers an enterprise-grade, Android mobile POS computer ready to help you assist customers. This all-in-one device offers built-in capabilities to accept payments, conduct business, and track sales all from the palm of your hand. Complete with a 6-inch HD touch display, integrated payment, flexible Android 10 OS and Qualcomm 660 octa-core processor, the M60 Pay handheld computer provides seamless integration, effortless provisioning and simplified device management via EloView® or your preferred 3rd-party MDM.

With rugged Corning Gorilla Glass technology to provide protection against unintentional spills, the M60 Pay is purpose-built to endure commercial use. From table service and line busting to curbside pickup and accepting payment almost anywhere, Elo's M60 Pay allows your employees to be ready on the go.

Fully integrated payment via NFC, EMV and MSR (BCR on select models)

Secure - PCI-PTS 6.x Certified

Optional accessories including docking station, multi-unit device charger, handstrap and more

Seamless Provisioning with EloView, Google Zero Touch or GMS

M60 Pay Mobile Computer

Specifications					
Display	6" Optically Bonded High Definition LCD				
Touchscreen	Projective capacitive with Corning Gorilla Glass, Water rejection, Anti-Fingerprint Coating				
Operating System	Android 10 with Google™ Play Services (AOSP capable); Planned upgrade to Android 12 available with OS 360 subscription				
Processor	Qualcomm Snapdragon 660 2.2GHz Octa-Core Processor				
Memory	3GB				
Storage	32GB				
Expansion Card Slot	MicroSD up to 32GB SDHC and up to 256 GB SDXC; Option to support 1x nano-SAM card via a Micro SD slot.				
I/O Ports	USB Type-C for display, charging and data				
Wireless	802.11a/b/g/n/ac with 2x2 MU-MIMO, Bluetooth 5.0				
Cellular	Available on cellular SKU's with user accessible nano SIM slot. LTE US and Canada Carriers: AT&T, T-Mobile, TELUS; LTE Europe: Open Carrier For E862945 (M60C), E898054 (M60SC): WCDMA: B2, B4, B5; LTE: B2, B4, B12, B13, B66 For E993295 (M60C), E897852 (M60SC): WCDMA: B1, B8; LTE: B1, B3, B7, B8, B20				
GPS	Simultaneous GNSS Receiver for GPS, GLONASS, Galileo and BeiDou; AGPS support				
LED	1x combination Green/Amber LED for battery/charging status, 1x combination Blue/Red user programmable LED				
Keyboard	On screen keyboard				
Audio	Microphone; 1W Front facing speaker; USB-C headset support				
Buttons	Left and Right Programmable Buttons; Left and Right BCR trigger buttons (M60S/M60SC models only); Power Button				
Payment Card Readers	EMV Contactless ISO 14443-A/B, MiFare, ISO-18092; EMV Chip Card Rader (chip and pin-on-glass); 3-track MSR ISO 7810/7811				
Barcode Scanner	SE4720 scan engine with 1D/2D Imager (M60S/M60SC models only)				
Certification	PCI-PTS 6.x, EMV L1 & L2, Visa PayWave, Mastercard PayPass, Amex ExpressPay, Discover D-PAS, Mastercard TQM, Apple Pay™, Google Pay™, Samsung Pay™				
Camera	8MP Auto-Focus with Flash LED and Flashlight (Torch)				
Sensors	Light sensor (automatically adjust backlight brightness); Proximity sensor (disable display and touch when user places against head); Accelerometer				
Contrast Ratio	1500:1				
Native (optimal) Resolution	1440 x 720				
Brightness	430 nits				
Battery	Rechargeable Li-Polymer, 3.8V/4000mAh, Serviceable Battery, Qualcomm Quick Charge 4				
Dimensions	M60/M60C: 7.32" x 3.40" x 0.77" / 186 mm x 86.4 mm x 19.5 mm M60S/M60SC: 7.32" x 3.40" x 1.27" / 186 mm x 86.4 mm x 32.3 mm				
Weight	M60: 0.79 lbs / 362 g; M60C: 0.82 lbs / 370 g; M60S: 0.87 lbs / 396 g; M60SC: 0.89 lbs / 403 g				
Drop Specification	Multiple 1m drops				
Tumble Specification	200 tumbles, 1.6ft./0.5m per IEC 60068-2-32				
Sealing	IP54 per IEC standard 60529				
Temperature	Operating: 32°F to 122°F (0°C to 50°C); Storage: -22°F to 140°F (-30°C to 60°C)				
Humidity	5% to 95% non-condensing				
Regulatory Approvals and Declarations	UL, FCC (US) - Class B, cUL, IC (Canada), CB (International Safety), CE (Europe) - Class B, RCM (Australia), China RoHS				
ESD	Class A: 8kV contact, 15kV air				
Warranty	1-year				
3 year + ADP - Elo P/N: E672040 , 5 year + ADP - Elo P/N: E672239 1 year + AUR + ADP - Elo P/N: E894512, 3 year + AUR + ADP - Elo P/N: E672440, 5 year + AUR + ADP - Elo P/N: E672646 Extended Warranty 3 year + ADP + OS 360 - Elo P/N: E893726, 4 year + ADP + OS 360 - Elo P/N: E150782 3 year + AUR + ADP + OS 360 - Elo P/N: E894122, 4 year + AUR + ADP + OS 360 - Elo P/N: E150971 3 year OS 360 - Elo P/N: E873133, 4 year OS 360 - Elo P/N: E565885					
Security Updates	Monthly Android security updates available with Elo OS 360 package.				
What's in the box	Elo M60 Pay, USB Type-C Charger, Quick Install Guide				

Ordering Information

Model	Part Number	os	Cellular/WiFi	Integrated Peripherals	Availability
M60	E863128	Android 10 (GMS)	WiFi	EMV, NFC, MSR	Worldwide
M60C	E862945	Android 10 (GMS)	Cellular (AT&T, T-Mobile, TELUS)	EMV, NFC, MSR	United States, Canada
M60C	E993295	Android 10 (GMS)	Cellular (Open Carrier)	EMV, NFC, MSR	Europe
M60S	E897667	Android 10 (GMS)	WiFi	EMV, NFC, MSR, Barcode Scanner	Worldwide
M60SC	E898054	Android 10 (GMS)	Cellular (AT&T, T-Mobile, TELUS)	EMV, NFC, MSR, Barcode Scanner	United States, Canada
M60SC	E897852	Android 10 (GMS)	Cellular (Open Carrier)	EMV, NFC, MSR, Barcode Scanner	Europe

Learn more about Elo at **EloTouch.com**.

Americas Europe (EMEA)

Tel +1 408 597 8000 Tel +32 (0)16 70 45 00 elosales.na@elotouch.com EMEA.Sales@elotouch.com

Asia Pacific

Tel +86 (21) 3329 1385 www.elotouch.com.cn

Elo reserves the right to change or update, without notice, any information contained herein; to change, without notice, the design, construction, materials, processing or specifications of any products; and to discontinue or limit production or distribution of any products. Elo, the Elo logo, EloCare and EloView are either trademarks or registered trademarks of Elo Touch Solutions, Inc. Android is a trademark of Google LLC. Google Play and the Google Play logo are trademarks of Google LLC. All other trademarks are the property of their respective owners. © 2023 Elo Touch Solutions, Inc. All rights reserved. 23111AES00154

