

Lenovo ThinkPad P14s *i* Gen 4 Lenovo's Lightest Mobile Workstation



The Lenovo ThinkPad P14s *i*, our thinnest and lightest mobile workstation, combines the latest Intel vPro[®] with 13th Gen Intel[®] Core[™] processors and NVIDIA[®] professional graphics, all in a 14-inch chassis. Perfect for highly-mobile power users, the P14s *i* strikes the balance between power and mobility-allowing students, architects, and engineers to be creative anytime, anywhere.

Processor: 5.2GHz 14 Cores Intel vPro with 13th Gen Intel Core i5, i7



Memory: 64GB LPDDR5X 4800MHz¹ with Discrete Graphics Storage: 2TB M.2 PCIE Gen4 One NMVe SSD up to 2TB

Features



Modern Design Built with sustainable materials and certifications and a choice of Thunder Black or Storm Grey chassis



14" 16:10 Display Six high quality options to suit your budget



Security

The latest security features including dTPM 2.0, an embedded chip dedicated to storing encryption keys



ISV Certifications Certified by many of the leading industry software applications

Lenovo ThinkPad P14s *i* Gen 4 Product Specifications

Performance

Processor

Intel vPro[®] with 13th Gen Intel[®] Core[™] i5, i7 (up to 14 cores, up to 5.2GHz)

Graphics

Discrete: up to NVIDIA RTX[™] A500 4GB GDDR6 VRAM

Processor Integrated: Intel Iris Xe²

Total Memory

Up to 64GB LPDDR5x 4800MHz¹ (Discrete Graphics)

Up to 48GB DDR5 5200MHz¹ (Integrated Graphics)

Memory DIMM Capacity

Integrated Graphics:

SDRAM: 16GB DDR5 5200MHz¹ SoDIMM: 8GB / 16GB / 32GB DDR5 5200MHz1 (1 Soldered Down, 1 SoDIMM Slot)

Discrete:

SDRAM Only: 16GB / 32GB / 64GB LPDDR5x 4800MHz¹ (2 Soldered Down)

Total Storage

Up to 2TB NVMe PCIe Gen4 SSD 1 Drive

Camera

HD RGB Camera with ThinkPad Webcam Privacy Shutter

5MP+IR³ with ThinkPad Webcam **Privacy Shutter**

FHD Hybrid IR Camera³ with ThinkPad Webcam Privacy Shutter

Battery 39.3WHr, 52.5WHr

Power Supply

65W, 100W AC Adapter Type-C

Design **Dimensions (WxDxH)**

(mm): 317.7 x 226.9 x 17.9 (inches): 12.51 x 8.93 x 0.7

Weight Starting at 1.34kg / 2.97lbs

1 Memory spec frequency listed; system support frequency

may vary by configuration 2 Dual RAM channel required

- 3 Optional
- 4 Bluetooth 5.2 is hardware ready but may run at a lower version due to OS limitation
- 5 6GHz channel of Wi-Fi 6E is only available
 - with Windows 11



Display

14" 16:10 Display

2.8K OLED (2880 x 1800)

- IPS 400nit, 100% DCI P3, X-Rite FCC, AGAR, LBL, Eyesafe

FHD+ (2240 x 1400)

- IPS, 300nit, 100% sRGB, AG, LBL

WUXGA (FHD+) (1920 x 1200)

- IPS, Touch, 500nit, Privacy Guard, LCLW, 72% CG, AG
- IPS, 400nit, 100% sRGB, 100% sRGB, ICC Template Color Calibration, LBL, AG, Evesafe
- IPS, Touch, 300nit, LCLW, 45% CG, AG
- IPS, 300nit, 45% CG, AG

Connectivity

Ports

(2) USB-A 3.2 Gen 1 (5Gbps)*, 1 Always On

- (2) USB-C[®] Thunderbolt 4
- (1) HDMI 2.0b
- (1) Mic/Headphone Combo Jack
- (1) RJ-45 Gigabit Ethernet

Smart Card Reader³

WLAN

Intel Wi-Fi 6E AX211 (2x2ax) + Bluetooth[™] 5.2 vPro^{4,5}

WWAN

FIBOCOM L860-R 4G_LTE CAT16 with eSIM²

Quectel CAT4 EM05 with eSIM³ Near Field Communication (NFC)³

Kevboard

ThinkPad Backlit or non-Backlit

Color Options

Thunder Black or Storm Grey

- For a full list of configuration details please visit: https://psref.lenovo.com
- USB port transfer speeds are approximate and depend on many factors, such as processing capability of host/ peripheral devices, file attributes, system configuration and operating environments; actual speeds will vary and may be less than expected.



Lenovo Options & Accessories



ThinkVision P27h-30 Display



ThinkPad Workstation Thunderbolt[™] 4 Dock



ThinkPad 14-inch Professional Slim Topload

For a full list of accessories and options, please visit: accsmartfind.lenovo.com

For more details on ThinkStation and ThinkPad, please visit: lenovo.com/workstations

Visit us on social media: #lenovoworkstations



May 2023 ©Lenovo. All rights reserved. Lenovo is not responsible for photographic or typographic errors. Lenovo makes no representation or warranty regarding third-party products or services. LENOVO, ThinkStation, and ThinkPad are trademarks of Lenovo

Lenovo ThinkPad P14s *i* Gen 4 General Specifications

Software

Operating System

Windows 11 Pro Windows 11 Home

Windows 10 Pro (preinstalled Through downgrade rights in Windows 11 Pro)

Ubuntu® Linux®1

Red Hat[®] Enterprise Linux[®] (certified)

Windows Preloads

Lenovo Commercial Vantage

Additional Features

Ultra Performance Mode

Self Healing BIOS

ISV Certifications

Including AutoCAD®, CATIA®, Creo®, Inventor[®], Microstation[®], NX[®], Solid Edge®, SOLIDWORKS®, Vectorworks®

For a complete list of ISV certifications visit https://thinkworkstations.com/

Security

ThinkShield dTPM 2.0 Touch Fingerprint Reader ThinkPad Webcam Privacy Shutter Kensington Lock Slot

Sustainability

Materials

50% Recycled Aluminum A Cover 90% Recycled Magnesium C Cover 55% Recycled Aluminum D Cover 90% PCC Plastic Speaker Enclosure 90% PCC Plastic Battery Pack Enclosure 90% PCC Plastic Slim 65W AC Adapter 90% PCC Plastic Standard 65W AC Adapter 30% PCC Plastic 100W AC Adapter² Low Temperature Solder³ Plastic free packaging with 90% recycled and/or FSC certified content (standard)⁴

Certifications

FPFAT®5 Gold ENERGY STAR^{®6} **RoHS** Compliant TCO 9.0

Recommended Services

Lenovo offers a comprehensive portfolio of services to support and protect your ThinkPad investmentso you can focus on your business, not your IT.

Premier Support

1 Select versions available via preload

2 90% PCC Plastic coming soon

ClickPad

intel

Bypass phone menus and scripted troubleshooting to access advancedlevel technicians with the expertise needed to quickly diagnose and solve problems.

3 Motherboard, memory, SSD, fingerprint reader module,

4 Product packaging shall contain, on average, a minimum total percentage of 90% by weight of any combination of

the following materials: Recycled content, biobased plastic, non-wood biobased fiber material, and/or sustainably

Warranty Extensions (1 to 5 years total duration)

This fixed-term, fixed-cost service helps you accurately budget for PC expenses, protect your valuable investment, and potentially lower the cost of ownership over time.

Warranty Upgrades— Onsite and Next Business Day

Maximizes PC uptime and productivity by providing convenient, fast repair service the next business day.

5 Certification available on select models

- 6 Certification available on select models; EPEAT registered where applicable. EPEAT registration varies by country. See www.epeat.net for registration status by country
- For a full list of configuration details please visit: https://psref.lenovo.com

PR(

forested material

NVIDIA is a trademark and/or registered trademark of NVIDIA Corporation in the U.S. and other countries. Intel, Intel vPro, Core, Iris, and Thunderbolt are trademarks of Intel Corporation or its subsidiaries. Linux is the registered trademark of Linus Torvalds in the U.S. and other countries. Ubuntu is a registered trademark of Canonical Ltd. Microsoft and Windows are registered trademarks of Microsoft Corporation. Other company, product, and service names may be trademarks or service marks of others

