



HP EliteBook 630 13.3 inch G10 Notebook PC Wolf Pro Security Edition (7Z1M4UT)



Overview

Empowering the hybrid workforce

Simplify hybrid work with the cost-effective, highly secure, and easy to manage HP EliteBook 630. With the latest Intel® processor[2], this PC easily adapts for use at home, in the office, or when traveling.

Latest Intel® processor

Drive performance with the latest Intel® [2] processor, on this globally available and easy-to-service laptop.

Crystal-clear speakers

Enjoy the crystal-clear audio performance delivered by HP Dynamic Audio[4] and HP AI Noise Reduction.[4]

Protected by HP Wolf Security

HP Wolf Pro Security Edition PCs interlace HP Sure Click Pro with HP Sure Sense Pro providing more in-depth coverage than the standard versions through a 1-year or 3-year user license with HP Support.[3] This creates a powerful, single solution that doesn't require an IT-managed PC environment.

Help protect our shared future

This PC contains at least 50-percent post-consumer recycled plastic in the keycaps.[5]

Features

Windows 11

Work anywhere without compromising on performance or security with Windows 11 powered by HP's collaboration and connectivity technology.

Security is your top priority

The HP Wolf Pro Security Edition provides preconfigured enterprise-level PC protection for small and medium sized businesses.^[1]

Designed for where life takes you

Express yourself in almost any light using the ultra-bright outdoor viewable touch display with anti-glare and ambient light sensors.

Fast and efficient wireless LAN

The portability of your PC and the reliability of a fast connection determines where you can work. Get a fast and reliable connection in dense wireless environments with gigabit-speed Wi-Fi 6.^[6]

Automatic recovery from firmware attacks

Firmware attacks can completely devastate your PC. Stay protected with HP's self-healing BIOS - HP Sure Start Gen7 automatically recovers the BIOS from malware, rootkits, or corruption.

Keep your PC's security protections in place

Stop unwanted changes to security settings and help limit the spread of malware with HP Sure Run Gen5 which identifies, quarantines, and provides reporting on attackers trying to kill processes.

[2] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. AMD's numbering is not a measurement of clock speed.

[3] HP Wolf Pro Security Edition (including HP Sure Click Pro and HP Sure Sense Pro) is available preloaded on select SKUs and, depending on the HP product purchased, includes a paid 1-year or 3-year license. The HP Wolf Pro Security Edition software is licensed under the license terms of the HP Wolf Security Software - End-User license Agreement (EULA) that can be found at: https://support.hp.com/us-en/document/ish_3875769-3873014-16 as that EULA is modified by the following: "7. Term. Unless otherwise terminated earlier pursuant to the terms contained in this EULA, the license for the HP Wolf Pro Security Edition (HP Sure Sense Pro and HP Sure Click Pro) is effective upon activation and will continue for either a twelve (12) month or thirty-six (36) month license term ("Initial Term"). At the end of the Initial Term you may either (a) purchase a renewal license for the HP Wolf Pro Security Edition from HP.com, HP Sales or an HP Channel Partner, or (b) continue using the standard versions of HP Sure Click and HP Sure Sense at no additional cost with no future software updates or HP Support."

[4] Requires the myHP application and Windows OS.

[5] Recycled plastic content percentage is based on the definition set in the IEEE 1680.1-2018 standard.

[1] This product includes a one (1) year license of HP Wolf Pro Security Edition which includes HP Sure Click Pro and HP Sure Sense Pro. The HP Wolf Pro Security Edition software is licensed under the license terms of the HP End User License Agreement (EULA) that can be found at: https://support.hp.com/us-en/document/ish_3875769-3873014-16 as modified by the following: "7. Term. Unless otherwise terminated earlier pursuant to the terms contained in this EULA, the license for the HP Wolf Pro Security Edition (HP Sure Sense Pro and HP Sure Click Pro) is effective upon activation and will continue for twelve (12) months thereafter ("Initial Term"). At the end of the Initial Term you may either (a) purchase a renewal license for the HP Wolf Pro Security Edition from HP.com, HP Sales or an HP Channel Partner, or (b) continue using the

standard versions of HP Sure Click and HP Sure Sense at no additional cost with no future software updates or HP Support.”

[6] Wireless access point and internet service required and sold separately. Availability of public wireless access points limited. Wi-Fi 6 is backwards compatible with prior 802.11 specs. The specifications for Wi-Fi 6 (802.11ax) are draft and are not final. If the final specifications differ from the draft specifications, it may affect the ability of the PC to communicate with other 802.11ax devices. Wi-Fi® supporting gigabit speeds is achievable with Wi-Fi 6 (802.11ax) when transferring files between two devices connected to the same router. Requires a wireless router, sold separately, that supports 160MHz channels.

Specifications

Operating system	Windows 11 Pro ^[1]
Product color	Pike silver aluminum
Processor family	13th Generation Intel® Core™ i7 processor
Processor	Intel® Core™ i7-1355U (up to 5.0 GHz with Intel® Turbo Boost Technology, 12 MB L3 cache, 10 cores, 12 threads) ^[6,7]
Memory	16 GB DDR4-3200 MHz RAM (1 x 16 GB)
Memory Slots	2 SODIMM
Internal Storage	256 GB PCIe® NVMe™ SSD
Graphics	Integrated
Graphics (integrated)	Intel® UHD Graphics
Display	33.8 cm (13.3") diagonal, FHD (1920 x 1080), touch, IPS, narrow bezel, anti-glare, 250 nits, 45% NTSC
Display	13.3" diagonal, FHD (1920 x 1080), touch, IPS, narrow bezel, anti-glare, 250 nits, 45% NTSC ^[13,15,16,17]
Display size (diagonal)	33.8 cm (13.3")
Display size (diagonal)	13.3"
Audio	Dual stereo speakers, dual array microphones
Minimum dimensions (W x D x H)	30.69 x 20.84 x 1.59 cm
Minimum dimensions (W x D x H)	12.08 x 8.2 x 0.62 in
Weight	Starting at 1.22 kg <i>(Weight will vary by configuration. Does not include power adapter.)</i>
Weight	Starting at 2.7 lb <i>(Weight will vary by configuration. Does not include power adapter.)</i>
Keyboard	HP Premium Collaboration Keyboard – spill-resistant, backlit keyboard
Pointing device	Clickpad with multi-touch gesture support, taps enabled as default
Camera	IR camera
Ports	1 Thunderbolt™ 4 with USB Type-C® 40Gbps signaling rate (USB Power Delivery, DisplayPort™ 1.4); 2 USB Type-A 5Gbps signaling rate (1 power); 1 AC power; 1 HDMI 2.1; 1 stereo headphone/microphone combo jack; 1 RJ-45 ^[42] <i>(HDMI cable sold separately.)</i>
Wireless	Intel® Wi-Fi 6E AX211 (2x2) and Bluetooth® 5.3 wireless card (supporting gigabit data rate)
Power	HP Smart 45 W External AC power adapter ^[37]
Battery type	HP Long Life 3-cell, 42 Wh Li-ion
Battery weight	0.40 lb
Battery weight	181.83 g

Energy star certified

ENERGY STAR® certified

Management features

HP Client Management Script Library (download); HP Driver Packs (download); HP Client Catalog (download); HP Manageability Integration Kit Gen4 (download); HP Image Assistant Gen5 (download); HP Patch Assistant (download); HP Cloud Recovery; HP Connect for Microsoft Endpoint Manager^[22,23,24]

Sustainable impact specifications

Low Halogen; Bulk packaging available; Molded paper pulp cushion inside box is 100% sustainably sourced and recyclable; Outside box and corrugated cushions are 100% sustainably sourced and recyclable; 5% post-consumer recycled plastic; Ocean-bound plastic in speaker enclosure(s)

Security management

Absolute persistence module; HP Secure Erase; HP Sure Click; HP Sure Sense; BIOS Update via Network; HP Sure Admin; HP BIOSphere Gen6; HP Client Security Manager Gen7; TPM 2.0 embedded security chip (Common Criteria EAL4+ and FIPS 140-2 Level 2 Certified); HP Sure Start Gen7; HP Wake on WLAN; HP Tamper Lock; HP Sure Run Gen5; HP Sure Recover Gen5; Secured-Core PC Enable^[25,26,27,28,29,30,31,32,33,34]

Software included

HP Connection Optimizer; HP Hotkey Support; HP Power Manager; myHP; HP Privacy Settings; HP Notifications; HP PC Hardware Diagnostics Windows; HP Services Scan; HP Smart Support (download)^[20,21,38,57]

UPC number

(ABA) 197497076905; (ABL) 197497076899

Manufacturer Warranty

1-year and 3-year limited warranties and 90 day software limited warranty options depending on country. Batteries have a default one year limited warranty. Refer to <http://www.hp.com/support/batterywarranty/> for additional battery information. On-site service and extended coverage is also available. HP Care Pack Services are optional extended service contracts that go beyond the standard limited warranties. To choose the right level of service for your HP product, use the HP Care Pack Services Lookup Tool at: <http://www.hp.com/go/cpc> .

Additional specifications

Accessories	HP 435 Multi-Device Wireless Mouse 3B4Q5AA; HP 655 Wireless Mouse and Keyboard Combo 4R009AA; HP Universal USB-C Multiport Hub 50H55AA; HP Renew Business 15.6 Laptop Bag 3E5F8AA; HP 325 FHD Webcam 53X27AA
Battery brand	HP
Battery capacity	42
Battery capacity uom	Wh
Battery cells number	3
Battery life	Long Life
Battery life note	Battery is internal and not replaceable by customer. Serviceable by warranty.
Battery type	Li-ion
Bluetooth version	Bluetooth® 5.3
Brightness	250 nits
Camera Infrared	IR
Certifications and compliances	CCC; CECP; GS Mark
Color gamut	45% NTSC
Display	33.8 cm (13.3") diagonal FHD touch display
Display	13.3" diagonal FHD touch display
Display bezel	narrow bezel
Display brightness	250
Display brightness uom	nits
Display panel technology	IPS
Display resolution (pixels)	1920 x 1080
Display resolution standard	FHD
Display size (diagonal) uom	"
Display size (diagonal, imperial)	13.3
Display size (diagonal, metric)	33.8
Display size (diagonal, metric) uom	cm
Display surface treatment	anti-glare
Display touchscreen type	touch screen
ECC memory	non-ECC
Fingerprint reader	Fingerprint sensor
Keyboard backlight	backlit
Keyboard features	Spill-resistant

Keyboard name	HP Premium Collaboration Keyboard
Legal tagline	HP recommends Windows 11 Pro for business
Memory and storage	16 GB memory; 256 GB SSD storage
Memory layout (slots & size)	1 x 16 GB
Memory module type	DIMM
Memory size	16
Memory size uom	GB
Memory speed	3200
Memory speed uom	MHz
Memory type	DDR4
Number of memory slots	1
Playbook TS icon OS	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c03905482.png
Playbook TS icon battery life	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c03905264.png
Playbook TS icon connectivity	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08201987.png
Playbook TS icon dimensions NB	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08250394.png
Playbook TS icon display NB	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08205649.png
Playbook TS icon graphics	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08169202.png
Playbook TS icon memory	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08267700.png
Playbook TS icon processor	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08201972.png
Playbook TS icon storage	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08192819.png
Playbook TS icon weight imperial	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c05790117.png
Playbook TS icon weight metric	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08267650.png
Processor Brand	Intel®
Processor cache	12 MB L3
Processor core	10
Processor family	Core™ i7
Processor frequency technology	Intel® Turbo Boost Technology
Processor generation	13th Generation
Processor maximum frequency	5.0
Processor maximum frequency uom	GHz
Processor model	1355U
Processor threads	12
Product brand name	HP

Product long name specifications	HP EliteBook 630 13.3 inch G10 Notebook PC Wolf Pro Security Edition, 13.3", touch screen, Windows 11 Pro, Intel® Core™ i7, 16GB RAM, 256GB SSD, FHD
Product short name specifications	HP EliteBook 630 13.3 inch G10 Notebook PC Wolf Pro Security Edition, 13.3", Intel® Core™ i7, 16GB RAM, 256GB SSD
Security Software Licenses	HP Wolf Pro Security Edition (1 year)
Standard memory note	Transfer rates up to 3200 MT/s.
Storage capacity	256
Storage capacity uom 01	GB
Storage interface 01	PCIe®
Storage interface protocol 01	NVMe™
Storage type	SSD
Storage type 01	SSD
Touchscreen	Yes
UNSPSC code	43211503
Wireless Model	Wi-Fi 6E AX211
Wireless antenna	2x2
Wireless standard	Wi-Fi 6E
Wireless supplier	Intel®
Wireless transfer speeds	Supporting Gigabit data rate

[1] Not all features are available in all editions or versions of Windows. Systems may require upgraded and/or separately purchased hardware, drivers, software or BIOS update to take full advantage of Windows functionality. Windows is automatically updated and enabled. High speed internet and Microsoft account required. ISP fees may apply and additional requirements may apply over time for updates. See <http://www.windows.com>.

[6] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[7] Intel® Turbo Boost performance varies depending on hardware, software and overall system configuration. See <http://www.intel.com/technology/turboboost/> for more information.

[13] HD content required to view HD images.

[15] Resolutions are dependent upon monitor capability, and resolution and color depth settings.

[16] HP Sure View Reflect integrated privacy screen is an optional feature that must be configured at purchase and is designed to function in landscape orientation.

[17] Actual brightness will be lower with touchscreen or Sure View.

[20] HP Support Assistant requires Windows and Internet access.

[21] HP Services Scan is provided with Windows Update on select products and will check entitlement on each hardware device to determine if an HP TechPulse-enabled service has been purchased, and will download applicable software automatically. HP TechPulse is a telemetry and analytics platform that provides critical data around devices and applications. For full system requirements or to disable this feature, please visit <http://www.hpdaas.com/requirements>. Not applicable in China.

[22] HP Connect for Microsoft Endpoint Manager is available from the Azure Market Place for HP Pro, Elite, Z and Point-of-Sale PCs managed with Microsoft Endpoint Manager. Subscription to Microsoft Endpoint Manager required and sold separately. Network connection required.

[23] HP Manageability Integration Kit can be downloaded from <http://www8.hp.com/us/en/ads/clientmanagement/overview.html> .

[24] HP Patch Assistant available on select HP PCs with the HP Manageability Kit that are managed through Microsoft System Center Configuration Manager. HP Manageability Integration Kit can be downloaded from <http://www8.hp.com/us/en/ads/clientmanagement/overview.html> .

[25] HP Sure Click requires Windows 10 Pro or higher or Enterprise. See https://bit.ly/2PrLT6A_SureClick for complete details.

[26] HP Sure Sense is available on select HP PCs with Windows 10 Pro, Windows 10 Enterprise, Windows 11 Pro, or Windows 11 Enterprise OS25. HP Sure Run Gen5 is available on select HP PCs and requires Windows 10 and higher. HP Sure Recover Gen5 with Embedded Reimaging is an optional feature which requires Windows 10 and higher must be configured at purchase. You must back up important files, data, photos, videos, etc. before use to avoid loss of data. Network based recovery using Wi-Fi is only available on PCs with Intel Wi-Fi Module.

[27] HP Sure Run Gen5 is available on select HP PCs and requires Windows 10 and higher.

[28] HP Sure Recover Gen5 with Embedded Reimaging is an optional feature which requires Windows 10 and higher must be configured at purchase. You must back up important files, data, photos, videos, etc. before use to avoid loss of data. Network based recovery using Wi-Fi is only available on PCs with Intel Wi-Fi Module.

[29] HP Sure Start Gen7 is available on select HP PCs and requires Windows 10 and higher.

[30] HP Client Security Manager Gen7 requires Windows and is available on the select HP Elite and Pro PCs.

[31] HP BIOSphere Gen6 features may vary depending on the platform and configuration.

[32] HP Secure Erase for the methods outlined in the National Institute of Standards and Technology Special Publication 800-88 "Clear" sanitation method. HP Secure Erase does not support platforms with Intel® Optane™.

[33] Absolute firmware module is shipped turned off and can only be activated with the purchase a license subscription and full activation of the software agent. License subscriptions can be purchased for terms ranging multiple years. Service is limited, check with Absolute for availability outside the U.S. Certain conditions apply. For full details visit: <https://www.absolute.com/about/legal/agreements/absolute/>

[34] Secured-Core PC Enable requires an Intel® vPro® , AMD Ryzen™ Pro processor or Qualcomm® processor with SD850 or higher and requires 8 GB or more system memory. Secured-core PC is enabled from the factory.

[37] Availability may vary by country.

[38] HP Power Manager requires Windows 10 and higher and can be downloaded from the Microsoft Store.

[42] SuperSpeed USB 20Gbps is not available with Thunderbolt™ 4.

[57] HP Smart Support requires HP TechPulse to be installed. For more information about how to enable or to download HP Smart Support, please visit <http://www.hp.com/smart-support> .

Disclaimer — Copyright

Intel, Core, Iris and Intel vPro are trademarks or registered trademarks of Intel Corporation or its subsidiaries in the United States and other countries. Bluetooth is a trademark owned by its proprietor and used by HP Inc. under license. DisplayPort™ and the DisplayPort™ logo are trademarks owned by the Video Electronics Standards Association (VESA®) in the United States and other countries. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum. ENERGY STAR is a registered trademark of the U.S. Environmental Protection Agency. All other trademarks are the property of their respective owners.

© Copyright 2023 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements

accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – May 23, 2023 7:12 AM UTC+0000