



C2G
3ft (0.9m) Ultra Flexible High Speed HDMI® Cable with Low Profile Connectors - 4K 60Hz (3-Pack)
Part No. CG-C2G21008



3-Pack

The Ultra Flexible High Speed HDMI Cable with Low Profile Connectors supports all HDMI 2.0 features and is perfect for home theater or desktop audio video applications requiring high speed HDMI features and video resolutions up to 4K (4096 x 2160 at 60hz, 4:4:4). The ultra-flexible cable construction and the low profile, compact connector design make this cable an ideal fit for installations in tight spaces. The Ethernet capabilities of the cable allow a user to connect multiple Ethernet enabled HDMI devices through a single Ethernet connection for accessing interactive online content or updating device firmware. This fully-functional, high bandwidth cable is tested to perform at industry standards and is backed by a lifetime warranty. Experience the latest HDMI features including:

Learn more about how this C2G product and other C2G products can help you adapt your Chromebook to meet your needs by visiting our [Chromebook Adapters New Technology page](#).

Features & Benefits

Supports all HDMI 2.0 features including resolutions up to 4K (4096 x 2160 at 60hz, 4:4:4)

Supports HDMI features including 3D video

Ultra-flexible cable construction

Low profile, compact connector design

Specifications

General Info

Product Line	C2G	Color	Black
UPC Number	757120210085	Country Of Origin	China
Application Sector	Residential, Commercial	Type	Cable

Dimensions

Cable Length	3 ft
--------------	------

Technical Information

Jacket Material	Flexible PVC	Wire Gauge	36 AWG
Video Resolution	4K 60Hz, 4K 30Hz, 4K, 1080p	Bend Radius	25.4 mm
Cable Type	High Speed HDMI, Ultra-Flexible, Video	Jacket Rating	Standard Non-Rated
Data Transfer Rate	18 Gbps	Adapter Rear	HDMI Male
Adapter Front	HDMI Male		