



DAYTONA

Stable, reliable POS terminal that's made to last

Great reliability and an industrial project: **DAYTONA** is ideal for point-of-sale applications that require larger workload in multiple environments. The terminal is developed to support **any kind of software application** thanks to different CPU performance levels. DAYTONA establishes a new standard for touchscreen terminals, with **top-notch RAM and SSD**. Thanks to the easy-access SSD with **detached slot**, it won't be hard to open the device in case of assistance. This terminal is developed to be flexible, and can easily updated to become your company's most loyal helper.



CHARACTERISTICS

1. Field upgradeable

Quickly upgradeable RAM and SSD to increase system specifications

2. Optional Wi-Fi® antenna

No need for cabling - easily upgrade to high speed wireless access

3. USB-C on all 4 sides of the terminal for proprietary peripherals

Consolidate peripheral integrations for attended and unattended applications

4. Multiple CPU options

Celeron® and i3 configurations: keep consistent look and feel across your business environment

5. Multiple operating systems

Compatible in both Windows 10 IoT, Windows 11 (only i3 model), and Linux

6. Cable management

Easily hide cables in the base for a clean installation

MARKETS

- Retail
- Hospitality
- Entertainment
- Gaming, Lottery and Betting

MODELS

- Windows® - J3455 8GB/128GB SSD - 4:3 (15")
 - Windows® - i3 8145UE 8GB/128GB SSD - 4:3 (15")
-

ACCESSORIES

- Second display 10.1"
 - Customer display LCM 2x20
 - MSR
-

TECHNICAL SHEET

	WINDOWS® - J3455	WINDOWS® - i3 8145UE
Processor	Celeron® J3455, 2M Cache, up to 2.3GHz	Intel®, Core i3 8145UE, 4M Cache, up to 3,90GHz, TPM 2.0
Memory	1 x SO-DIMM, DDR3L, 8GB	2 x SO-DIMM, DDR4 8GB Up to 32GB
Storage	2.5" SATA SSD, 128GB	
I/O	USB: 3.0 x 4, 2.0 x 2, TypeC x 1 (TYPE C USB 2.0 HS only 5V/2A) Serial ports: RJ50 x 2 Display: HDMI x 1 up to 1920x1080 LAN: RJ45 x 1 Cash Drawer: RJ11 x 1	USB: 3.0 x 4, 2.0 x 2, TypeC x 1 (TYPE C USB 2.0 HS only 5V/2A) Serial ports: RJ50 x 1 Display: HDMI x 1 up to 1920x1080 LAN: RJ45 x 2 Cash Drawer: RJ11 x 1
LCD	15" TFT	
Brightness	350 NITS	
Resolution	1024x768	
Touch screen	PCAP True Flat	
Speaker	1 x 3W	
Expansion	M 2 E Key for Wi-Fi®/Bluetooth® (Module optional) MiniPCle	
OS	Windows® 10 IOT	Windows® 10 IOT / Windows® 11
Electrical specifications	Device: 60 W/12 V DC Jack Adapter Power supply: from 100 Vac to 240 Vac	
Dimensions	362 mm (L) x 210 mm (W) x 330 mm (H)	
Weight	4.9 Kg	

MODELS



934MS011500L33

PCPOS DAYTONA 15" NO OS SSD
128GB J3455 8GB



934MS011700L33

PCPOS DAYTONA 15" NO OS SSD
128GB i3-8145UE 8GB



934MS012200L33

PCPOS DAYTONA 15" WIN SSD
128GB J3455 8GB



934MS012400L33

PCPOS DAYTONA 15" WIN SSD
128GB i3-8145UE 8GB

Via Berettine, 2 - 43010 Fontevivo PR - VAT: IT02498250345 - TEL: +39 0521 680111 - FAX: +39 0521 610701 - UNIQUE CODE: 8RQN7AZ

The technical data on this website are not binding and may be changed without advanced notice.

Last update: 22 December 2023