

ThinkPad E14 Gen 5 (AMD)

Weighing at just 1.41 kg (3.11 lbs), this ThinkPad is built to amplify business computing for the hybrid workforce. It is powered by AMD Ryzen 7 processors and AMD Radeon Graphics to tackle heavy workloads- from trading to video editing and beyond. The multiple ports such as Wi-Fi 6 facilitate stable network connectivity for on-the-go users whereas the USB-C 3.2 Gen 1 port support data transfers, power delivery and compatibility with a wide range of devices and peripherals.



Combining efficiency with compatibility

The 14" multi-touch screen allows users to interact with the device while using touch-based applications or working with creative software. The anti-glare surface, 16:10 aspect ratio, 100% sRGB color gamut offers an immersive visual experience.

Advanced security and collaboration features

Multimedia features such as Synaptic HD audio chip, dual Dolby Atmos speakers, Dolby Voice dual-array mics and FHD 1080p camera ensure users engage in productive communication and have professional-grade web conferences.

Smart features for the smarter you

Minimal preloaded applications mean maximum battery life and responsiveness for users, and faster deployment for IT admins.

Lenovo devices that are a class apart

The entry-level ThinkPad, E Series features the famous keyboard and trackpoint, and is MIL-SPEC tested ensuring the build quality for which ThinkPad is renowned.

Lenovo services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



Return To Depot Repair Warranty

- No-hassle repair process at a Lenovo service center
- Lenovo pays for all shipping between the customer and service facility
- Avoid unplanned operational expense with a simple annual fee

Accessories

Lenovo 15.6" Laptop Casual Backpack

- Extra cushioning and padding for maximum comfort
- Waterproof fabric to keep your gadgets dry and safe
- Conveniently placed compartments and pockets for easy access.



PN: GX40Q17225

Lenovo Go USB-C ANC In-Ear Headphones

- Microsoft Teams certified, with premium ANC and ENC technology
- Best-in-class noise cancellation with inline separate mic for better voice pickup
- Comes with a multifunctional control box designed for easy use



PN: 4XD1C99220, GXD1C99237

ThinkPad E14 Gen 5 (AMD)

Key Specifications

Processor

AMD Ryzen 3 / 5 / 7

Operating System

Windows 11 Pro, Windows 11 Home, Windows 11 Home Single Language, Windows 11 DG Windows 10 Pro 64

Display

14", WUXGA (1920x1200), IPS, Anti-glare surface, 16:10 Aspect Ratio

- 300nits Brightness, 45% NTSC Color Gamut

- 300nits Brightness, 45% NTSC Color Gamut, touch

14", 2.2K (2240x1400), IPS, Anti-glare surface, 16:10 Aspect Ratio

- 300nits Brightness, 100% sRGB Color Gamut, Eyesafe Certified

Touchscreen

Optional Multi-touch

Graphics

AMD Radeon Graphics (integrated)

Memory

Up to 40GB DDR4-3200 offering

1x Soldered + 1x SO-DIMM

Storage

Up to two M.2 PCIe NVMe SSD

M.2 2242 SSD up to 512GB

M.2 2280 SSD up to 1TB

Audio

High Definition (HD) Audio

2W x2, Dolby Atmos Stereo speakers

Dolby Voice Dual-array microphone

Battery[†]

47Wh or 57Wh battery, up to 15.03 hr Battery life, Rapid Charge support

Power Adapter

One of the following

65W USB-C (2-pin)

65W USB-C (3-pin)

Camera

One of the following

FHD 1080p + IR Hybrid with Privacy Shutter

FHD 1080p with Privacy Shutter

HD 720p with Privacy Shutter

Keyboard

6-row, spill-resistant, optional backlight, TrackPoint and Mylar surface touchpad

56 x 115 mm (2.24 x 4.53 inches)

Dimensions

Starting at 313 x 219.3 x 17.99 mm (12.32 x 8.63 x 0.71 inches)

Weight

Aluminium bottom cover: starting at 1.53 kg (3.37 lbs) PC-ABS bottom cover: starting at 1.41 kg (3.11 lbs)

Green Certifications

EPEAT Gold Registered, ENERGY STAR 8.0, ErP Lot 6, ErP Lot 26, FSC certified carton, TCO Certified 9.0, RoHS compliant

Other Certifications

(Optional) Eyesafe Certified 2.0, (Optional) TUV Rheinland Low Blue Light (Hardware Solution), (Optional) TUV Rheinland Low Blue

Light (Software Solution)

Connectivity

I/O Ports

1x USB 3.2 Gen 1, 1x USB 3.2 Gen 1, 1x USB-C 3.2 Gen 1, 1x USB-C 3.2 Gen 2, 1x HDMI 1.4b, 1x Ethernet (RJ-45), 1x Headphone / microphone combo jack (3.5mm)

WLAN + Bluetooth

One of the following

Realtek Wi-Fi 6 RTL8852BE, 11ax 2x2 + BT5.1

Realtek Wi-Fi 6E RTL8852CE, 11ax 2x2 + BT5.1

Wi-Fi 6, 11ax 2x2 + BT5.1

Wi-Fi 6E, 11ax 2x2 + BT5.1

Docking

Various docking solutions supported via USB-C.

Security & Privacy

Fingerprint Reader

IR Camera with Windows Hello

Discrete TPM 2.0, TCG certified

Firmware TPM 2.0

Kensington Nano Security Slot

Camera privacy shutter

Touch style fingerprint reader

IR camera for Windows Hello

Manageability

Non-DASH