



HP ProBook 450 15.6 inch G10 Notebook PC Wolf Pro Security Edition (822P3UT)



Overview

Essential, commercial-grade features

The HP ProBook 450 15-inch laptop provides growing businesses with the commercial-grade performance, multi-layered endpoint security, and durability in an easily upgradeable design. Powered by the latest Intel® processor[2] and long battery life, this feature-rich PC is well-equipped for long-term productivity and helps enable hybrid work.

Optimized for hybrid work

Look your best wherever you work with enhanced camera features and lighting adjustments.[3]

Tested for durability

Passed 19 MIL-STD tests[6] for durability and easily serviceable—helping make the most of your IT investment.

Performance for growing business

Keep up with demanding tasks with the latest Intel® CPU[2,4], long battery life, and upgradeable memory and storage.

Protected by HP Wolf Security

HP Wolf Pro Security Edition PCs interlace HP Sure Click Pro with HP Sure Sense Pro providing more in-depth coverage than the standard versions through a 1-year or 3-year user license with HP Support.[6] This creates a powerful, single solution that doesn't require an IT-managed PC environment.

Features

Windows 11

Work anywhere without compromising on performance or security with Windows 11 powered by HP's collaboration and connectivity technology.

Security is your top priority

The HP Wolf Pro Security Edition provides preconfigured enterprise-level PC protection for small and medium sized businesses.^[1]

Fast and efficient wireless LAN

The portability of your PC and the reliability of a fast connection determines where you can work. Get a fast and reliable connection in dense wireless environments with gigabit-speed Wi-Fi 6.^[7]

HP Sure Sense

Malware is evolving rapidly and traditional antivirus can't always recognize new attacks. Protect your PC against never-before-seen attacks with HP Sure Sense, which uses deep learning AI to provide exceptional protection against advanced malware.

Browse confidently

Help protect your PC from websites and read only Microsoft Office and PDF attachments with embedded malware, ransomware, or viruses with hardware-enforced security from HP Sure Click.^[8]

Work without interruption

Keep productivity high and downtime low with the fully integrated and automated features of the HP BIOSphere Gen6 firmware ecosystem. Your PCs have extra protection thanks to automatic updates and security checks.^[9]

[2] Multicore is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[3] Requires myHP application and Windows OS.

[4] Optional feature that must be configured at the time of purchase.

[6] MIL-STD testing is not intended to demonstrate fitness for U.S. Department of Defense contract requirements or for military use. Test results are not a guarantee of future performance under these test conditions. Accidental damage requires an optional HP Accidental Damage Protection Care Service.

[1] This product includes a one (1) year license of HP Wolf Pro Security Edition which includes HP Sure Click Pro and HP Sure Sense Pro. The HP Wolf Pro Security Edition software is licensed under the license terms of the HP End User License Agreement (EULA) that can be found at: https://support.hp.com/us-en/document/ish_3875769-3873014-16 as modified by the following: "7. Term. Unless otherwise terminated earlier pursuant to the terms contained in this EULA, the license for the HP Wolf Pro Security Edition (HP Sure Sense Pro and HP Sure Click Pro) is effective upon activation and will continue for twelve (12) months thereafter ("Initial Term"). At the end of the Initial Term you may either (a) purchase a renewal license for the HP Wolf Pro Security Edition from HP.com, HP Sales or an HP Channel Partner, or (b) continue using the standard versions of HP Sure Click and HP Sure Sense at no additional cost with no future software updates or HP Support."

[7] Wireless access point and internet service required and sold separately. Availability of public wireless access points limited. Wi-Fi 6 is backwards compatible with prior 802.11 specs. The specifications for Wi-Fi 6 (802.11ax) are draft and are not final. If the final specifications differ from the draft specifications, it may affect

the ability of the PC to communicate with other 802.11ax devices. Wi-Fi® supporting gigabit speeds is achievable with Wi-Fi 6 (802.11ax) when transferring files between two devices connected to the same router. Requires a wireless router, sold separately, that supports 160MHz channels.

[8] HP Sure Click supports Microsoft® Internet Explorer and Chromium™. Supported attachments include Microsoft Office (Word, Excel, PowerPoint) and PDF files in read only mode, when Microsoft Office or Adobe Acrobat are installed.

[9] HP BIOSphere Gen6 requires Windows 10 and is available on select HP Pro and Elite PCs. Features may vary depending on the platform and configurations.

Specifications

Operating system	Windows 11 Pro ^[1]
Product color	Pike silver plastic
Processor family	13th Generation Intel® Core™ i5 processor
Processor	Intel® Core™ i5-1335U (up to 4.6 GHz with Intel® Turbo Boost Technology, 12 MB L3 cache, 10 cores, 12 threads) ^[6,7]
Memory	8 GB DDR4-3200 MHz RAM (1 x 8 GB)
Memory Slots	2 SODIMM
Internal Storage	256 GB PCIe® NVMe™ SSD
Graphics	Integrated
Graphics (integrated)	Intel® UHD Graphics
Display	39.6 cm (15.6") diagonal, FHD (1920 x 1080), IPS, narrow bezel, anti-glare, 250 nits, 45% NTSC
Display	15.6" diagonal, FHD (1920 x 1080), IPS, narrow bezel, anti-glare, 250 nits, 45% NTSC ^[14,15,16]
Display size (diagonal)	39.6 cm (15.6")
Display size (diagonal)	15.6"
Audio	Dual stereo speakers, dual array microphones
Minimum dimensions (W x D x H)	35.94 x 23.39 x 1.99 cm
Minimum dimensions (W x D x H)	14.14 x 9.2 x 0.78 in
Weight	Starting at 1.79 kg <i>(Weight will vary by configuration. Does not include power adapter.)</i>
Weight	Starting at 3.94 lb <i>(Weight will vary by configuration. Does not include power adapter.)</i>
Keyboard	HP Premium Keyboard – spill-resistant, backlit keyboard with numeric keypad
Pointing device	Clickpad with multi-touch gesture support, taps enabled as default
Camera	720p HD camera
Ports	2 USB Type-A 5Gbps signaling rate (1 charging, 1 power); 1 AC power; 1 HDMI 2.1; 1 stereo headphone/microphone combo jack; 1 RJ-45; 2 USB Type-C® 10Gbps signaling rate (USB Power Delivery, DisplayPort™ 2.1) <i>(HDMI cable sold separately.)</i>
Package dimensions (W x D x H)	6.9 x 48.3 x 30.5 cm
Wireless	Intel® Wi-Fi 6E AX211 (2x2) and Bluetooth® 5.3 wireless card (supporting gigabit data rate)
Power	45 W USB Type-C™ adapter ^[37]
Battery type	HP Long Life 3-cell, 42 Wh Li-ion
Energy star certified	ENERGY STAR® certified

Management features

HP Client Management Script Library (download); HP Driver Packs (download); HP Client Catalog (download); HP Manageability Integration Kit Gen4 (download); HP Image Assistant Gen5 (download); HP Cloud Recovery^[20,21]

Sustainable impact specifications

Low Halogen; Bulk packaging available; Molded paper pulp cushion inside box is 100% sustainably sourced and recyclable; Outside box and corrugated cushions are 100% sustainably sourced and recyclable; 10% post-consumer recycled plastic

Security management

Absolute persistence module; HP DriveLock and Automatic DriveLock; HP Secure Erase; HP Sure Click; HP Sure Sense; BIOS Update via Network; HP Sure Admin; HP BIOSphere Gen6; HP Client Security Manager Gen7; TPM 2.0 embedded security chip (Common Criteria EAL4+ and FIPS 140-2 Level 2 Certified); HP Sure Start Gen7; HP Wake on WLAN; HP Tamper Lock; HP Sure Run Gen5; Secured-Core PC Enable^[22,23,24,25,26,27,28,29,30,31,32,33,34]

Software included

HP Connection Optimizer; HP Hotkey Support; HP Support Assistant; HP Power Manager; myHP; HP Privacy Settings; HP Notifications; HP QuickDrop; HP PC Hardware Diagnostics Windows; HP Services Scan; HP Smart Support (download)^[17,18,19,44,45]

UPC number

(ABA) 197497290592; (ABL) 197497290585

Manufacturer Warranty

1-year and 3-year limited warranties and 90 day software limited warranty options depending on country. Batteries have a default one year limited warranty. Refer to <http://www.hp.com/support/batterywarranty/> for additional battery information. On-site service and extended coverage is also available. HP Care Pack Services are optional extended service contracts that go beyond the standard limited warranties. To choose the right level of service for your HP product, use the HP Care Pack Services Lookup Tool at: <http://www.hp.com/go/cpc> .

Additional specifications

Accessories	HP Universal USB-C Multiport Hub 50H55AA; HP Prelude Pro Recycle Backpack 1X644AA; HP 355 Compact Multi-Device Bluetooth Keyboard 692T0AA; HP 128 Laser Wired Mouse 265D9AA; HP 325 FHD Webcam 53X27AA
Battery brand	HP
Battery capacity	42
Battery capacity uom	Wh
Battery cells number	3
Battery life	Long Life
Battery life note	Battery is internal and not replaceable by customer. Serviceable by warranty.
Battery type	Li-ion
Bluetooth version	Bluetooth® 5.3
Brightness	250 nits
Camera resolution (vertical)	720p
Camera resolution standard	HD
Color gamut	45% NTSC
Display	15.6" diagonal FHD display
Display	39.6 cm (15.6") diagonal FHD display
Display bezel	narrow bezel
Display brightness	250
Display brightness uom	nits
Display panel technology	IPS
Display resolution (pixels)	1920 x 1080
Display resolution standard	FHD
Display size (diagonal) uom	"
Display size (diagonal, imperial)	15.6
Display size (diagonal, metric)	39.6
Display size (diagonal, metric) uom	cm
Display surface treatment	anti-glare
ECC memory	non-ECC
Graphic card footnote number	[43]
Keyboard backlight	backlit
Keyboard features	Spill-resistant

Keyboard keypad	numeric keypad
Keyboard name	HP Premium Keyboard
Legal tagline	HP recommends Windows 11 Pro for business
Memory and storage	8 GB memory; 256 GB SSD storage
Memory layout (slots & size)	1 x 8 GB
Memory module type	DIMM
Memory size	8
Memory size uom	GB
Memory speed	3200
Memory speed uom	MHz
Memory type	DDR4
Number of memory slots	1
Package dimensions (W x D x H)	2.71 x 19.01 x 12 in
Playbook TS icon OS	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c03905482.png
Playbook TS icon battery life	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c03905264.png
Playbook TS icon connectivity	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08201987.png
Playbook TS icon dimensions NB	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08250394.png
Playbook TS icon display NB	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08205649.png
Playbook TS icon graphics	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08169202.png
Playbook TS icon memory	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08267700.png
Playbook TS icon processor	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08201972.png
Playbook TS icon storage	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08192819.png
Playbook TS icon weight imperial	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c05790117.png
Playbook TS icon weight metric	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08267650.png
Processor Brand	Intel®
Processor cache	12 MB L3
Processor core	10
Processor family	Core™ i5
Processor frequency technology	Intel® Turbo Boost Technology
Processor generation	13th Generation
Processor maximum frequency	4.6
Processor maximum frequency uom	GHz
Processor model	1335U
Processor threads	12

Product brand name	HP
Product long name specifications	HP ProBook 450 15.6 inch G10 Notebook PC Wolf Pro Security Edition, 15.6", Windows 11 Pro, Intel® Core™ i5, 8GB RAM, 256GB SSD, FHD
Product short name specifications	HP ProBook 450 15.6 inch G10 Notebook PC Wolf Pro Security Edition, 15.6", Intel® Core™ i5, 8GB RAM, 256GB SSD
Security Software Licenses	HP Wolf Pro Security Edition (1 year)
Standard memory note	Transfer rates up to 3200 MT/s.
Storage capacity	256
Storage capacity uom 01	GB
Storage interface 01	PCIe®
Storage interface protocol 01	NVMe™
Storage type	SSD
Storage type 01	SSD
Touchscreen	No
UNSPSC code	43211503
Wireless Model	Wi-Fi 6E AX211
Wireless antenna	2x2
Wireless standard	Wi-Fi 6E
Wireless supplier	Intel®
Wireless transfer speeds	Supporting Gigabit data rate

[1] Not all features are available in all editions or versions of Windows. Systems may require upgraded and/or separately purchased hardware, drivers, software or BIOS update to take full advantage of Windows functionality. Windows is automatically updated and enabled. High speed internet and Microsoft account required. ISP fees may apply and additional requirements may apply over time for updates. See <http://www.windows.com>.

[6] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[7] Intel® Turbo Boost performance varies depending on hardware, software and overall system configuration. See <http://www.intel.com/technology/turboboost/> for more information.

[14] High-definition (HD) / Full high-definition (FHD) content required to view HD /FHD images.

[15] Resolutions are dependent upon monitor capability, and resolution and color depth settings.

[16] Actual brightness will be lower with touchscreen.

[17] HP Support Assistant requires Windows and Internet access.

[18] HP Quick Drop requires Internet access and Windows 10 or higher PC preinstalled with HP QuickDrop app and either an Android device (phone or tablet) running Android 7 or higher with the Android HP QuickDrop app, and /or an iOS device (phone or tablet) running iOS 12 or higher with the iOS HP QuickDrop app.

[19] HP Smart Support requires HP TechPulse to be installed. For more information about how to enable or to download HP Smart Support, please visit <http://www.hp.com/smart-support>.

[20] HP Manageability Integration Kit can be downloaded from <http://www8.hp.com/us/en/ads/clientmanagement/overview.html> .

[21] HP Cloud Recovery is available for Z by HP, HP Elite and Pro desktops and laptops PCs with Intel® or AMD processors and requires an open, wired network connection. Note: You must back up important files, data, photos, videos, etc. before use to avoid loss of data. Detail please refer to: <https://support.hp.com/us-en/document/c05115630> .

[22] Absolute agent is shipped turned off, and will be activated when customers activate a purchased subscription. Subscriptions can be purchased for terms ranging multiple years. Service is limited, check with Absolute for availability outside the U.S. The Absolute Recovery Guarantee is a limited warranty. Certain conditions apply. For full details visit: <http://www.absolute.com/company/legal/agreements/computrace-agreement> . Data Delete is an optional service provided by Absolute Software. If utilized, the Recovery Guarantee is null and void. In order to use the Data Delete service, customers must first sign a Pre-Authorization Agreement and either obtain a PIN or purchase one or more RSA SecurID tokens from Absolute Software.

[23] HP Secure Erase: For the methods outlined in the National Institute of Standards and Technology Special Publication 800-88 "Clear" sanitation method. HP Secure Erase does not support platforms with Intel® Optane™.

[24] HP Sure Click requires Windows 10 Pro or higher or Enterprise. See https://bit.ly/2PrLT6A_SureClick for complete details.

[25] HP Sure Sense is available on select HP PCs with Windows 10 Pro, Windows 10 Enterprise, Windows 11 Pro, or Windows 11 Enterprise OS.

[26] HP Sure Run Gen5 is available on select HP PCs and requires Windows 10 and higher.

[27] HP Sure Recover Gen5 with Embedded Reimaging is an optional feature which requires Windows 10 and higher must be configured at purchase. You must back up important files, data, photos, videos, etc. before use to avoid loss of data. Network based recovery using Wi-Fi is only available on PCs with Intel Wi-Fi Module.

[28] HP Sure Start Gen7 is available on select HP PCs and requires Windows 10 and higher.

[29] HP Sure Admin requires Windows 10 or higher, HP BIOS, HP Manageability Integration Kit from <http://www.hp.com/go/clientmanagement> and HP Sure Admin Local Access Authenticator smartphone app from the Android or Apple store.

[30] HP Client Security Manager Gen7 requires Windows and is available on the select HP Elite and Pro PCs.

[31] HP BIOSphere Gen6 features may vary depending on the platform and configuration.

[32] HP Secure Erase for the methods outlined in the National Institute of Standards and Technology Special Publication 800-88 "Clear" sanitation method. HP Secure Erase does not support platforms with Intel® Optane™.

[33] HP Fingerprint sensor is an optional feature that must be configured at purchase.

[34] Secured-Core PC Enable requires an Intel® vPro® , AMD Ryzen™ Pro processor or Qualcomm® processor with SD850 or higher and requires 8 GB or more system memory. Secured-core PC is enabled from the factory.

[37] Availability may vary by country.

[44] HP Power Manager requires Windows 10 and higher and can be downloaded from the Microsoft Store.

[45] HP Services Scan is provided with Windows Update on select products and will check entitlement on each hardware device to determine if an HP TechPulse-enabled service has been purchased, and will download applicable software automatically. HP TechPulse is a telemetry and analytics platform that provides critical data around devices and applications. For full system requirements or to disable this feature, please visit <http://www.hpdaas.com/requirements> . Not applicable in China.

Disclaimer — Copyright

Intel, Core, Pentium, Iris and Intel vPro are trademarks or registered trademarks of Intel Corporation or its subsidiaries in the United States and other countries. NVIDIA, the NVIDIA logo are trademarks and/or registered trademarks of

NVIDIA Corporation in the U.S. and other countries. Bluetooth is a trademark owned by its proprietor and used by HP Inc. under license. DisplayPort™ and the DisplayPort™ logo are trademarks owned by the Video Electronics Standards Association (VESA®) in the United States and other countries. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum. SDXC is a registered trademark of SD-3C in the United States, other countries or both. ENERGY STAR is a registered trademark of the U.S. Environmental Protection Agency. All other trademarks are the property of their respective owners.

© Copyright 2023 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – May 23, 2023 12:25 PM UTC+0000