

DISPLAY

Panel Size:	105"
Panel Type:	TFT LCD Module with DLED Backlight, VA
Display Area (mm):	2465.92(H) x 1049.56 (V) (104.6"diagonal)
Aspect Ratio:	21:9
Resolution:	WUHD 5120x2160(Pixels)
Colors:	1.07B colors (10bit)
Brightness:	400 nits (typ.) 300 nits (min.)
Contrast Ratio:	4000:1(Typ.) 5000:1(Min. with DCR enabled)
Response Time:	6.5ms
Viewing Angles:	H = 178, V = 178 (Typ.)
Backlight Life:	30,000 Hours (Min.)
Surface Treatment:	Panel Hard Coating 3H Glass Anti-Glare 7H
Bezel:	19.5/19.5/29.8/41.2
Orientation:	Landscape

PLATFORM

Processor:	Octa-Core CPU (A76*4 + A55*4)
RAM:	8GB LPDDR
Storage:	64GB eMMC

TOUCH

Type/ Tech:	IR Recognition
Touch Resolution:	32767 x 32767
Touch Point:	Windows: 40 Android: 20

INPUT

HDMI:	x3 (HDMI 2.0) (HDMI 2 & 3 & 4 support CEC) x1 (HDMI 2.1) (HDMI 1 support CEC)
DisplayPort:	1
Audio:	1
MIC(Microphone):	Yes
RS232:	1
OPS:	1

OUTPUT

HDMI:	1
Audio:	1
SPDIF:	1

LAN

RJ45:	1 in 1 out 1G for Android & OPS, type-C 100M
-------	---

USB

Type A:	USB2.0 * 1 (bottom) (for FW upgrade) USB3.0 * 6 (Top*2 + Rear *2 + Front *2), all support Smart USB
Type B:	3 (bottom x 1; side x 2)
Type C:	1 (side) [1*PD65W(65W with OPS, 100W without OPS) + DP1.2 + Data + 10M/100M sharing] 1 (Front) (1*PD15W + DP1.2 + Data + 10M/100M sharing)

SPEAKERS

16W x 2 + 15W x 1 subwoofer

TOP CAMERA PLATE

Yes

COMPATIBILITY

HDMI:	5120x2160
-------	-----------

EMBEDDED OS

Android 13

BUNDLE SOFTWARE

Wireless Presentation:	EAirplay, Miracast
------------------------	--------------------

SPECIAL FEATURES

All-in-one USB port:	Yes
One Click to Cloud Drive:	Yes
Simple LAN sharing between IFP and slot-in device:	(10/100/1000M) (USB Type-C 10/100, Android & PC 10/100/1000)
Light Sensor:	x1

POWER

Voltage:	100-240VAC +/- 10% Wide Range
Consumption:	On: TBD W(typ.) / Off: <0.5W

ERGONOMICS

Wall Mount (VESA®):	1000 x 400
----------------------	------------

OPERATING CONDITIONS

Temperature (° C):	0°C to 40°C
Humidity:	20% ~ 80% RH non-condensing

DIMENSIONS (W X H X D)

Physical (inch / mm):	98.71 x 44.49 x 4.06 in / 2507.2 x 1130.1 x 103.2mm
Packaging (inch / mm):	105.19 x 11.02 x 51.38 in / 2668 x 280 x 1305mm

WEIGHT

Net (lb / kg):	201.5lb/91.4Kg
Gross (lb / kg):	263.5lb/119.5Kg

REGULATIONS

CB, cTUVus, FCC/FCC IC , CE-EMC&RCM, ERP, UKCA-EMC, UKCA-Safety, BSMI-EMC, BSMI-Safety, LBL, Flicker free

PACKAGE CONTENTS

1. 3m power cord by ship area
2. Remote control with AAA battery
3. 3m touch USB cable
4. Touch pen x 2
5. Quick Start Guide + Compliance statement
6. RS232 adapter
7. Clamp x 5
8. Camera Plate
9. Screw x 6 (2 for camera , 4 for wall mount)
10. HDMI cable 3m